



Halolite

QVF133/135/137/139

Halolite

Halolite is a floodlight with a compact and sturdy design. It is light weight with a die-casted aluminium housing and corrosion-proof powder coating. Its high grade anodised reflectors provide an efficient beam for either downward or upward applications. Easy lamp replacement and rear access for mains connection. Merchandise packaging is available.

Benefits

- Compact and sturdy design
- Rugged, light weight, corrosion-proof, die-casted aluminium housing with powder coating
- High-grade anodised reflectors to provide an efficient beam for either downwards or upwards application
- Toughened glass cover and IP54 waterproof and heat resistant silicon gaskets
- Easy lamp replacement through front window and easy rear access for main connections

Features

- Compact and sturdy design
- Rugged, light weight, corrosion-proof, die-casted aluminium housing with powder coating
- High-grade anodized reflectors to provide an efficient beam for either downward or upward applications
- Toughened glass cover
- IP54; waterproof and heat resistant silicone gaskets
- Wide light beam
- Easy lamp replacement through front window without affecting beam adjustment
- Easy rear access for main connections

Halolite

Application

- Garden lighting
- Billboard lighting
- Sculptures
- Security lighting

Versions



QVF135 HAL-TDS500W

