



CoreLine Panel – the clear choice for LED

CoreLine Panel

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Enables a simple switch from basic conventional luminaires to LED luminaires
- Energy savings of up to 50% compared to functional TL-D luminaires
- Uniform surface of light
- Easy connection (with looping)

Features

- Integrated LED technology
- Slim housing made from aluminum
- Choice of two color temperatures: 3000 and 4000 K
- Non-Office Compliant (NOC) version and Office Compliant version (OC) available
- Suspension and plaster-ceiling installations are possible with accessories
- Optional emergency lighting

Application

- Offices
- Retail
- Healthcare

Specifications

CoreLine Panel

Type	RC132V (module size 600 mm version)
	RC133V (module size 625 mm version)
Ceiling type	Exposed T-bar ceiling
Ceiling grid	Module size in length: 600 mm
	Module size in length: 625 mm
Light source	Non-replaceable LED module
Power (+/-10%)	Standard version: 41 W
	NOC version: 42 W
Beam angle	Standard version: 110°
	NOC version: 120°
Luminous flux	3400 lm
Correlated Color	3000 K
Temperature	4000 K
Color Rendering Index	> 80
Lumen maintenance at median useful life*	L75
50000 h	
Control gear failure rate	5%
at median useful life	
50000 h	

Performance Ambient	+25 °C
Temperature Tq	
Operating temperature range	+10 to +40°C
Driver	Built-in
Mains voltage	230 or 240 V / 50-60 Hz
Material	Housing: zinc-coated steel
	Rim and diffuser: plastic (aluminum rim for NOC versions)
	Optical cover: PMMA
Color	White (RAL 9003)
Connection	Push-in connector (PI) or with pull relief (PIP)
Maintenance	Optical module sealed for life; no internal cleaning required
Installation	Individual; lay-in in exposed ceiling grids
	No through-wiring possible
Remarks	Includes safety cable


Specifications

Type	RC127V (module size 600 x 600 and 300 x 1200 mm versions)
	RC128V (module size 625 x 625 mm version)
Ceiling type	Exposed T-bar ceiling
Ceiling grid	Module size in length: 600 mm
	Module size in length: 625 mm
	Module size in length: 1200 mm
Light source	Non-replaceable LED module
Power	42 W
Beam angle	120°
Luminous flux	3400 lm
Correlated Color	3000 K
Temperature	4000 K
Color Rendering Index	> 80
Median useful life	50,000 hours
L70B50	
Median useful life	30,000 hours
L80B50	
Median useful life	15,000 hours
L90B50	

Driver failure rate	0.38% per 5000 hours
Average ambient temperature	+25 °C
Operating temperature range	+10 to +40 °C
Driver	Separate
Mains voltage	220-240 V / 50-60 Hz
Dimming	DALI
Material	Housing: steel
	Rim: aluminum
	Diffuser: polystyrene
Color	White (RAL 9003)
Connection	Push-in connector (PI) or with pull relief (PIP)
Maintenance	Optical module sealed for life; no internal cleaning required
Installation	Individual; lay-in in exposed ceiling grids
	No through-wiring possible
Remarks	Includes safety cable

CoreLine Panel

Versions



CoreLine Panel - LED module
3600 lm - 840 neutral white -
Power supply unit with DALI
interface



CoreLine Panel - LED module
3600 lm - 840 neutral white -
Power supply unit with DALI
interface



RC132V W30L60

Product details



CoreLine
Panel_RC132V_W60L60_RC133V_
W62L62_PSU-DPP.TIF



CoreLine Panel
RC132V_W60L60_RC133V_W62L6
2_plaster ceiling-DPP.TIF



CoreLine Panel
RC132V_W60L60_RC133V_W62L6
2_surface mounted-DPP.TIF



CoreLine Panel
RC132V_W60L60_RC133V_W62L6
2_suspended-DPP.TIF

CoreLine Panel

Product details



CoreLine
Panel_RC132V_connection box-
DPP.TIF



CoreLine
Panel_RC132V_RC133V_with
integrated driver-DPP.TIF



Connection of safety cable to
CoreLine Panel



CoreLine Panel PSU connection



CoreLine
Panel_RC132V_W30L60_PSU-
DPP.TIF



CoreLine Panel
RC132V_W30L60_plaster ceiling-
DPP.TIF



CoreLine Panel
RC132V_W30L60_surface
mounted-DPP.TIF



CoreLine Panel
RC132V_W30L60_suspended-
DPP.TIF

CoreLine Panel

Product details



CoreLine
Panel_RC132V_W30L120_PSU-
DPP.TIF



CoreLine Panel
RC132V_W30L120_plaster ceiling-
DPP.TIF



CoreLine Panel
RC132V_W30L120_surface
mounted-DPP.TIF



CoreLine Panel
RC132V_W30L120_suspended-
DPP.TIF



Smooth optic for office compliant
panel



CoreLine Panel Dali connection



CoreLine
Panel_RC132V_W60L60_RC133V_
W62L62_IA1-DPP.TIF



CoreLine Panel IA1 connection

CoreLine Panel

Product details



CoreLine
Panel_RC132V_W30L120_IA1-
DPP.TIF



Connection of suspension cable to
CoreLine Panel

Accessories

Steel

Ordercode 912401483178



White

Ordercode 912401483179,
912401483180



CoreLine Panel

Application Conditions	
Ambient temperature range	+10 to +40 °C
Approval and Application	
Ingress protection code	IP20/44
General Information	
Beam angle of light source	120 °
CE mark	CE mark
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	-
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	White

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	1%	Yes
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	-	Yes
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	-	Yes
910503910307	RC132V LED36S/840 PSU W60L60 NOC	Not applicable	-
910503910310	RC132V LED36S/840 PSU W60L60 OC	Not applicable	-
910503910311	RC132V LED34S/830 PSU W60L60 OC	Not applicable	-
910503910312	RC133V LED36S/840 PSU W62L62 OC	Not applicable	-
910503910313	RC133V LED34S/830 PSU W62L62 OC	Not applicable	-
911401735502	RC132V LED43S/840 PSU W60L60 NOC	Not applicable	Yes
911401735522	RC132V LED43S/840 PSU W60L60 OC	Not applicable	Yes
911401735532	RC133V LED43S/840 PSU W62L62 OC	Not applicable	Yes
911401735542	RC132V LED43S/840 PSD W60L60 OC	10%	Yes
911401735552	RC133V LED43S/840 PSD W62L62 OC	10%	Yes
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	10%	Yes
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	10%	Yes
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	10%	Yes
912401483127	RC132V LED36S/840 W60L60 IA1 OC	10%	Yes
912401483128	RC132V LED34S/830 W60L60 IA1 OC	10%	Yes
912401483129	RC133V LED36S/840 W62L62 IA1 OC	10%	Yes
912401483165	RC132V LED36S/840 PSD W60L60 OC	10%	Yes
912401483166	RC132V LED34S/830 PSD W60L60 OC	10%	Yes
912401483167	RC133V LED36S/840 PSD W62L62 OC	10%	Yes
912401483168	RC133V LED34S/830 PSD W62L62 OC	10%	Yes
912401483171	RC132V LED34S/830 PSU W60L60 NOC	Not applicable	-
912401483172	RC133V LED36S/840 PSU W62L62 NOC	Not applicable	-
912401483173	RC133V LED34S/830 PSU W62L62 NOC	Not applicable	-
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	10%	Yes
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	-	Yes
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	-	Yes
910503910309	RC132V LED36S/840 PSU W30L120 NOC	Not applicable	-
910503910314	RC132V LED36S/840 PSU W30L120 OC	Not applicable	-
910503910315	RC132V LED34S/830 PSU W30L120 OC	Not applicable	-
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	10%	Yes
912401483130	RC132V LED36S/840 W30L120 IA1 OC	10%	Yes
912401483169	RC132V LED36S/840 PSD W30L120 OC	10%	Yes
912401483170	RC132V LED34S/830 PSD W30L120 OC	10%	Yes
910503910308	RC132V LED18S/840 PSU W30L60 NOC	Not applicable	-

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	IK02
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	IK02
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	IK02
910503910307	RC132V LED36S/840 PSU W60L60 NOC	IK03
910503910310	RC132V LED36S/840 PSU W60L60 OC	IK03
910503910311	RC132V LED34S/830 PSU W60L60 OC	IK03
910503910312	RC133V LED36S/840 PSU W62L62 OC	IK03

Order Code	Full Product Name	Mech. impact protection code
910503910313	RC133V LED34S/830 PSU W62L62 OC	IK03
911401735502	RC132V LED43S/840 PSU W60L60 NOC	IK03
911401735522	RC132V LED43S/840 PSU W60L60 OC	IK03
911401735532	RC133V LED43S/840 PSU W62L62 OC	IK03
911401735542	RC132V LED43S/840 PSD W60L60 OC	IK03
911401735552	RC133V LED43S/840 PSD W62L62 OC	IK03
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	IK03

CoreLine Panel

Order Code	Full Product Name	Mech. impact protection code
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	IK03
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	IK03
912401483127	RC132V LED36S/840 W60L60 IA1 OC	IK03
912401483128	RC132V LED34S/830 W60L60 IA1 OC	IK03
912401483129	RC133V LED36S/840 W62L62 IA1 OC	IK03
912401483165	RC132V LED36S/840 PSD W60L60 OC	IK03
912401483166	RC132V LED34S/830 PSD W60L60 OC	IK03
912401483167	RC133V LED36S/840 PSD W62L62 OC	IK03
912401483168	RC133V LED34S/830 PSD W62L62 OC	IK03
912401483171	RC132V LED34S/830 PSU W60L60 NOC	IK03
912401483172	RC133V LED36S/840 PSU W62L62 NOC	IK03
912401483173	RC133V LED34S/830 PSU W62L62 NOC	IK03

Order Code	Full Product Name	Mech. impact protection code
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	IK02
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	IK02
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	IK02
910503910309	RC132V LED36S/840 PSU W30L120 NOC	IK03
910503910314	RC132V LED36S/840 PSU W30L120 OC	IK03
910503910315	RC132V LED34S/830 PSU W30L120 OC	IK03
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	IK03
912401483130	RC132V LED36S/840 W30L120 IA1 OC	IK03
912401483169	RC132V LED36S/840 PSD W30L120 OC	IK03
912401483170	RC132V LED34S/830 PSD W30L120 OC	IK03
910503910308	RC132V LED18S/840 PSU W30L60 NOC	IK03

Controls and Dimming

Order Code	Full Product Name	Dimmable
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	Yes
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	Yes
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	Yes
910503910307	RC132V LED36S/840 PSU W60L60 NOC	No
910503910310	RC132V LED36S/840 PSU W60L60 OC	No
910503910311	RC132V LED34S/830 PSU W60L60 OC	No
910503910312	RC133V LED36S/840 PSU W62L62 OC	No
910503910313	RC133V LED34S/830 PSU W62L62 OC	No
911401735502	RC132V LED43S/840 PSU W60L60 NOC	No
911401735522	RC132V LED43S/840 PSU W60L60 OC	No
911401735532	RC133V LED43S/840 PSU W62L62 OC	No
911401735542	RC132V LED43S/840 PSD W60L60 OC	Yes
911401735552	RC133V LED43S/840 PSD W62L62 OC	Yes
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	Yes
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	Yes
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	Yes
912401483127	RC132V LED36S/840 W60L60 IA1 OC	Yes
912401483128	RC132V LED34S/830 W60L60 IA1 OC	Yes
912401483129	RC133V LED36S/840 W62L62 IA1 OC	Yes

Order Code	Full Product Name	Dimmable
912401483165	RC132V LED36S/840 PSD W60L60 OC	Yes
912401483166	RC132V LED34S/830 PSD W60L60 OC	Yes
912401483167	RC133V LED36S/840 PSD W62L62 OC	Yes
912401483168	RC133V LED34S/830 PSD W62L62 OC	Yes
912401483171	RC132V LED34S/830 PSU W60L60 NOC	No
912401483172	RC133V LED36S/840 PSU W62L62 NOC	No
912401483173	RC133V LED34S/830 PSU W62L62 NOC	No
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	Yes
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	Yes
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	Yes
910503910309	RC132V LED36S/840 PSU W30L120 NOC	No
910503910314	RC132V LED36S/840 PSU W30L120 OC	No
910503910315	RC132V LED34S/830 PSU W30L120 OC	No
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	Yes
912401483130	RC132V LED36S/840 W30L120 IA1 OC	Yes
912401483169	RC132V LED36S/840 PSD W30L120 OC	Yes
912401483170	RC132V LED34S/830 PSD W30L120 OC	Yes
910503910308	RC132V LED18S/840 PSU W30L60 NOC	No

Operating and Electrical

Order Code	Full Product Name	Input Voltage
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	220 to 240 V
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	220 to 240 V
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	220 to 240 V
910503910307	RC132V LED36S/840 PSU W60L60 NOC	220 to 240 V
910503910310	RC132V LED36S/840 PSU W60L60 OC	220 to 240 V
910503910311	RC132V LED34S/830 PSU W60L60 OC	220 to 240 V
910503910312	RC133V LED36S/840 PSU W62L62 OC	220 to 240 V
910503910313	RC133V LED34S/830 PSU W62L62 OC	220 to 240 V
911401735502	RC132V LED43S/840 PSU W60L60 NOC	220 to 240 V
911401735522	RC132V LED43S/840 PSU W60L60 OC	220 to 240 V
911401735532	RC133V LED43S/840 PSU W62L62 OC	220 to 240 V

Order Code	Full Product Name	Input Voltage
911401735542	RC132V LED43S/840 PSD W60L60 OC	220 to 240 V
911401735552	RC133V LED43S/840 PSD W62L62 OC	220 to 240 V
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	220-240 V
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	220-240 V
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	220-240 V
912401483127	RC132V LED36S/840 W60L60 IA1 OC	220-240 V
912401483128	RC132V LED34S/830 W60L60 IA1 OC	220-240 V
912401483129	RC133V LED36S/840 W62L62 IA1 OC	220-240 V
912401483165	RC132V LED36S/840 PSD W60L60 OC	220 to 240 V
912401483166	RC132V LED34S/830 PSD W60L60 OC	220 to 240 V
912401483167	RC133V LED36S/840 PSD W62L62 OC	220 to 240 V

CoreLine Panel

Order Code	Full Product Name	Input Voltage
912401483168	RC133V LED34S/830 PSD W62L62 OC	220 to 240 V
912401483171	RC132V LED34S/830 PSU W60L60 NOC	220 to 240 V
912401483172	RC133V LED36S/840 PSU W62L62 NOC	220 to 240 V
912401483173	RC133V LED34S/830 PSU W62L62 NOC	220 to 240 V
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	220 to 240 V
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	220 to 240 V
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	220 to 240 V
910503910309	RC132V LED36S/840 PSU W30L120 NOC	220 to 240 V

Order Code	Full Product Name	Input Voltage
910503910314	RC132V LED36S/840 PSU W30L120 OC	220 to 240 V
910503910315	RC132V LED34S/830 PSU W30L120 OC	220 to 240 V
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	220-240 V
912401483130	RC132V LED36S/840 W30L120 IA1 OC	220-240 V
912401483169	RC132V LED36S/840 PSD W30L120 OC	220 to 240 V
912401483170	RC132V LED34S/830 PSD W30L120 OC	220 to 240 V
910503910308	RC132V LED18S/840 PSU W30L60 NOC	220 to 240 V

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Protection class IEC	ENEC mark	Gear
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	-	Safety class I	-	-
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	-	Safety class I	-	-
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	-	Safety class I	-	-
910503910307	RC132V LED36S/840 PSU W60L60 NOC	-	Safety class II	ENEC mark	-
910503910310	RC132V LED36S/840 PSU W60L60 OC	-	Safety class II	ENEC mark	-
910503910311	RC132V LED34S/830 PSU W60L60 OC	-	Safety class II	ENEC mark	-
910503910312	RC133V LED36S/840 PSU W62L62 OC	-	Safety class II	ENEC mark	-
910503910313	RC133V LED34S/830 PSU W62L62 OC	-	Safety class II	ENEC mark	-
911401735502	RC132V LED43S/840 PSU W60L60 NOC	-	Safety class II	ENEC mark	-
911401735522	RC132V LED43S/840 PSU W60L60 OC	-	Safety class II	ENEC mark	-
911401735532	RC133V LED43S/840 PSU W62L62 OC	-	Safety class II	ENEC mark	-
911401735542	RC132V LED43S/840 PSD W60L60 OC	-	Safety class II	ENEC mark	-
911401735552	RC133V LED43S/840 PSD W62L62 OC	-	Safety class II	ENEC mark	-
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	-	Safety class I	ENEC mark	-
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	-	Safety class I	ENEC mark	-
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	-	Safety class I	ENEC mark	-
912401483127	RC132V LED36S/840 W60L60 IA1 OC	-	Safety class I	ENEC mark	-
912401483128	RC132V LED34S/830 W60L60 IA1 OC	-	Safety class I	ENEC mark	-
912401483129	RC133V LED36S/840 W62L62 IA1 OC	-	Safety class I	ENEC mark	-

Order Code	Full Product Name	Cap-Base	Protection class IEC	ENEC mark	Gear
912401483165	RC132V LED36S/840 PSD W60L60 OC	-	Safety class II	ENEC mark	-
912401483166	RC132V LED34S/830 PSD W60L60 OC	-	Safety class II	ENEC mark	-
912401483167	RC133V LED36S/840 PSD W62L62 OC	-	Safety class II	ENEC mark	-
912401483168	RC133V LED34S/830 PSD W62L62 OC	-	Safety class II	ENEC mark	-
912401483171	RC132V LED34S/830 PSU W60L60 NOC	-	Safety class II	ENEC mark	-
912401483172	RC133V LED36S/840 PSU W62L62 NOC	-	Safety class II	ENEC mark	-
912401483173	RC133V LED34S/830 PSU W62L62 NOC	-	Safety class II	ENEC mark	-
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	-	Safety class I	-	-
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	-	Safety class I	-	-
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	-	Safety class I	-	-
910503910309	RC132V LED36S/840 PSU W30L120 NOC	-	Safety class II	ENEC mark	-
910503910314	RC132V LED36S/840 PSU W30L120 OC	-	Safety class II	ENEC mark	-
910503910315	RC132V LED34S/830 PSU W30L120 OC	-	Safety class II	ENEC mark	-
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	-	Safety class I	ENEC mark	-
912401483130	RC132V LED36S/840 W30L120 IA1 OC	-	Safety class I	ENEC mark	-
912401483169	RC132V LED36S/840 PSD W30L120 OC	-	Safety class II	ENEC mark	-
912401483170	RC132V LED34S/830 PSD W30L120 OC	-	Safety class II	ENEC mark	-
910503910308	RC132V LED18S/840 PSU W30L60 NOC	-	Safety class II	ENEC mark	-

General Information (2/2)

Order Code	Full Product Name	Lamp family code	Product Family Code
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	LED36	RC132V
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	-	RC132V
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	-	RC132V
910503910307	RC132V LED36S/840 PSU W60L60 NOC	LED36S	-
910503910310	RC132V LED36S/840 PSU W60L60 OC	LED36S	-
910503910311	RC132V LED34S/830 PSU W60L60 OC	-	-
910503910312	RC133V LED36S/840 PSU W62L62 OC	LED36S	-
910503910313	RC133V LED34S/830 PSU W62L62 OC	-	-
911401735502	RC132V LED43S/840 PSU W60L60 NOC	-	-
911401735522	RC132V LED43S/840 PSU W60L60 OC	-	-
911401735532	RC133V LED43S/840 PSU W62L62 OC	-	-
911401735542	RC132V LED43S/840 PSD W60L60 OC	-	-
911401735552	RC133V LED43S/840 PSD W62L62 OC	-	-
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	-	-
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	-	-
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	-	-
912401483127	RC132V LED36S/840 W60L60 IA1 OC	-	-
912401483128	RC132V LED34S/830 W60L60 IA1 OC	-	-
912401483129	RC133V LED36S/840 W62L62 IA1 OC	-	-

Order Code	Full Product Name	Lamp family code	Product Family Code
912401483165	RC132V LED36S/840 PSD W60L60 OC	-	-
912401483166	RC132V LED34S/830 PSD W60L60 OC	-	-
912401483167	RC133V LED36S/840 PSD W62L62 OC	-	-
912401483168	RC133V LED34S/830 PSD W62L62 OC	-	-
912401483171	RC132V LED34S/830 PSU W60L60 NOC	-	-
912401483172	RC133V LED36S/840 PSU W62L62 NOC	-	-
912401483173	RC133V LED34S/830 PSU W62L62 NOC	-	-
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	LED36	RC132V
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	-	-
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	-	RC132V
910503910309	RC132V LED36S/840 PSU W30L120 NOC	LED36S	-
910503910314	RC132V LED36S/840 PSU W30L120 OC	LED36S	-
910503910315	RC132V LED34S/830 PSU W30L120 OC	-	-
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	-	-
912401483130	RC132V LED36S/840 W30L120 IA1 OC	-	-
912401483169	RC132V LED36S/840 PSD W30L120 OC	-	-
912401483170	RC132V LED34S/830 PSD W30L120 OC	-	-
910503910308	RC132V LED18S/840 PSU W30L60 NOC	-	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	4000 K	≥80	100 lm/W	3600 lm
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	4000 K	≥80	100 lm/W	3600 lm
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	4000 K	≥80	100 lm/W	3600 lm
910503910307	RC132V LED36S/840 PSU W60L60 NOC	4000 K	≥80	110 lm/W	3600 lm
910503910310	RC132V LED36S/840 PSU W60L60 OC	4000 K	≥80	110 lm/W	3600 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
910503910311	RC132V LED34S/830 PSU W60L60 OC	3000 K	≥80	105 lm/W	3400 lm
910503910312	RC133V LED36S/840 PSU W62L62 OC	4000 K	≥80	110 lm/W	3600 lm
910503910313	RC133V LED34S/830 PSU W62L62 OC	3000 K	≥80	105 lm/W	3400 lm
911401735502	RC132V LED43S/840 PSU W60L60 NOC	4000 K	>80	123 lm/W	4300 lm
911401735522	RC132V LED43S/840 PSU W60L60 OC	4000 K	>80	123 lm/W	4300 lm

CoreLine Panel

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401735532	RC133V LED43S/840 PSU W62L62 OC	4000 K	>80	123 lm/W	4300 lm
911401735542	RC132V LED43S/840 PSD W60L60 OC	4000 K	>80	116 lm/W	4300 lm
911401735552	RC133V LED43S/840 PSD W62L62 OC	4000 K	>80	116 lm/W	4300 lm
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	4000 K	≥80	100 lm/W	3600 lm
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	3000 K	≥80	94 lm/W	3400 lm
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	4000 K	≥80	100 lm/W	3600 lm
912401483127	RC132V LED36S/840 W60L60 IA1 OC	4000 K	≥80	100 lm/W	3600 lm
912401483128	RC132V LED34S/830 W60L60 IA1 OC	3000 K	≥80	94 lm/W	3400 lm
912401483129	RC133V LED36S/840 W62L62 IA1 OC	4000 K	≥80	100 lm/W	3600 lm
912401483165	RC132V LED36S/840 PSD W60L60 OC	4000 K	≥80	105 lm/W	3600 lm
912401483166	RC132V LED34S/830 PSD W60L60 OC	3000 K	≥80	100 lm/W	3400 lm
912401483167	RC133V LED36S/840 PSD W62L62 OC	4000 K	≥80	105 lm/W	3600 lm
912401483168	RC133V LED34S/830	3000 K	≥80	100 lm/W	3600 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
	PSD W62L62 OC				
912401483171	RC132V LED34S/830 PSU W60L60 NOC	3000 K	≥80	105 lm/W	3400 lm
912401483172	RC133V LED36S/840 PSU W62L62 NOC	4000 K	≥80	110 lm/W	3600 lm
912401483173	RC133V LED34S/830 PSU W62L62 NOC	3000 K	≥80	105 lm/W	3600 lm
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	4000 K	≥80	100 lm/W	3600 lm
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	4000 K	≥80	100 lm/W	3600 lm
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	4000 K	≥80	100 lm/W	3600 lm
910503910309	RC132V LED36S/840 PSU W30L120 NOC	4000 K	≥80	105 lm/W	3600 lm
910503910314	RC132V LED36S/840 PSU W30L120 OC	4000 K	≥80	110 lm/W	3600 lm
910503910315	RC132V LED34S/830 PSU W30L120 OC	3000 K	≥80	105 lm/W	3400 lm
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	4000 K	≥80	100 lm/W	3600 lm
912401483130	RC132V LED36S/840 W30L120 IA1 OC	4000 K	≥80	100 lm/W	3600 lm
912401483169	RC132V LED36S/840 PSD W30L120 OC	4000 K	≥80	105 lm/W	3600 lm

CoreLine Panel

		Init. Corr.	Init. Color	Initial LED	Initial
Order Code	Full Product Name	Color Temperature	Rendering Index	luminaire efficacy	luminous flux
912401483170	RC132V LED34S/830 PSD W30L120 OC	3000 K	≥80	100 lm/W	3600 lm
910503910308	RC132V LED18S/840	4000 K	≥80	110 lm/W	1800 lm

		Init. Corr.	Init. Color	Initial LED	Initial
Order Code	Name	Temperature	Index	luminaire efficacy	luminous flux
	PSU W30L60 NOC				

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	40 W
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	36 W
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	40 W
910503910307	RC132V LED36S/840 PSU W60L60 NOC	33 W
910503910310	RC132V LED36S/840 PSU W60L60 OC	33 W
910503910311	RC132V LED34S/830 PSU W60L60 OC	33 W
910503910312	RC133V LED36S/840 PSU W62L62 OC	33 W
910503910313	RC133V LED34S/830 PSU W62L62 OC	33 W
911401735502	RC132V LED43S/840 PSU W60L60 NOC	35 W
911401735522	RC132V LED43S/840 PSU W60L60 OC	35 W
911401735532	RC133V LED43S/840 PSU W62L62 OC	35 W
911401735542	RC132V LED43S/840 PSD W60L60 OC	37 W
911401735552	RC133V LED43S/840 PSD W62L62 OC	37 W
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	34 W
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	34 W
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	34 W
912401483127	RC132V LED36S/840 W60L60 IA1 OC	34 W
912401483128	RC132V LED34S/830 W60L60 IA1 OC	34 W
912401483129	RC133V LED36S/840 W62L62 IA1 OC	34 W

Order Code	Full Product Name	Initial input power
912401483165	RC132V LED36S/840 PSD W60L60 OC	35 W
912401483166	RC132V LED34S/830 PSD W60L60 OC	35 W
912401483167	RC133V LED36S/840 PSD W62L62 OC	35 W
912401483168	RC133V LED34S/830 PSD W62L62 OC	35 W
912401483171	RC132V LED34S/830 PSU W60L60 NOC	33 W
912401483172	RC133V LED36S/840 PSU W62L62 NOC	33 W
912401483173	RC133V LED34S/830 PSU W62L62 NOC	33 W
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	36 W
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	36 W
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	36 W
910503910309	RC132V LED36S/840 PSU W30L120 NOC	33 W
910503910314	RC132V LED36S/840 PSU W30L120 OC	33 W
910503910315	RC132V LED34S/830 PSU W30L120 OC	33 W
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	34 W
912401483130	RC132V LED36S/840 W30L120 IA1 OC	34 W
912401483169	RC132V LED36S/840 PSD W30L120 OC	35 W
912401483170	RC132V LED34S/830 PSD W30L120 OC	35 W
910503910308	RC132V LED18S/840 PSU W30L60 NOC	16 W

Mechanical and Housing

Order Code	Full Product Name	Diameter	Width
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	-	- mm
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	-	-
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	-	-
910503910307	RC132V LED36S/840 PSU W60L60 NOC	-	-
910503910310	RC132V LED36S/840 PSU W60L60 OC	-	-
910503910311	RC132V LED34S/830 PSU W60L60 OC	-	-
910503910312	RC133V LED36S/840 PSU W62L62 OC	-	-
910503910313	RC133V LED34S/830 PSU W62L62 OC	-	-
911401735502	RC132V LED43S/840 PSU W60L60 NOC	-	-
911401735522	RC132V LED43S/840 PSU W60L60 OC	-	-
911401735532	RC133V LED43S/840 PSU W62L62 OC	-	-
911401735542	RC132V LED43S/840 PSD W60L60 OC	-	-
911401735552	RC133V LED43S/840 PSD W62L62 OC	-	-
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	-	-
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	-	-
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	-	-

Order Code	Full Product Name	Diameter	Width
912401483127	RC132V LED36S/840 W60L60 IA1 OC	-	-
912401483128	RC132V LED34S/830 W60L60 IA1 OC	-	-
912401483129	RC133V LED36S/840 W62L62 IA1 OC	-	-
912401483165	RC132V LED36S/840 PSD W60L60 OC	-	-
912401483166	RC132V LED34S/830 PSD W60L60 OC	-	-
912401483167	RC133V LED36S/840 PSD W62L62 OC	-	-
912401483168	RC133V LED34S/830 PSD W62L62 OC	-	-
912401483171	RC132V LED34S/830 PSU W60L60 NOC	-	-
912401483172	RC133V LED36S/840 PSU W62L62 NOC	-	-
912401483173	RC133V LED34S/830 PSU W62L62 NOC	-	-
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	-	- mm
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	-	-
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	-	-
910503910309	RC132V LED36S/840 PSU W30L120 NOC	-	-
910503910314	RC132V LED36S/840 PSU W30L120 OC	-	-
910503910315	RC132V LED34S/830 PSU W30L120 OC	-	-

CoreLine Panel

Order Code	Full Product Name	Diameter	Width
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	-	-
912401483130	RC132V LED36S/840 W30L120 IA1 OC	-	-
912401483169	RC132V LED36S/840 PSD W30L120 OC	-	-

Order Code	Full Product Name	Diameter	Width
912401483170	RC132V LED34S/830 PSD W30L120 OC	-	-
910503910308	RC132V LED18S/840 PSU W30L60 NOC	-	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
910500465357	RC132V LED36S/840 PSD W60L60 ELB3 OC	30000 h	15000 h
910500465360	RC132V LED36S/840 W60L60 ELB3 IA1 NOC	30000 h	15000 h
910500465362	RC132V LED36S/840 W60L60 ELB3 IA1 OC	30000 h	15000 h
910503910307	RC132V LED36S/840 PSU W60L60 NOC	-	-
910503910310	RC132V LED36S/840 PSU W60L60 OC	-	-
910503910311	RC132V LED34S/830 PSU W60L60 OC	-	-
910503910312	RC133V LED36S/840 PSU W62L62 OC	-	-
910503910313	RC133V LED34S/830 PSU W62L62 OC	-	-
911401735502	RC132V LED43S/840 PSU W60L60 NOC	-	-
911401735522	RC132V LED43S/840 PSU W60L60 OC	-	-
911401735532	RC133V LED43S/840 PSU W62L62 OC	-	-
911401735542	RC132V LED43S/840 PSD W60L60 OC	-	-
911401735552	RC133V LED43S/840 PSD W62L62 OC	-	-
912401483123	RC132V LED36S/840 W60L60 IA1 NOC	-	-
912401483124	RC132V LED34S/830 W60L60 IA1 NOC	-	-
912401483125	RC133V LED36S/840 W62L62 IA1 NOC	-	-
912401483127	RC132V LED36S/840 W60L60 IA1 OC	-	-
912401483128	RC132V LED34S/830 W60L60 IA1 OC	-	-
912401483129	RC133V LED36S/840 W62L62 IA1 OC	-	-
912401483165	RC132V LED36S/840 PSD W60L60 OC	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
912401483166	RC132V LED34S/830 PSD W60L60 OC	-	-
912401483167	RC133V LED36S/840 PSD W62L62 OC	-	-
912401483168	RC133V LED34S/830 PSD W62L62 OC	-	-
912401483171	RC132V LED34S/830 PSU W60L60 NOC	-	-
912401483172	RC133V LED36S/840 PSU W62L62 NOC	-	-
912401483173	RC133V LED34S/830 PSU W62L62 NOC	-	-
910500465358	RC132V LED36S/840 PSD W30L120 ELB3 OC	30000 h	15000 h
910500465361	RC132V LED36S/840 W30L120 ELB3 IA1 NOC	30000 h	15000 h
910500465363	RC132V LED36S/840 W30L120 ELB3 IA1 OC	30000 h	15000 h
910503910309	RC132V LED36S/840 PSU W30L120 NOC	-	-
910503910314	RC132V LED36S/840 PSU W30L120 OC	-	-
910503910315	RC132V LED34S/830 PSU W30L120 OC	-	-
912401483126	RC132V LED36S/840 W30L120 IA1 NOC	-	-
912401483130	RC132V LED36S/840 W30L120 IA1 OC	-	-
912401483169	RC132V LED36S/840 PSD W30L120 OC	-	-
912401483170	RC132V LED34S/830 PSD W30L120 OC	-	-
910503910308	RC132V LED18S/840 PSU W30L60 NOC	-	-

