



Tempo – compact and consistent

Tempo 2 RVP251

Tempo is a complete floodlighting range offering a wide choice of lamp types and symmetrical and asymmetrical reflectors. It is designed for general-purpose floodlighting, and is particularly suited to small- to medium-scale area or surface lighting. The Tempo series' compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. A universal mounting bracket allows ceiling, wall or surface mounting with a wide range of adjustment for both down- and uplighting. Tempo's all-weather construction is designed to make cleaning and servicing easy and fast. Access to the lamp and gear is simple, via the hinged front glass with its quick-release stainless-steel clips. All Tempo luminaires are RoHS-compliant.

Benefits

- Complete floodlighting range with a wide choice of lamp types and symmetrical or asymmetrical reflectors for highly efficient beam distribution
- Ideal for a variety of outdoor applications from architectural, facade and billboard lighting to area and (leisure) sports lighting
- Optimal visual integration with compact housing and metallic grey finish

Features

- Wide choice of lamp types
- Symmetrical and asymmetrical reflectors
- Compact housing with metallic grey finish
- Aiming device
- Hinged front glass with quick-release clips

Tempo 2 RVP251

Application

- Facades
- Area lighting
- Architectural lighting
- Billboards

Specifications

Type	RVP251
Light source	HID:
	- 1 x MASTERColour CDM-TD / RX7s / 150 W
	- 1 x MHN-TD / RX7s / 150 W
	- 1 x SON-TPP / E40 / 150 W
Lamp included	Yes (K or light color 830 or 842)
Gear and compensation (integrated)	Electromagnetic (low loss), 230 or 240 V / 50 Hz:
	- Inductive (IN)
	- Inductive, parallel compensated (IC)
Optic	Asymmetrical (A)
	Symmetrical (S)
Materials and finishing	Housing: die-cast aluminum, corrosion-resistant powder coating
	Glass: thermally hardened, 4 mm thick
	Gasket: premium bonded silicone
	Mounting bracket: steel
	Aiming device cap: nylon
	Fixation clips: stainless steel
	Reflector: anodized, high-purity aluminum

Color	Grey, RAL 9007, powder-coated
	Color-matched bracket, grommet and hinges
Installation	Ceiling, wall or floor mounting
	Cable entry via M20 cable gland
	Ambient temperature outdoor: 35°C
	Drag factor (SCx): 0.138 m
Maintenance	Max adjustment from the horizontal: 175°
	Hinged front glass with quick-release clips for in-position lamp replacement
	No internal cleaning required
Main applications	Area, facade, billboard, architectural lighting

Versions



Tempo 2 RVP251 area flood-lighting
luminaire

Tempo 2 RVP251

Product details



Rear view



Aiming device for easy adjustment and alignment



Integrated gear unit

