



Contempo RVP150/250/350

ConTempo

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

Benefits

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminium housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodised reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Features

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Application

- Functional: bays, outdoor storage areas, surveillance, parking areas, construction sites
- Recreational/sports: training fields, game courts, swimming pools
- Decorative: facades, edifices, billboards, gardens, patios, fountains, bridges, landscapes

Versions



RVP350/RVP250

General Information

| | |
|-------------------------|-------------|
| Country version | NO |
| Gear | CONV |
| Number of light sources | 1 |
| Optic type | Symmetrical |

General Information

| Order Code | Full Product Name | Cap-Base | Lamp family code | Lamp power |
|--------------|---------------------------------------|----------|------------------|------------|
| 910403339901 | RVP350 HPI-T250W IC 220V-50Hz S SP BK | - | HPI-TP | 250 W |
| 910403342301 | RVP350 SON-T250W IC 220V-50Hz S SP BK | - | SON-T | 250 W |
| 910403342501 | RVP350 SON-T400W IC 220V-50Hz S SP BK | - | SON-T | 400 W |

| Order Code | Full Product Name | Cap-Base | Lamp family code | Lamp power |
|--------------|---------------------------------------|----------|------------------|------------|
| 910403342801 | RVP350 HPI-T400W IC 220V-50Hz S SP BK | - | HPI-TP | 400 W |
| 911401044580 | RVP350 HPI-T400W IC 230V-50Hz S SP | E40 | HPI-TP | 400 W |

Mechanical and Housing

| Order Code | Full Product Name | Colour |
|--------------|---------------------------------------|--------|
| 910403339901 | RVP350 HPI-T250W IC 220V-50Hz S SP BK | Black |
| 910403342301 | RVP350 SON-T250W IC 220V-50Hz S SP BK | Black |
| 910403342501 | RVP350 SON-T400W IC 220V-50Hz S SP BK | Black |

| Order Code | Full Product Name | Colour |
|--------------|---------------------------------------|--------|
| 910403342801 | RVP350 HPI-T400W IC 220V-50Hz S SP BK | Black |
| 911401044580 | RVP350 HPI-T400W IC 230V-50Hz S SP | - |

