



Contempo RVP150/250/350

ConTempo 150-250-350

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

Benefits

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminium housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodised reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Features

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

ConTempo 150-250-350

Application

- Functional: bays, outdoor storage areas, surveillance, parking areas, construction sites
- Recreational/sports: training fields, game courts, swimming pools
- Decorative: facades, edifices, billboards, gardens, patios, fountains, bridges, landscapes

Versions



RVP350/RVP250

General Information

| | |
|-------------------------|-------------|
| Country version | NO |
| Gear | CONV |
| Lamp power | 150 W |
| Number of light sources | 1 pc |
| Optic type | Symmetrical |

General Information

| Order Code | Full Product Name | Cap-Base | Lamp family code | Order Code | Full Product Name | Cap-Base | Lamp family code |
|--------------|----------------------------------|----------|------------------|--------------|------------------------------------|----------|------------------|
| 911401043480 | RVP250 MHN-TD150W IC 230V-50Hz S | R7S | MHN-TD | 911401043780 | RVP250 SON-T150W IC 230V-50Hz S SP | E40 | SON-T |
| | SP | | | | | | |

