



Contempo RVP150/250/350

ConTempo 150-250-350 *do not use*

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

Benefits

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Features

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

ConTempo 150-250-350 *do not use*

Application

- Functional: bays, outdoor storage areas, surveillance, parking areas, construction sites
- Recreational/sports: training fields, game courts, swimming pools
- Decorative: facades, edifices, billboards, gardens, patios, fountains, bridges, landscapes

Versions



RVP350/RVP250

General Information

Country version	NO
Gear	CONV
Number of light sources	1 pc

General Information

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
910403339901	RVP350 HPI-T250W IC 220V-50Hz S SP BK	-	HPI-TP	250 W	Symmetrical
910403342301	RVP350 SON-T250W IC 220V-50Hz S SP BK	-	SON-T	250 W	Symmetrical
910403342501	RVP350 SON-T400W IC 220V-50Hz S SP BK	-	SON-T	400 W	Symmetrical
910403342801	RVP350 HPI-T400W IC 220V-50Hz S SP BK	-	HPI-TP	400 W	Symmetrical
911401043780	RVP250 SON-T150W IC 230V-50Hz S SP	E40	SON-T	150 W	Symmetrical
911401044380	RVP350 SON-T400W IC 230V-50Hz S SP	E40	SON-T	400 W	Symmetrical

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
911401044480	RVP350 HPI-T250W IC 230V-50Hz S SP	E40	HPI-TP	250 W	Symmetrical
911401044580	RVP350 HPI-T400W IC 230V-50Hz S SP	E40	HPI-TP	400 W	Symmetrical
911401047980	RVP350 HPI-T250W IC 220V-60Hz S SP	E40	HPI-TP	250 W	Symmetrical
911401048180	RVP350 HPI-T400W IC 220V-60Hz S SP	E40	HPI-TP	400 W	Symmetrical
911401048480	RVP350 HPI-T250W IC 220V-60Hz A SP	E40	HPI-TP	250 W	Asymmetrical
911401048580	RVP350 HPI-T400W IC 220V-60Hz A SP	E40	HPI-TP	400 W	Asymmetrical

Mechanical and Housing

Order Code	Full Product Name	Color
910403339901	RVP350 HPI-T250W IC 220V-50Hz S SP BK	Black
910403342301	RVP350 SON-T250W IC 220V-50Hz S SP BK	Black
910403342501	RVP350 SON-T400W IC 220V-50Hz S SP BK	Black

Order Code	Full Product Name	Color
910403342801	RVP350 HPI-T400W IC 220V-50Hz S SP BK	Black
911401043780	RVP250 SON-T150W IC 230V-50Hz S SP	-
911401044380	RVP350 SON-T400W IC 230V-50Hz S SP	-

ConTempo 150-250-350 *do not use*

Order Code	Full Product Name	Color
911401044480	RVP350 HPI-T250W IC 230V-50Hz S SP	-
911401044580	RVP350 HPI-T400W IC 230V-50Hz S SP	-
911401047980	RVP350 HPI-T250W IC 220V-60Hz S SP	-

Order Code	Full Product Name	Color
911401048180	RVP350 HPI-T400W IC 220V-60Hz S SP	-
911401048480	RVP350 HPI-T250W IC 220V-60Hz A SP	-
911401048580	RVP350 HPI-T400W IC 220V-60Hz A SP	-

