



A smooth design solution for a seamless look

PAR30S LED Single Optic Lamps with AirFlux Technology

Philips PAR30S LED Single Optic Lamps with AirFlux Technology provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Advantages

- Will not fade colors, avoids inventory spoilage
- Lowers maintenance costs by reducing re-lamp frequency
- 5-year limited warranty**
- ** For details see: http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd.

Fonctions

- Retail Optic reduces glare to improve shopper experience
- 25,000-hour rated average life*
- 12W PAR30S saves 63 watts when compared to a 75W halogen PAR30S
- 83 CRI for excellent color rendering
- Virtually UV/IR free in the beam
- Contains no mercury

Application

- Ideal for general and accent lighting in retail, hospitality and office spaces.

PAR30S LED Single Optic Lamps with AirFlux Technology


Mises en garde et sécurité

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
- CAUTION: Risk of electric shock— do not use where directly exposed to water
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs,change the location of the products involved. This RFLD device complies with Canadian ICES-005.


Versions



Schéma dimensionnel





Product	D	C
9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	97 mm	119 mm
9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	97 mm	119 mm




Product	D	C
9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	97 mm	94 mm
9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	97 mm	94 mm


PAR30S LED Single Optic Lamps with AirFlux Technology




Accent Diagrams




LEDspots 9,4W PAR30L E26 930 25D



LEDspots 9,4W PAR30L E26 930 40D




LEDspots 9,4W PAR30S E26 930 25D




LEDspots 9,4W PAR30S E26 930 40D

PAR30S LED Single Optic Lamps with AirFlux Technology


Beam Diagrams




LEDspots 9,4W PAR30L E26 930 25D



LEDspots 9,4W PAR30L E26 930 40D



LEDspots 9,4W PAR30S E26 930 25D



LEDspots 9,4W PAR30S E26 930 40D

