



Attractive LED alternative to popular incandescents.

A-Shape LED

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Benefits

- Long life properties-- lowers maintenance costs by reducing re-lamp frequency
- Will not fade colors, avoids inventory spoilage
- Contains no mercury
- Emits virtually no UV/IR light in the beam
- 3-year or 5-year limited warranty depending upon operating hours
- 80% more Energy Efficient when compared to traditional incandescent bulbs.
- Selection of ENERGY STAR® qualified models

Features

- Smooth dimming to 10% of full light levels*
- Remote phosphor (yellow) disappears when energized to create even, soft white light
- 25,000-hour rated average life⁺
- Instant-on light
- ⁺Rated average life based on engineering testing and probability analysis.
- Selection of durable plastic housings or classic glass housings
- ^{*} Dimmable when using leading edge dimmers (see Philips Website: www.philips.com/ledtechguide for compatible leading edge dimmers).

A-Shape LED


Application

- Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, multi-unit residences and government buildings.


Versions



Single Contact Medium Screw A19 (A19) Amber



Single Contact Medium Screw



Single Contact Medium Screw



Single Contact Medium Screw A19 (A19) Frosted



GU24 A 19mm Frosted



GU24 A 21mm Frosted



Single Contact Medium Screw A19 (A19) Frosted

A-Shape LED

Versions



E26 A21



Single Contact Medium Screw A19 (A19) Frosted



Single Contact Medium Screw A19 (A19) Frosted



Single Contact Medium Screw A19 (A19) Frosted




Single Contact Medium Screw A19 (A19) Frosted



Single Contact Medium Screw A19 (A19) Frosted





Dimensional drawing



Product	D	C
5A19/PER/927-22/P/E26/WG 6/1FB T20	2-1/2 in	4-7/16 in
8.8A19/PER/927-22/P/E26/WG 6/1FB T20	2-1/2 in	4-7/16 in

A-Shape LED

Dimensional drawing



Product	D	C
5A19/PER/940/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
5A19/PER/927/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
8.8A19/PER/950/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
8.8A19/PER/927/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
8.8A19/PER/940/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
5A19/PER/930/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
5A19/PER/950/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in
8.8A19/PER/930/P/E26/DIM 6/1FB T20	2-1/2 in	4-7/16 in




Product	D	C
8A19/PER/927-922/CL/G/E26/WGX 1FB T20	2-3/8 in	4-1/4 in
5A19/PER/927-922/CL/G/E26/WGX 1FB T20	2-3/8 in	4-1/4 in

Product	D	C
8.8A19/PER/930/P/GU24/DIM 6/1FB T20	2-3/8 in	4-3/16 in

Product	D	C
12.2A19/PER/940/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
12.2A19/PER/927/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
16A19/PER/940/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
16A19/PER/950/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
12.2A19/PER/927-22/P/E26/WG 6/1FB T20	2-3/8 in	4-7/16 in
16A19/PER/927/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
16A19/PER/927-22/P/E26/WG 6/1FB T20	2-3/8 in	4-7/16 in
12.2A19/PER/950/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
16A19/PER/930/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in
12.2A19/PER/930/P/E26/DIM 6/1FB T20	2-3/8 in	4-7/16 in

A-Shape LED

Dimensional drawing






Product	D	C
4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	2-3/8 in	4-3/16 in

Product	D	C
8.5A19/LED/927/FR/P/ND 4/1FB	2-3/8 in	4-1/8 in
8.5A19/LED/930/FR/P/ND 4/1FB	2-3/8 in	4-1/8 in
8.5A19/LED/950/FR/P/ND 4/1FB	2-3/8 in	4-1/8 in
5A19/LED/930/FR/P/ND 4/1FB	2-3/8 in	4-1/8 in
5A19/LED/950/FR/P/ND 4/1FB	2-3/8 in	4-1/8 in
5A19/LED/927/FR/P/ND 4/1FB	2-3/8 in	4-1/8 in
8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-1/8 in
8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-1/8 in
5A19/LED/930/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-1/8 in
8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-1/8 in
5A19/LED/950/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-1/8 in
5A19/LED/927/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-1/8 in
8A19/PER/850/FR/P/E26/D 4/4CT	2-3/8 in	4-1/8 in
8A19/PER/827/FR/P/E26/D 4/4CT	2-3/8 in	4-1/8 in
8A19/PER/830/FR/P/E26/D 4/4CT	2-3/8 in	4-1/8 in
8A19/PER/840/FR/P/E26/D 4/4CT	2-3/8 in	4-1/8 in

Product	D	C
10A19/LED/930/FR/P/ND 4/1FB	2-3/8 in	4-3/16 in
10A19/LED/927/FR/P/ND 4/1FB	2-3/8 in	4-3/16 in
10A19/LED/950/FR/P/ND 4/1FB	2-3/8 in	4-3/16 in

A-Shape LED

Dimensional drawing





Product	D	C
13.5A19/LED/930/FR/P/ND 4/1FB	2-3/8 in	4-5/8 in
13.5A19/LED/927/FR/P/ND 4/1FB	2-3/8 in	4-5/8 in
13.5A19/LED/950/FR/P/ND 4/1FB	2-3/8 in	4-5/8 in
16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-5/8 in
16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-5/8 in
12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-5/8 in
12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-5/8 in
16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-5/8 in
12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	2-3/8 in	4-5/8 in
14A19/PER/827/FR/P/E26/D 4/4CT	2-3/8 in	4-5/8 in
14A19/PER/840/FR/P/E26/D 4/4CT	2-3/8 in	4-5/8 in
14A19/PER/850/FR/P/E26/D 4/4CT	2-3/8 in	4-5/8 in
14A19/PER/830/FR/P/E26/D 4/4CT	2-3/8 in	4-5/8 in

Product	D	C
8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	2-7/16 in	4-3/8 in

Product	D	C
5A19/LED/927/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
5A19/LED/950/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
5A19/LED/930/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
8A19/LED/927/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
8A19/LED/930/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
8A19/LED/950/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	2-3/8 in	4-3/16 in
12A19/LED/927/FR/Glass/E26/DIM 1FB T20	2-5/8 in	4-9/16 in
12A19/LED/950/FR/Glass/E26/DIM 1FB T20	2-5/8 in	4-9/16 in
12A19/LED/930/FR/Glass/E26/DIM 1FB T20	2-5/8 in	4-9/16 in

A-Shape LED

Dimensional drawing



Product	D	C
29A21/PER/850/FR/P/E26/D/HO 4/1PF	3-1/16 in	5-7/16 in

Product	D	C
16A21/PER/930/P/GU24/DIM 4/1FB T20	3-1/16 in	5-9/16 in

Operating and electrical

Voltage (Nom)	120 V
Starting Time (Nom)	0.5 s

Light technical

Llmf At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	- kWh
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	- kWh
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	- kWh
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	- kWh
556795	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	- kWh
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	- kWh
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	- kWh
560994	12.2A19/PER/950/P/E26/DIM 6/1FB T20	- kWh
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	- kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	- kWh
561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	- kWh
561035	12.2A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
561043	12.2A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
561050	12.2A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	- kWh
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	- kWh
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	- kWh
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	-
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	-
573238	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	-
571505	29A21/PER/850/FR/P/E26/D/HO 4/1PF	-
565085	5A19/LED/927/FR/P/ND 4/1FB	-
565093	5A19/LED/930/FR/P/ND 4/1FB	-
565100	5A19/LED/950/FR/P/ND 4/1FB	-

A-Shape LED

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
565119	8.5A19/LED/927/FR/P/ND 4/1FB	-
565127	8.5A19/LED/930/FR/P/ND 4/1FB	-
565135	8.5A19/LED/950/FR/P/ND 4/1FB	-
571588	5A19/LED/927/FR/P/E26/ND/T20 6/1FB	-
571596	5A19/LED/930/FR/P/E26/ND/T20 6/1FB	-
571604	5A19/LED/950/FR/P/E26/ND/T20 6/1FB	-
571612	8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	-
571620	8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	-
571638	8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	-
581751	8A19/PER/827/FR/P/E26/D 4/4CT	-
581785	8A19/PER/850/FR/P/E26/D 4/4CT	-
581769	8A19/PER/830/FR/P/E26/D 4/4CT	-
581777	8A19/PER/840/FR/P/E26/D 4/4CT	-
565143	10A19/LED/927/FR/P/ND 4/1FB	-
565150	10A19/LED/930/FR/P/ND 4/1FB	-
565168	10A19/LED/950/FR/P/ND 4/1FB	-
565176	13.5A19/LED/927/FR/P/ND 4/1FB	-
565184	13.5A19/LED/930/FR/P/ND 4/1FB	-
565192	13.5A19/LED/950/FR/P/ND 4/1FB	-
571646	12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	-
571653	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	-

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
571661	12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	-
571679	16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	-
571687	16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	-
571695	16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	-
581801	14A19/PER/827/FR/P/E26/D 4/4CT	-
581827	14A19/PER/830/FR/P/E26/D 4/4CT	-
581835	14A19/PER/840/FR/P/E26/D 4/4CT	-
581868	14A19/PER/850/FR/P/E26/D 4/4CT	-
578534	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	-
578542	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	-
578559	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	-
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	-
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	-
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	-
578583	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	-
578591	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	-
578609	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	-
578617	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	-
578625	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	-
578633	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	-

Controls and dimming

Order Code	Full Product Name	Dimmable
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	Yes
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	Yes
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	Yes
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	Yes
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	Yes
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	Yes
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	Yes
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	Yes
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	Yes
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	Yes
556795	4.5A19/VIN/820/E26/CL/GL/DIM 4/FB T20	Yes
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
560994	12.2A19/PER/950/P/E26/DIM 6/1FB T20	Yes
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	Yes
561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	Yes
561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	Yes
561035	12.2A19/PER/927/P/E26/DIM 6/1FB T20	Yes
561043	12.2A19/PER/930/P/E26/DIM 6/1FB T20	Yes
561050	12.2A19/PER/940/P/E26/DIM 6/1FB T20	Yes
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	Yes
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	Yes
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	Yes
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	Yes
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	Only with specific dimmers
573238	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	No

Order Code	Full Product Name	Dimmable
571505	29A21/PER/850/FR/P/E26/D/HO 4/1PF	Only with specific dimmers
565085	5A19/LED/927/FR/P/ND 4/1FB	No
565093	5A19/LED/930/FR/P/ND 4/1FB	No
565100	5A19/LED/950/FR/P/ND 4/1FB	No
565119	8.5A19/LED/927/FR/P/ND 4/1FB	No
565127	8.5A19/LED/930/FR/P/ND 4/1FB	No
565135	8.5A19/LED/950/FR/P/ND 4/1FB	No
571588	5A19/LED/927/FR/P/E26/ND/T20 6/1FB	No
571596	5A19/LED/930/FR/P/E26/ND/T20 6/1FB	No
571604	5A19/LED/950/FR/P/E26/ND/T20 6/1FB	No
571612	8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	No
571620	8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	No
571638	8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	No
581751	8A19/PER/827/FR/P/E26/D 4/4CT	Only with specific dimmers
581785	8A19/PER/850/FR/P/E26/D 4/4CT	Only with specific dimmers
581769	8A19/PER/830/FR/P/E26/D 4/4CT	Only with specific dimmers
581777	8A19/PER/840/FR/P/E26/D 4/4CT	Only with specific dimmers
565143	10A19/LED/927/FR/P/ND 4/1FB	No
565150	10A19/LED/930/FR/P/ND 4/1FB	No
565168	10A19/LED/950/FR/P/ND 4/1FB	No
565176	13.5A19/LED/927/FR/P/ND 4/1FB	No
565184	13.5A19/LED/930/FR/P/ND 4/1FB	No
565192	13.5A19/LED/950/FR/P/ND 4/1FB	No
571646	12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	No
571653	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	No
571661	12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	No

A-Shape LED

Order Code	Full Product Name	Dimmable
571679	16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	No
571687	16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	No
571695	16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	No
581801	14A19/PER/827/FR/P/E26/D 4/4CT	Only with specific dimmers
581827	14A19/PER/830/FR/P/E26/D 4/4CT	Only with specific dimmers
581835	14A19/PER/840/FR/P/E26/D 4/4CT	Only with specific dimmers
581868	14A19/PER/850/FR/P/E26/D 4/4CT	Only with specific dimmers
578534	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578542	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578559	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers

Order Code	Full Product Name	Dimmable
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578583	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578591	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578609	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578617	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578625	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers
578633	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	Only with specific dimmers

Operating and electrical

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	60 Hz	40 W	5 W
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	60 Hz	60 W	8.8 W
545897	8.8A19/PER/940/P/E26/DI M 6/1FB T20	60 Hz	60 W	8.8 W
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	60 Hz	40 W	5 W
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	60 Hz	60 W	8.8 W
550442	8.8A19/PER/930/P/E26/DI M 6/1FB T20	60 Hz	60 W	8.8 W
550459	8.8A19/PER/950/P/E26/DI M 6/1FB T20	60 Hz	60 W	8.8 W
556795	4.5A19/VIN/820/E26/CL/GL/ DIM 4/1FBH T20	60 Hz	60 W	4.5 W
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	50 to 60 Hz	40 W	5 W
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	50 to 60 Hz	60 W	8 W
560994	12.2A19/PER/950/P/E26/DI M 6/1FB T20	60 Hz	75 W	12.2 W
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	60 Hz	75 W	12.2 W

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	60 Hz	100 W	16 W
561035	12.2A19/PER/927/P/E26/DI M 6/1FB T20	60 Hz	75 W	12.2 W
561043	12.2A19/PER/930/P/E26/DI M 6/1FB T20	60 Hz	75 W	12.2 W
561050	12.2A19/PER/940/P/E26/DI M 6/1FB T20	60 Hz	75 W	12.2 W
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	60 Hz	100 W	16 W
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	60 Hz	60 W	8.8 W
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	60 Hz	100 W	16 W
573238	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	60 Hz	60 W	8.8 W
571505	29A21/PER/850/FR/P/E26/D/HO 4/1PF	60 Hz	150 W	29 W
565085	5A19/LED/927/FR/P/ND 4/1FB	60 Hz	40 W	5 W
565093	5A19/LED/930/FR/P/ND 4/1FB	60 Hz	40 W	5 W
565100	5A19/LED/950/FR/P/ND 4/1FB	60 Hz	40 W	5 W
565119	8.5A19/LED/927/FR/P/ND 4/1FB	60 Hz	60 W	8.5 W
565127	8.5A19/LED/930/FR/P/ND 4/1FB	60 Hz	60 W	8.5 W
565135	8.5A19/LED/950/FR/P/ND 4/1FB	60 Hz	60 W	8.5 W
571588	5A19/LED/927/FR/P/E26/N D/T20 6/1FB	60 Hz	40 W	5 W

A-Shape LED

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
571596	5A19/LED/930/FR/P/E26/N D/T20 6/1FB	60 Hz	40 W	5 W
571604	5A19/LED/950/FR/P/E26/N D/T20 6/1FB	60 Hz	40 W	5 W
571612	8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	60 Hz	60 W	8.8 W
571620	8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	60 Hz	60 W	8.8 W
571638	8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	60 Hz	60 W	8.8 W
581751	8A19/PER/827/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
581785	8A19/PER/850/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
581769	8A19/PER/830/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
581777	8A19/PER/840/FR/P/E26/D 4/4CT	60 Hz	60 W	8 W
565143	10A19/LED/927/FR/P/ND 4/1FB	60 Hz	75 W	10 W
565150	10A19/LED/930/FR/P/ND 4/1FB	60 Hz	75 W	10 W
565168	10A19/LED/950/FR/P/ND 4/1FB	60 Hz	75 W	10 W
565176	13.5A19/LED/927/FR/P/ND 4/1FB	60 Hz	100 W	13.5 W
565184	13.5A19/LED/930/FR/P/ND 4/1FB	60 Hz	100 W	13.5 W
565192	13.5A19/LED/950/FR/P/ND 4/1FB	60 Hz	100 W	13.5 W
571646	12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	60 Hz	75 W	12.2 W
571653	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	60 Hz	75 W	12.2 W
571661	12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	60 Hz	75 W	12.2 W
571679	16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	60 Hz	100 W	16.6 W

Order Code	Full Product Name	Input Frequency	Wattage Equivalent	Power (Nom)
571687	16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	60 Hz	100 W	16.6 W
571695	16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	60 Hz	100 W	16.6 W
581801	14A19/PER/827/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
581827	14A19/PER/830/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
581835	14A19/PER/840/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
581868	14A19/PER/850/FR/P/E26/D 4/4CT	60 Hz	100 W	14 W
578534	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 Hz	40 W	5 W
578542	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	60 Hz	40 W	5 W
578559	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 Hz	40 W	5 W
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 Hz	60 W	8 W
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	60 Hz	60 W	8 W
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 Hz	60 W	8 W
578583	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 Hz	75 W	9.5 W
578591	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	60 Hz	75 W	9.5 W
578609	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 Hz	75 W	9.5 W
578617	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	60 Hz	100 W	12 W
578625	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	60 Hz	100 W	12 W
578633	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 Hz	100 W	12 W

General information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	E26	15000 h	50000
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	E26	15000 h	50000
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000

A-Shape LED

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
556795	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	E26	15000 h	20000X
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	E26	15000 h	20000X
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	E26	15000 h	20000X
560994	12.2A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	E26	15000 h	50000
561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	E26	15000 h	50000
561035	12.2A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561043	12.2A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561050	12.2A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	E26	15000 h	50000
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	E26	15000 h	50000
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	GU24	15000 h	50000X
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	GU24	15000 h	50000
573238	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	E26	15000 h	50000
571505	29A21/PER/850/FR/P/E26/D/HO 4/1PF	E26	15000 h	50000
565085	5A19/LED/927/FR/P/ND 4/1FB	E26	11000 h	50000
565093	5A19/LED/930/FR/P/ND 4/1FB	E26	11000 h	50000
565100	5A19/LED/950/FR/P/ND 4/1FB	E26	11000 h	50000
565119	8.5A19/LED/927/FR/P/ND 4/1FB	E26	11000 h	50000
565127	8.5A19/LED/930/FR/P/ND 4/1FB	E26	11000 h	50000
565135	8.5A19/LED/950/FR/P/ND 4/1FB	E26	11000 h	50000
571588	5A19/LED/927/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
571596	5A19/LED/930/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571604	5A19/LED/950/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571612	8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571620	8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571638	8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
581751	8A19/PER/827/FR/P/E26/D 4/4CT	E26	15000 h	50000
581785	8A19/PER/850/FR/P/E26/D 4/4CT	E26	15000 h	50000
581769	8A19/PER/830/FR/P/E26/D 4/4CT	E26	15000 h	50000
581777	8A19/PER/840/FR/P/E26/D 4/4CT	E26	15000 h	50000
565143	10A19/LED/927/FR/P/ND 4/1FB	E26	11000 h	50000
565150	10A19/LED/930/FR/P/ND 4/1FB	E26	11000 h	50000
565168	10A19/LED/950/FR/P/ND 4/1FB	E26	11000 h	50000
565176	13.5A19/LED/927/FR/P/ND 4/1FB	E26	11000 h	50000
565184	13.5A19/LED/930/FR/P/ND 4/1FB	E26	11000 h	50000
565192	13.5A19/LED/950/FR/P/ND 4/1FB	E26	11000 h	50000
571646	12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571653	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571661	12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571679	16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571687	16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
571695	16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	E26	11000 h	50000
581801	14A19/PER/827/FR/P/E26/D 4/4CT	E26	15000 h	50000
581827	14A19/PER/830/FR/P/E26/D 4/4CT	E26	15000 h	50000
581835	14A19/PER/840/FR/P/E26/D 4/4CT	E26	15000 h	50000
581868	14A19/PER/850/FR/P/E26/D 4/4CT	E26	15000 h	50000
578534	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578542	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578559	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X

A-Shape LED

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle	Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X	578609	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X	578617	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X	578625	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578583	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X	578633	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X
578591	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	15000 h	20000X					

Light technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	250°	922-927	2200, 2700 K	90	450 lm
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	250°	922-927	2200, 2700 K	90	800 lm
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	250°	940	4000 K	90	800 lm
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	250°	927	2700 K	90	450 lm
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	250°	930	3000 K	90	450 lm
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	250°	940	4000 K	90	450 lm
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	250°	950	5000 K	90	450 lm
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	250°	927	2700 K	90	800 lm
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	250°	930	3000 K	90	800 lm
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	250°	950	5000 K	90	800 lm
556795	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	-	820	2000 K	80	300 lm
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	300°	927-922	2700, 2200 K	90	450 lm
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	300°	927-922	2700, 2200 K	90	800 lm
560994	12.2A19/PER/950/P/E26/DIM 6/1FB T20	250°	950	5000 K	90	1100 lm
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	250°	950	5000 K	90	1600 lm
561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	250°	922-927	2200, 2700 K	90	1100 lm
561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	250°	922-927	2200, 2700 K	90	1600 lm
561035	12.2A19/PER/927/P/E26/DIM 6/1FB T20	250°	927	2700 K	90	1100 lm
561043	12.2A19/PER/930/P/E26/DIM 6/1FB T20	250°	930	3000 K	90	1100 lm
561050	12.2A19/PER/940/P/E26/DIM 6/1FB T20	250°	940	4000 K	90	1100 lm
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	250°	927	2700 K	90	1600 lm
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	250°	930	3000 K	90	1600 lm
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	250°	940	4000 K	90	1600 lm
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	250°	930	3000 K	90	800 lm
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	250°	930	3000 K	90	1600 lm
573238	8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF	220°	927	2700 K	90	800 lm
571505	29A21/PER/850/FR/P/E26/D/HO 4/IPF	250°	850	5000 K	80	2610 lm
565085	5A19/LED/927/FR/P/ND 4/1FB	150°	927	2700 K	90	450 lm
565093	5A19/LED/930/FR/P/ND 4/1FB	150°	930	3000 K	90	450 lm
565100	5A19/LED/950/FR/P/ND 4/1FB	150°	950	5000 K	90	450 lm
565119	8.5A19/LED/927/FR/P/ND 4/1FB	150°	927	2700 K	90	800 lm
565127	8.5A19/LED/930/FR/P/ND 4/1FB	150°	930	3000 K	90	800 lm
565135	8.5A19/LED/950/FR/P/ND 4/1FB	150°	950	5000 K	90	800 lm
571588	5A19/LED/927/FR/P/E26/ND/T20 6/1FB	250°	927	2700 K	90	450 lm
571596	5A19/LED/930/FR/P/E26/ND/T20 6/1FB	250°	930	3000 K	90	450 lm

A-Shape LED

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index	
					(Nom)	Luminous Flux (Nom)
571604	5A19/LED/950/FR/P/E26/ND/T20 6/1FB	250 °	950	5000 K	90	450 lm
571612	8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	250 °	927	2700 K	90	800 lm
571620	8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	250 °	930	3000 K	90	800 lm
571638	8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	250 °	950	5000 K	90	800 lm
581751	8A19/PER/827/FR/P/E26/D 4/4CT	-	827	2700 K	80	800 lm
581785	8A19/PER/850/FR/P/E26/D 4/4CT	-	850	5000 K	80	800 lm
581769	8A19/PER/830/FR/P/E26/D 4/4CT	-	830	3000 K	80	800 lm
581777	8A19/PER/840/FR/P/E26/D 4/4CT	-	841	4000 K	80	800 lm
565143	10A19/LED/927/FR/P/ND 4/1FB	150 °	927	2700 K	90	1000 lm
565150	10A19/LED/930/FR/P/ND 4/1FB	150 °	930	3000 K	90	1000 lm
565168	10A19/LED/950/FR/P/ND 4/1FB	150 °	950	5000 K	90	1000 lm
565176	13.5A19/LED/927/FR/P/ND 4/1FB	150 °	927	2700 K	90	1500 lm
565184	13.5A19/LED/930/FR/P/ND 4/1FB	150 °	930	3000 K	90	1500 lm
565192	13.5A19/LED/950/FR/P/ND 4/1FB	150 °	950	5000 K	90	1500 lm
571646	12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	250 °	927	2700 K	90	1100 lm
571653	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	250 °	930	3000 K	90	1100 lm
571661	12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	250 °	950	5000 K	90	1100 lm
571679	16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	250 °	927	2700 K	90	1500 lm
571687	16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	250 °	930	3000 K	90	1500 lm
571695	16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	250 °	950	5000 K	90	1500 lm
581801	14A19/PER/827/FR/P/E26/D 4/4CT	-	827	2700 K	80	1600 lm
581827	14A19/PER/830/FR/P/E26/D 4/4CT	-	830	3000 K	80	1600 lm
581835	14A19/PER/840/FR/P/E26/D 4/4CT	-	841	4000 K	80	1600 lm
581868	14A19/PER/850/FR/P/E26/D 4/4CT	-	850	5000 K	80	1600 lm
578534	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	320 °	927	2700 K	90	450 lm
578542	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	320 °	930	3000 K	90	450 lm
578559	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	320 °	950	5000 K	90	450 lm
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	320 °	927	2700 K	90	800 lm
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	320 °	930	3000 K	90	800 lm
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	320 °	950	5000 K	90	800 lm
578583	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	320 °	927	2700 K	90	1100 lm
578591	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	320 °	930	3000 K	90	1100 lm
578609	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	320 °	950	5000 K	90	1100 lm
578617	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	320 °	927	2700 K	90	1600 lm
578625	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	320 °	930	3000 K	90	1600 lm
578633	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	320 °	950	5000 K	90	1600 lm

Mechanical and housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape	Order Code	Full Product Name	Bulb Finish	Bulb Shape
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	Frosted	A19 (A19)	549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	Clear	A19 (A19)
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	Frosted	A19 (A19)	549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	Clear	A19 (A19)
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	560994	12.2A19/PER/950/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561019	16A19/PER/950/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	Frosted	A19 (A19)
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	Frosted	A19 (A19)
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561035	12.2A19/PER/927/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561043	12.2A19/PER/930/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561050	12.2A19/PER/940/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)	561068	16A19/PER/927/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
556795	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	Amber	A19 (A19)	561076	16A19/PER/930/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)

A-Shape LED

Order Code	Full Product Name	Bulb Finish	Bulb Shape
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	Frosted	A19 (A19)
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	Frosted	A19 (A19)
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	Frosted	A21 (A21)
573238	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	Frosted	A19 (A19)
571505	29A21/PER/850/FR/P/E26/D/HO 4/1PF	Frosted	A21 (A21)
565085	5A19/LED/927/FR/P/ND 4/1FB	Frosted	A19 (A19)
565093	5A19/LED/930/FR/P/ND 4/1FB	Frosted	A19 (A19)
565100	5A19/LED/950/FR/P/ND 4/1FB	Frosted	A19 (A19)
565119	8.5A19/LED/927/FR/P/ND 4/1FB	Frosted	A19 (A19)
565127	8.5A19/LED/930/FR/P/ND 4/1FB	Frosted	A19 (A19)
565135	8.5A19/LED/950/FR/P/ND 4/1FB	Frosted	A19 (A19)
571588	5A19/LED/927/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571596	5A19/LED/930/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571604	5A19/LED/950/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571612	8.8A19/LED/927/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571620	8.8A19/LED/930/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571638	8.8A19/LED/950/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
581751	8A19/PER/827/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
581785	8A19/PER/850/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
581769	8A19/PER/830/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
581777	8A19/PER/840/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
565143	10A19/LED/927/FR/P/ND 4/1FB	Frosted	A19 (A19)
565150	10A19/LED/930/FR/P/ND 4/1FB	Frosted	A19 (A19)
565168	10A19/LED/950/FR/P/ND 4/1FB	Frosted	A19 (A19)
565176	13.5A19/LED/927/FR/P/ND 4/1FB	Frosted	A19 (A19)

Order Code	Full Product Name	Bulb Finish	Bulb Shape
565184	13.5A19/LED/930/FR/P/ND 4/1FB	Frosted	A19 (A19)
565192	13.5A19/LED/950/FR/P/ND 4/1FB	Frosted	A19 (A19)
571646	12.2A19/LED/927/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571653	12.2A19/LED/930/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571661	12.2A19/LED/950/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571679	16.6A19/LED/927/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571687	16.6A19/LED/930/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
571695	16.6A19/LED/950/FR/P/E26/ND/T20 6/1FB	Frosted	A19 (A19)
581801	14A19/PER/827/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
581827	14A19/PER/830/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
581835	14A19/PER/840/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
581868	14A19/PER/850/FR/P/E26/D 4/4CT	Frosted	A19 (A19)
578534	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578542	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578559	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578567	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578575	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578641	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578583	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578591	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578609	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578617	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578625	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)
578633	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	Frosted	A19 (A19)

Temperature

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
479428	5A19/PER/927-22/P/E26/WG 6/1FB T20	-	-	149 °F
479444	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	-	-	176 °F
545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	-	-	194 °F
550400	5A19/PER/927/P/E26/DIM 6/1FB T20	-	-	167 °F
550418	5A19/PER/930/P/E26/DIM 6/1FB T20	-	-	167 °F
547042	5A19/PER/940/P/E26/DIM 6/1FB T20	-	-	167 °F
550426	5A19/PER/950/P/E26/DIM 6/1FB T20	-	-	167 °F
550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	-	-	194 °F
550442	8.8A19/PER/930/P/E26/DIM 6/1FB T20	-	-	194 °F
550459	8.8A19/PER/950/P/E26/DIM 6/1FB T20	-	-	194 °F

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
556795	4.5A19/VIN/820/E26/CL/GL/DI M 4/FBH T20	-	-	131 °F
549485	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	-	-	122 °F
549493	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	-	-	140 °F
560994	12.2A19/PER/950/P/E26/DIM 6/1FB T20	-	-	185 °F
561019	16A19/PER/950/P/E26/DIM 6/1FB T20	-	-	194 °F
561000	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	-	-	185 °F
561027	16A19/PER/927-22/P/E26/WG 6/1FB T20	-	-	194 °F
561035	12.2A19/PER/927/P/E26/DIM 6/1FB T20	-	-	185 °F
561043	12.2A19/PER/930/P/E26/DIM 6/1FB T20	-	-	185 °F










A-Shape LED

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
561050	12.2A19/PER/940/P/E26/DIM 6/1FB T20	-	-	185 °F
561068	16A19/PER/927/P/E26/DIM 6/1FB T20	-	-	194 °F
561076	16A19/PER/930/P/E26/DIM 6/1FB T20	-	-	194 °F
561456	16A19/PER/940/P/E26/DIM 6/1FB T20	-	-	194 °F
557660	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	-	-	194 °F
558684	16A21/PER/930/P/GU24/DIM 4/1FB T20	113 °F	-4 °F	194 °F
573238	8.8A19/PER/927/FR/P/E26/D2 D/T20 4/1PF	-	-	203 °F
571505	29A21/PER/850/FR/P/E26/D/ HO 4/1PF	113 °F	-4 °F	212 °F
565085	5A19/LED/927/FR/P/ND 4/1FB	-	-	167 °F
565093	5A19/LED/930/FR/P/ND 4/1FB	-	-	167 °F
565100	5A19/LED/950/FR/P/ND 4/1FB	-	-	167 °F
565119	8.5A19/LED/927/FR/P/ND 4/1FB	-	-	185 °F
565127	8.5A19/LED/930/FR/P/ND 4/1FB	-	-	185 °F
565135	8.5A19/LED/950/FR/P/ND 4/1FB	-	-	185 °F
571588	5A19/LED/927/FR/P/E26/ND/ T20 6/1FB	-	-	149 °F
571596	5A19/LED/930/FR/P/E26/ND/ T20 6/1FB	-	-	149 °F
571604	5A19/LED/950/FR/P/E26/ND/ T20 6/1FB	-	-	149 °F
571612	8.8A19/LED/927/FR/P/E26/ND /T20 6/1FB	-	-	185 °F
571620	8.8A19/LED/930/FR/P/E26/N D/T20 6/1FB	-	-	185 °F
571638	8.8A19/LED/950/FR/P/E26/N D/T20 6/1FB	-	-	185 °F
581751	8A19/PER/827/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
581785	8A19/PER/850/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
581769	8A19/PER/830/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
581777	8A19/PER/840/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
565143	10A19/LED/927/FR/P/ND 4/1FB	-	-	203 °F
565150	10A19/LED/930/FR/P/ND 4/1FB	-	-	203 °F











Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
565168	10A19/LED/950/FR/P/ND 4/1FB	-	-	203 °F
565176	13.5A19/LED/927/FR/P/ND 4/1FB	-	-	203 °F
565184	13.5A19/LED/930/FR/P/ND 4/1FB	-	-	203 °F
565192	13.5A19/LED/950/FR/P/ND 4/1FB	-	-	203 °F
571646	12.2A19/LED/927/FR/P/E26/N D/T20 6/1FB	-	-	185 °F
571653	12.2A19/LED/930/FR/P/E26/N D/T20 6/1FB	-	-	185 °F
571661	12.2A19/LED/950/FR/P/E26/N D/T20 6/1FB	-	-	185 °F
571679	16.6A19/LED/927/FR/P/E26/N D/T20 6/1FB	-	-	194 °F
571687	16.6A19/LED/930/FR/P/E26/N D/T20 6/1FB	-	-	194 °F
571695	16.6A19/LED/950/FR/P/E26/N D/T20 6/1FB	-	-	194 °F
581801	14A19/PER/827/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
581827	14A19/PER/830/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
581835	14A19/PER/840/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
581868	14A19/PER/850/FR/P/E26/D 4/4CT	113 °F	-4 °F	194 °F
578534	5A19/LED/927/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578542	5A19/LED/930/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578559	5A19/LED/950/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578567	8A19/LED/927/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578575	8A19/LED/930/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578641	8A19/LED/950/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578583	9.5A19/LED/927/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578591	9.5A19/LED/930/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578609	9.5A19/LED/950/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578617	12A19/LED/927/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-
578625	12A19/LED/930/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-

A-Shape LED











Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
578633	12A19/LED/950/FR/ Glass/E26/DIM 1FB T20	113 °F	-4 °F	-













A-Shape LED








A-Shape LED








A-Shape LED



A-Shape LED



(cd/1000lm) 0°



(cd/1000lm) 0°

A-Shape LED

