

SGP268 Broadway

Broadway SGP268 *do not use*

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

Benefits

- High IP

Features


- Dedicated faceted optics to optimize beam control and maximise light output
- Adjustable optics
- Choice of different bowls: curved or flat glass
- High IP: lamp compartment IP66, dust-tight and jet-water proof
- Dimming option available for SON-T 250/400W lamp versions
- Maintenance from above in an ergonomic position

Application

- Major urban roads
- Expressways
- Motorways

Broadway SGP268 *do not use*

Versions



SGP268 SON

General Information

| | |
|-------------------------|------------------|
| Optical cover/lens type | Glass bowl/cover |
| Lamp family code | SON-T |

General Information

| Order Code | Full Product Name | Cap-Base | Country version | Gear | Lamp power | Number of light sources | Optic type |
|--------------|--|----------|-----------------|------|------------|-------------------------|------------|
| 910401962780 | SGP268 SON-T150W 220V-50Hz GB SI | E40 | NO | SGR | 150 W | 1 pc | Open T-POT |
| 910401962880 | SGP268 SON-T250W 220V-50Hz GB SI | E40 | NO | SGR | 250 W | 1 pc | Open T-POT |
| 910401962980 | SGP268 SON-T400W 220V-50Hz GB SI | E40 | NO | SGR | 400 W | 1 pc | Open T-POT |
| 910403364180 | SGP268 SON-T400W 220V GB SI SD | E40 | CN | SGR | 400 W | 1 pc | Open T-POT |
| 910403364280 | SGP268 SON-T250W 220V GB SI SD | E40 | CN | SGR | 250 W | 1 pc | Open T-POT |
| 911400329180 | SGP268 SON-T150W 230V-50Hz GB SI | E40 | NO | SGR | 150 W | 1 pc | Open T-POT |
| 911400329480 | SGP268 SON-T250W 230V-50Hz GB SI | E40 | NO | SGR | 250 W | 1 pc | Open T-POT |
| 911400988680 | SGP268 SON-T400W 220V-50Hz GB ALU | E40 | NO | SGR | 400 W | 1 pc | Open T-POT |
| 911400988780 | SGP268 SON-T250W 220V-50Hz GB ALU | E40 | NO | SGR | 250 W | 1 pc | Open T-POT |
| 911400988980 | SGP268 SON-T150W 220V-50Hz GB ALU | E40 | NO | SGR | 150 W | 1 pc | Open T-POT |
| 911400998480 | SGP268 SON-T150W 220V-50Hz GB RAL7040 | E40 | NO | SGR | 150 W | 1 pc | - |
| 911400998580 | SGP268 SON-T250W 220V-50Hz GB RAL7040 | E40 | NO | SGR | 250 W | 1 pc | - |
| 911400998680 | SGP268 SON-T400W 220V-50Hz GB RAL7040 | E40 | NO | SGR | 400 W | 1 pc | - |
| 911400998780 | SGP268 SON-T150W 230V-50Hz GB RAL7040 | - | NO | CONV | 150 W | 1 pc | - |
| 911400998880 | SGP268 SON-T250W 230V-50Hz GB RAL7040 | - | NO | CONV | 250 W | 1 pc | - |
| 911400998980 | SGP268 SON-T400W 230V-50Hz GB RAL7040 | - | NO | CONV | 400 W | 1 pc | - |
| 911400999080 | SGP268 SON-T150W 240V-50Hz GB RAL7040 | - | NO | CONV | 150 W | 1 pc | - |
| 911400999180 | SGP268 SON-T250W 240V-50Hz GB RAL7040 | - | NO | CONV | 250 W | 1 pc | - |
| 911400999280 | SGP268 SON-T400W 240V-50Hz GB RAL7040 | - | NO | CONV | 400 W | 1 pc | - |
| 911400999380 | SGP268 SON-T250W 220V-50Hz GB SD RAL7040 | - | NO | - | 250 W | - | - |
| 911400999480 | SGP268 SON-T400W 220V-50Hz GB SD RAL7040 | - | NO | - | 400 W | - | - |

Light Technical

| Order Code | Full Product Name | Light output ratio | Order Code | Full Product Name | Light output ratio |
|--------------|----------------------------------|--------------------|--------------|-----------------------------------|--------------------|
| 910401962780 | SGP268 SON-T150W 220V-50Hz GB SI | 0.93 | 911400329180 | SGP268 SON-T150W 230V-50Hz GB SI | 0.84 |
| 910401962880 | SGP268 SON-T250W 220V-50Hz GB SI | 0.84 | 911400329480 | SGP268 SON-T250W 230V-50Hz GB SI | 0.93 |
| 910401962980 | SGP268 SON-T400W 220V-50Hz GB SI | 0.7 | 911400988680 | SGP268 SON-T400W 220V-50Hz GB ALU | - |
| 910403364180 | SGP268 SON-T400W 220V GB SI SD | - | 911400988780 | SGP268 SON-T250W 220V-50Hz GB ALU | - |
| 910403364280 | SGP268 SON-T250W 220V GB SI SD | - | 911400988980 | SGP268 SON-T150W 220V-50Hz GB ALU | - |

Broadway SGP268 *do not use*

| Order Code | Full Product Name | Light output ratio |
|--------------|---------------------------------------|--------------------|
| 911400998480 | SGP268 SON-T150W 220V-50Hz GB RAL7040 | - |
| 911400998580 | SGP268 SON-T250W 220V-50Hz GB RAL7040 | - |
| 911400998680 | SGP268 SON-T400W 220V-50Hz GB RAL7040 | - |
| 911400998780 | SGP268 SON-T150W 230V-50Hz GB RAL7040 | - |
| 911400998880 | SGP268 SON-T250W 230V-50Hz GB RAL7040 | - |
| 911400998980 | SGP268 SON-T400W 230V-50Hz GB RAL7040 | - |

| Order Code | Full Product Name | Light output ratio |
|--------------|--|--------------------|
| 911400999080 | SGP268 SON-T150W 240V-50Hz GB RAL7040 | - |
| 911400999180 | SGP268 SON-T250W 240V-50Hz GB RAL7040 | - |
| 911400999280 | SGP268 SON-T400W 240V-50Hz GB RAL7040 | - |
| 911400999380 | SGP268 SON-T250W 220V-50Hz GB SD RAL7040 | - |
| 911400999480 | SGP268 SON-T400W 220V-50Hz GB SD RAL7040 | - |

Mechanical and Housing

| Order Code | Full Product Name | Color |
|--------------|---------------------------------------|----------|
| 910401962780 | SGP268 SON-T150W 220V-50Hz GB SI | Silver |
| 910401962880 | SGP268 SON-T250W 220V-50Hz GB SI | Silver |
| 910401962980 | SGP268 SON-T400W 220V-50Hz GB SI | Silver |
| 910403364180 | SGP268 SON-T400W 220V GB SI SD | Silver |
| 910403364280 | SGP268 SON-T250W 220V GB SI SD | Silver |
| 911400329180 | SGP268 SON-T150W 230V-50Hz GB SI | Silver |
| 911400329480 | SGP268 SON-T250W 230V-50Hz GB SI | Silver |
| 911400988680 | SGP268 SON-T400W 220V-50Hz GB ALU | Aluminum |
| 911400988780 | SGP268 SON-T250W 220V-50Hz GB ALU | Aluminum |
| 911400988980 | SGP268 SON-T150W 220V-50Hz GB ALU | Aluminum |
| 911400998480 | SGP268 SON-T150W 220V-50Hz GB RAL7040 | - |

| Order Code | Full Product Name | Color |
|--------------|--|-------|
| 911400998580 | SGP268 SON-T250W 220V-50Hz GB RAL7040 | - |
| 911400998680 | SGP268 SON-T400W 220V-50Hz GB RAL7040 | - |
| 911400998780 | SGP268 SON-T150W 230V-50Hz GB RAL7040 | - |
| 911400998880 | SGP268 SON-T250W 230V-50Hz GB RAL7040 | - |
| 911400998980 | SGP268 SON-T400W 230V-50Hz GB RAL7040 | - |
| 911400999080 | SGP268 SON-T150W 240V-50Hz GB RAL7040 | - |
| 911400999180 | SGP268 SON-T250W 240V-50Hz GB RAL7040 | - |
| 911400999280 | SGP268 SON-T400W 240V-50Hz GB RAL7040 | - |
| 911400999380 | SGP268 SON-T250W 220V-50Hz GB SD RAL7040 | - |
| 911400999480 | SGP268 SON-T400W 220V-50Hz GB SD RAL7040 | - |

