



SGP338 Velocity

Velocity

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

Benefits

- Step dimming option available up to SON-T 250W lamp version

Features

- High quality optical system for clear tubular lamps
- Adjustable lamp position to obtain several light distributions
- Dustproof and jetproof (IP66) lamp compartment: no internal cleaning required
- Easy access and maintenance of gear and lamp

Application

- Motorways
- Major roads
- Expressways

Versions



General Information	
Country version	NO
Optical cover/lens type	GB
Lamp family code	SON-T
Number of light sources	1

General Information

Order Code	Full Product Name	Cap-Base	Gear	Lamp power
911400997780	SGP338 SON-T400W 220V-50Hz GB RAL7040	E40	SON gear	400 W
911400997880	SGP338 SON-T150W 230V-50Hz GB RAL7040	-	CONV	150 W

Order Code	Full Product Name	Cap-Base	Gear	Lamp power
911400997980	SGP338 SON-T250W 230V-50Hz GB RAL7040	-	CONV	250 W

