



# SGP338 Velocity

## Velocity \*do not use\*

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

### Benefits

- Step dimming option available up to SON-T 250W lamp version

### Features

- High quality optical system for clear tubular lamps
- Adjustable lamp position to obtain several light distributions
- Dustproof and jetproof (IP66) lamp compartment: no internal cleaning required
- Easy access and maintenance of gear and lamp

### Application

- Motorways
- Major roads
- Expressways

### Versions



**General Information**

Country version	NO
Optical cover/lens type	Glass bowl/cover
Lamp family code	SON-T

**General Information**

Order Code	Full Product Name	Cap-Base	Gear	Lamp power	Number of light sources
911400997880	SGP338 SON-T150W 230V-50Hz GB RAL7040	-	CONV	150 W	1 pc
911400997980	SGP338 SON-T250W 230V-50Hz GB RAL7040	-	CONV	250 W	1 pc
911400998080	SGP338 SON-T150W 240V-50Hz GB RAL7040	-	CONV	150 W	1 pc

Order Code	Full Product Name	Cap-Base	Gear	Lamp power	Number of light sources
911400998180	SGP338 SON-T250W 240V-50Hz GB RAL7040	-	CONV	250 W	1 pc
911400998280	SGP338 SON-T250W 220V-50Hz GB SD RAL7040	-	-	250 W	-

**Mechanical and Housing**

Order Code	Full Product Name	Color
911400997880	SGP338 SON-T150W 230V-50Hz GB RAL7040	-
911400997980	SGP338 SON-T250W 230V-50Hz GB RAL7040	-
911400998080	SGP338 SON-T150W 240V-50Hz GB RAL7040	-

Order Code	Full Product Name	Color
911400998180	SGP338 SON-T250W 240V-50Hz GB RAL7040	-
911400998280	SGP338 SON-T250W 220V-50Hz GB SD RAL7040	-

