



Selenium – timeless design

Selenium

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).

Benefits

- Timeless design in an efficient, ergonomic road-lighting luminaire with a simple, rounded form that reduces daytime visual impact
- Incorporates the renowned T-POT reflector for excellent optical performance
- Energy savings are possible by means of dimming with a switch, or stand-alone Chronosense system without pilot cable

Features

- Timeless design
- T-POT optic
- Dimming with switch or stand-alone Chronosense system (without pilot cable)
- Three tilt angles for optimal installation on mast or bracket

Application

- Industrial areas
- Roads
- Crossings, roundabouts

Specifications

Type	SGP340	Light source	HID:
------	--------	--------------	------

	- 1 x MASTER SON-T PIA Plus / E27 / 50, 70 W
	- 1 x MASTER SON-T PIA Plus / E40 / 100, 150, 250, 400 W
	- 1 x SON / E27 / 50, 70 W
	- 1 x SON / E40 / 100, 150, 250 W
	- 1 x SON-I / E27 / 50, 70 W
Lamp included	Yes (K) No
Mains voltage	230 or 240 V
Gear	Electro magnetic (low loss), 230 or 240 V / 50 Hz: - Inductive (IN) Electronic, 220 - 240 V / 50 - 60 Hz: - Electronic (EB)
Optic	Facetted semi closed T-POT (TP)
Optical cover	Glass flat (FG), reduce glare and improve night nuisance Polycarbonate bowl (PC) vandal-resistant
Ignitor	Series (SI) Series, self-stopping (SS) Semi-parallel (SP) Semi-parallel, self-stopping (ST)
Options	Lighting controls: Chronosense (CH) Light regulation: - Dimming switch (SW) - Dimming switch with reverse function (SWR) Photocell: NEMA socket (P1), Minicell (P3) Fuse (FU) included Knife-connector (KC) included

Materials and finishing	Canopy and frame: die-cast aluminum Mounting module: die-cast aluminum Optical covers: polycarbonate bowl or toughened glass Reflector: high-purity aluminum Closing clip: stainless steel
Color	Grey (RAL 7035) Other RAL colors available on request
Installation	Side-entry mounting: lateral entry Ø 48 / 60 mm (48/60) Post-top mounting: axial entry Ø 48 / 60 mm (48/60) Spigot is reversible for side-entry and post-top Recommended mounting height: 10 m Standard tilt angle post top: 5° Adjustable tilt angle: 0.5 and 15° Adjustable light distribution: 5 positions Max windage area: 0.14 m Max SCx values by side: 0.077 m
Maintenance	From above by opening the housing with a single quick-release clip No tools needed for geartry and disconnection of plug and socket
Accessories	Spigots for 34 mm side-entry, ZGP340 SP34S and 76 mm post-top, ZGP340 SP76P
Main applications	Industrial areas, roads, crossings, roundabouts

Versions




Selenium SGP340, svítidlo
pouličního osvětlení s plochým
sklem (FG)



Selenium SGP340, svítidlo uličního
osvětlení s polykarbonátovým
krytem (PC)



Dimensional drawing




Product
SGP340 SON-T150W K EBD II PC D9 48/60
SGP340 CPO-TW45W K EB II OR FG 48/60
SGP340 SON-T100W K EBD I FG D9 48/60
SGP340 SON-T400W I FG SKD 48/60
SGP340 SON-T100W K EBD II FG D9 48/60
SGP340 SON-T250W K I FG SKD 48/60
SGP340 CDO-TT70W K I OR FG SKD 48/60
SGP340 SON-T100W K II FG SKD 76
SGP340 SON-T250W II FG SKD FU KC 48/60
SGP340 SON-T250W K II FG SKD KC 48/60
SGP340 SON-T250W II FG SKD 76
SGP340 SON-T70W K EBD II FG D9 48/60
SGP340 SON-T100W K I PC SKD 48/60
SGP340 SON-T250W II FG SKD 48/60
SGP340 SON-T250W K II FG SKD 48/60
SGP340 SON-T150W I PC SKD 48/60
SGP340 SON-T100W I PC SKD 48/60
SGP340 SON-T100W II PC SKD 48/60
SGP340 SON-T70W K 240V I PC SKD P1 34/42
SGP340 SON-T50W K I PC SKD 48/60
SGP340 SON-T100W II FG SKD 48/60
SGP340 CDO-TT100W K II PC SKD 48/60
SGP340 SON-T250W K II PC SKD 48/60
SGP340 SON-T250W I FG SKD 48/60
SGP340 SON-T70W II FG SKD 48/60
SGP340 SON-T400W K I FG SKD 76
SGP340 SON-T150W II FG SKD KC 48/60
SGP340 SON-T250W K EBD I FG D9 48/60
SGP340 SON-T150W K I PC SKD 48/60
SGP340 CDO-TT50W K II OR PC SKD 48/60
SGP340 CPO-TW140W K EB II OR FG 48/60
SGP340 SON-T250W I PC SKD 48/60
SGP340 SON-T100W K EBD II PC D9 48/60
SGP340 SON-T100W K II FG SKD 48/60
SGP340 CPO-TW90W K EB II OR FG 48/60
SGP340 CDO-TT150W K I FG SKD 48/60
SGP340 CPO-TW60W K EBR II OR FG LS-8 48/
SGP340 CPO-TW60W K EB II OR PC 48/60
SGP340 SON-T150W II FG SKD 76
SGP340 SON-T250W II PC SKD 48/60
SGP340 CDO-TT150W K II PC SKD 48/60
SGP340 SON-T50W K II FG SKD 48/60
SGP340 SON-T250W K II FG SKD 76
SGP340 SON-T150W K 240V I FG SKD P1 34/4
SGP340 CPO-TW90W K EB II OR PC 48/60
SGP340 SON-T250W K I PC SKD 48/60
SGP340 SON-T70W II PC SKD 48/60
SGP340 SON-T70W K EBD I FG D9 48/60
SGP340 CDO-TT100W K II FG SKD 48/60
SGP340 SON-T150W K II FG SKD 48/60


Dimensional drawing

Product
SGP340 CPO-TW60W K EBR II OR PC LS-8 48/
SGP340 E27 II FG 48/60
SGP340 SON-T150W K 240V I PC SKD P1 34/4
SGP340 SON-T150W K EBD II FG D9 48/60
SGP340 SON-T250W K EBD I PC D9 48/60
SGP340 SON-T70W K I PC SKD 48/60
SGP340 CDO-TT250W K II FG SKD 48/60
SGP340 SON-T70W K EBD II PC D9 48/60
SGP340 CDO-TT250W K I FG SKD 48/60
SGP340 CPO-TW140W K EB II OR PC 48/60
SGP340 SON-T70W K II FG SKD 48/60
SGP340 CPO-TW90W K EBR II OR FG LS-8 48/
SGP340 CDO-TT70W K II OR FG SKD 48/60
SGP340 SON-T400W K I FG SKD 48/60
SGP340 CPO-TW45W K EB II OR PC 48/60
SGP340 SON-T150W K EBD I FG D9 48/60
SGP340 SON-T150W II FG SKD 48/60
SGP340 SON-T150W II PC MSP SKD 48/60
SGP340 CDO-TT70W K II OR PC SKD 48/60
SGP340 SON-T100W K II PC MSP SKD 48/60
SGP340 SON-T150W K II FG SKD 76
SGP340 CPO-TW140W K EBR II OR FG LS-8 48
SGP340 SON-T150W II FG SKD FU KC 48/60
SGP340 SON-T70W II FG SKD FU KC 48/60
SGP340 SON-T150W K I FG SKD 48/60
SGP340 SON-T50W K II PC SKD 48/60
SGP340 CDO-TT150W K II FG SKD 48/60
SGP340 SON-T100W K I FG SKD 48/60
SGP340 SON-T50W II PC SKD 48/60
SGP340 CPO-TW140W K EBR II OR PC LS-8 48
SGP340 SON-T150W K II FG SKD KC 48/60
SGP340 CPO-TW60W K EB II OR FG 48/60
SGP340 E40 II FG 48/60

Product details



Selenium SGP340 road-lighting luminaire with flat glass



Selenium SGP340 road-lighting luminaire with polycarbonate bowl

General Information

Number of light sources	1
Product Family Code	SGP340

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	5°

Mechanical and Housing

Colour	Gray
--------	------

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
12767500	SGP340 E27 II FG 48/60	IK08
12768200	SGP340 E40 II FG 48/60	IK08
62616200	SGP340 CPO-TW45W K EB II OR FG 48/60	IK08
62618600	SGP340 CPO-TW60W K EB II OR FG 48/60	IK08
62620900	SGP340 CPO-TW90W K EB II OR FG 48/60	IK08
62622300	SGP340 CPO-TW140W K EB II OR FG 48/60	IK08
62624700	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/	IK08
62626100	SGP340 CPO-TW90W K EBR II OR FG LS-8 48/	IK08
62628500	SGP340 CPO-TW140W K EBR II OR FG LS-8 48	IK08
13151100	SGP340 SON-T400W I FG SKD 48/60	IK08
05951600	SGP340 SON-T70W K EBD II FG D9 48/60	IK08
05952300	SGP340 SON-T100W K EBD II FG D9 48/60	IK08
05953000	SGP340 SON-T150W K EBD II FG D9 48/60	IK08
05955400	SGP340 SON-T70W K EBD I FG D9 48/60	IK08
05956100	SGP340 SON-T100W K EBD I FG D9 48/60	IK08
05957800	SGP340 SON-T150W K EBD I FG D9 48/60	IK08
05958500	SGP340 SON-T250W K EBD I FG D9 48/60	IK08
06418300	SGP340 SON-T100W K I FG SKD 48/60	IK08
06419000	SGP340 SON-T150W K I FG SKD 48/60	IK08
06420600	SGP340 SON-T250W K I FG SKD 48/60	IK08
63273600	SGP340 CDO-TT70W K I OR FG SKD 48/60	IK08
63275000	SGP340 CDO-TT70W K II OR FG SKD 48/60	IK08
63279800	SGP340 CDO-TT100W K II FG SKD 48/60	IK08
63281100	SGP340 CDO-TT150W K I FG SKD 48/60	IK08
63283500	SGP340 CDO-TT150W K II FG SKD 48/60	IK08
63285900	SGP340 CDO-TT250W K I FG SKD 48/60	IK08
63287300	SGP340 CDO-TT250W K II FG SKD 48/60	IK08
63572000	SGP340 SON-T50W K II FG SKD 48/60	IK08
12775000	SGP340 SON-T70W II FG SKD FU KC 48/60	IK08
63546100	SGP340 SON-T70W II FG SKD 48/60	IK08
12656200	SGP340 SON-T100W K II FG SKD 76	IK08
63557700	SGP340 SON-T100W K II FG SKD 48/60	IK08
12777400	SGP340 SON-T150W II FG SKD FU KC 48/60	IK08
12773600	SGP340 SON-T150W II FG SKD KC 48/60	IK08
61062800	SGP340 SON-T150W K 240V I FG SKD P1 34/4	IK08
12695100	SGP340 SON-T150W K II FG SKD KC 48/60	IK08
63560700	SGP340 SON-T150W K II FG SKD 48/60	IK08
63564500	SGP340 SON-T150W II FG SKD 48/60	IK08

Order Code	Full Product Name	Mech. impact protection code
12696800	SGP340 SON-T250W K II FG SKD KC 48/60	IK08
12778100	SGP340 SON-T250W II FG SKD FU KC 48/60	IK08
63566900	SGP340 SON-T250W K II FG SKD 48/60	IK08
63568300	SGP340 SON-T250W II FG SKD 48/60	IK08
63570600	SGP340 SON-T250W I FG SKD 48/60	IK08
13220400	SGP340 SON-T400W K I FG SKD 48/60	IK08
62615500	SGP340 CPO-TW45W K EB II OR PC 48/60	IK10
62617900	SGP340 CPO-TW60W K EB II OR PC 48/60	IK10
62619300	SGP340 CPO-TW90W K EB II OR PC 48/60	IK10
62621600	SGP340 CPO-TW140W K EB II OR PC 48/60	IK10
62623000	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/	IK10
62627800	SGP340 CPO-TW140W K EBR II OR PC LS-8 48	IK10
05960800	SGP340 SON-T70W K EBD II PC D9 48/60	IK10
05961500	SGP340 SON-T100W K EBD II PC D9 48/60	IK10
05962200	SGP340 SON-T150W K EBD II PC D9 48/60	IK10
05967700	SGP340 SON-T250W K EBD I PC D9 48/60	IK10
63272900	SGP340 CDO-TT50W K II OR PC SKD 48/60	IK08
63276700	SGP340 CDO-TT70W K II OR PC SKD 48/60	IK08
63280400	SGP340 CDO-TT100W K II PC SKD 48/60	IK08
63284200	SGP340 CDO-TT150W K II PC SKD 48/60	IK08
12752100	SGP340 SON-T50W II PC SKD 48/60	IK08
63573700	SGP340 SON-T50W K II PC SKD 48/60	IK08
12652400	SGP340 SON-T70W K I PC SKD 48/60	IK08
63550800	SGP340 SON-T70W II PC SKD 48/60	IK08
12653100	SGP340 SON-T100W K I PC SKD 48/60	IK08
63047300	SGP340 SON-T100W K II PC MSP SKD 48/60	IK08
63552200	SGP340 SON-T100W I PC SKD 48/60	IK08
63555300	SGP340 SON-T100W II PC SKD 48/60	IK08
12704000	SGP340 SON-T150W K 240V I PC SKD P1 34/4	IK08
12654800	SGP340 SON-T150W K I PC SKD 48/60	IK08
63559100	SGP340 SON-T150W I PC SKD 48/60	IK08
63563800	SGP340 SON-T150W II PC MSP SKD 48/60	IK08
13330000	SGP340 SON-T250W K I PC SKD 48/60	IK08
63567600	SGP340 SON-T250W K II PC SKD 48/60	IK08
63569000	SGP340 SON-T250W II PC SKD 48/60	IK08
12651700	SGP340 SON-T50W K I PC SKD 48/60	IK08
12661600	SGP340 SON-T150W II FG SKD 76	IK08
63571300	SGP340 SON-T400W K I FG SKD 76	IK08

General Information (1/2)

Order Code	Full Product Name	Cap-Base	CE mark	Coating	Optical cover/lens type	Gear	Lamp family code	Lamp power
12767500	SGP340 E27 II FG 48/60	E27	-	-	FG	E	-	-
12768200	SGP340 E40 II FG 48/60	E40	-	-	FG	E	-	-
62616200	SGP340 CPO-TW45W K EB II OR FG 48/60	PGZ12	CE mark	-	FG	EB	CPO-TW	45 W
62618600	SGP340 CPO-TW60W K EB II OR FG 48/60	PGZ12	CE mark	-	FG	EB	CPO-TW	60 W
62620900	SGP340 CPO-TW90W K EB II OR FG 48/60	PGZ12	CE mark	-	FG	EB	CPO-TW	90 W
62622300	SGP340 CPO-TW140W K EB II OR FG 48/60	PGZ12	CE mark	-	FG	EB	CPO-TW	140 W
62624700	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/	PGZ12	CE mark	-	FG	EBR	CPO-TW	60 W
62626100	SGP340 CPO-TW90W K EBR II OR FG LS-8 48/	PGZ12	CE mark	-	FG	EBR	CPO-TW	90 W
62628500	SGP340 CPO-TW140W K EBR II OR FG LS-8 48	PGZ12	CE mark	-	FG	EBR	CPO-TW	140 W
13151100	SGP340 SON-T400W I FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	400 W
05951600	SGP340 SON-T70W K EBD II FG D9 48/60	E27	CE mark	-	FG	EBD	SON-T	70 W
05952300	SGP340 SON-T100W K EBD II FG D9 48/60	E40	CE mark	-	FG	EBD	SON-T	100 W
05953000	SGP340 SON-T150W K EBD II FG D9 48/60	E40	CE mark	-	FG	EBD	SON-T	150 W
05955400	SGP340 SON-T70W K EBD I FG D9 48/60	E27	CE mark	-	FG	EBD	SON-T	70 W
05956100	SGP340 SON-T100W K EBD I FG D9 48/60	E40	CE mark	-	FG	EBD	SON-T	100 W
05957800	SGP340 SON-T150W K EBD I FG D9 48/60	E40	CE mark	-	FG	EBD	SON-T	150 W
05958500	SGP340 SON-T250W K EBD I FG D9 48/60	E40	CE mark	-	FG	EBD	SON-T	250 W
06418300	SGP340 SON-T100W K I FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	100 W
06419000	SGP340 SON-T150W K I FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	150 W
06420600	SGP340 SON-T250W K I FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	250 W
63273600	SGP340 CDO-TT70W K I OR FG SKD 48/60	E27	CE mark	-	FG	CONV	CDO-TT	70 W
63275000	SGP340 CDO-TT70W K II OR FG SKD 48/60	E27	CE mark	-	FG	CONV	CDO-TT	70 W
63279800	SGP340 CDO-TT100W K II FG SKD 48/60	E40	CE mark	-	FG	CONV	CDO-TT	100 W
63281100	SGP340 CDO-TT150W K I FG SKD 48/60	E40	CE mark	-	FG	CONV	CDO-TT	150 W
63283500	SGP340 CDO-TT150W K II FG SKD 48/60	E40	CE mark	-	FG	CONV	CDO-TT	150 W
63285900	SGP340 CDO-TT250W K I FG SKD 48/60	E40	CE mark	-	FG	CONV	CDO-TT	250 W
63287300	SGP340 CDO-TT250W K II FG SKD 48/60	E40	CE mark	-	FG	CONV	CDO-TT	250 W
63572000	SGP340 SON-T50W K II FG SKD 48/60	E27	CE mark	-	FG	CONV	SON-T	50 W
12775000	SGP340 SON-T70W II FG SKD FU KC 48/60	E27	CE mark	-	FG	CONV	SON-T	70 W
63546100	SGP340 SON-T70W II FG SKD 48/60	E27	CE mark	-	FG	CONV	SON-T	70 W
12656200	SGP340 SON-T100W K II FG SKD 76	E40	CE mark	-	FG	CONV	SON-T	100 W
63557700	SGP340 SON-T100W K II FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	100 W
12777400	SGP340 SON-T150W II FG SKD FU KC 48/60	E40	CE mark	-	FG	CONV	SON-T	150 W
12773600	SGP340 SON-T150W II FG SKD KC 48/60	E40	CE mark	-	FG	CONV	SON-T	150 W
61062800	SGP340 SON-T150W K 240V I FG SKD P1 34/4	E40	CE mark	-	FG	CONV	SON-T	150 W
12695100	SGP340 SON-T150W K II FG SKD KC 48/60	E40	CE mark	-	FG	CONV	SON-T	150 W
63560700	SGP340 SON-T150W K II FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	150 W
63564500	SGP340 SON-T150W II FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	150 W
12696800	SGP340 SON-T250W K II FG SKD KC 48/60	E40	CE mark	-	FG	CONV	SON-T	250 W
12778100	SGP340 SON-T250W II FG SKD FU KC 48/60	E40	CE mark	-	FG	CONV	SON-T	250 W
63566900	SGP340 SON-T250W K II FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	250 W
63568300	SGP340 SON-T250W II FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	250 W
63570600	SGP340 SON-T250W I FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	250 W
13220400	SGP340 SON-T400W K I FG SKD 48/60	E40	CE mark	-	FG	CONV	SON-T	400 W
62615500	SGP340 CPO-TW45W K EB II OR PC 48/60	PGZ12	CE mark	-	PC	EB	CPO-TW	45 W
62617900	SGP340 CPO-TW60W K EB II OR PC 48/60	PGZ12	CE mark	-	PC	EB	CPO-TW	60 W
62619300	SGP340 CPO-TW90W K EB II OR PC 48/60	PGZ12	CE mark	-	PC	EB	CPO-TW	90 W
62621600	SGP340 CPO-TW140W K EB II OR PC 48/60	PGZ12	CE mark	-	PC	EB	CPO-TW	140 W
62623000	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/	PGZ12	CE mark	-	PC	EBR	CPO-TW	60 W
62627800	SGP340 CPO-TW140W K EBR II OR PC LS-8 48	PGZ12	CE mark	-	PC	EBR	CPO-TW	140 W
05960800	SGP340 SON-T70W K EBD II PC D9 48/60	E27	CE mark	-	PC	EBD	SON-T	70 W

Order Code	Full Product Name	Cap-Base	CE mark	Coating	Optical cover/lens type	Gear	Lamp family code	Lamp power
05961500	SGP340 SON-T100W K EBD II PC D9 48/60	E40	CE mark	-	PC	EBD	SON-T	100 W
05962200	SGP340 SON-T150W K EBD II PC D9 48/60	E40	CE mark	-	PC	EBD	SON-T	150 W
05967700	SGP340 SON-T250W K EBD I PC D9 48/60	E40	CE mark	-	PC	EBD	SON-T	250 W
63272900	SGP340 CDO-TT50W K II OR PC SKD 48/60	E27	CE mark	-	PC	CONV	CDO-TT	50 W
63276700	SGP340 CDO-TT70W K II OR PC SKD 48/60	E27	CE mark	-	PC	CONV	CDO-TT	70 W
63280400	SGP340 CDO-TT100W K II PC SKD 48/60	E40	CE mark	-	PC	CONV	CDO-TT	100 W
63284200	SGP340 CDO-TT150W K II PC SKD 48/60	E40	CE mark	-	PC	CONV	CDO-TT	150 W
12752100	SGP340 SON-T50W II PC SKD 48/60	E27	CE mark	-	PC	CONV	SON-T	50 W
63573700	SGP340 SON-T50W K II PC SKD 48/60	E27	CE mark	-	PC	CONV	SON-T	50 W
12652400	SGP340 SON-T70W K I PC SKD 48/60	E27	CE mark	-	PC	CONV	SON-T	70 W
63550800	SGP340 SON-T70W II PC SKD 48/60	E27	CE mark	-	PC	CONV	SON-T	70 W
12653100	SGP340 SON-T100W K I PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	100 W
63047300	SGP340 SON-T100W K II PC MSP SKD 48/60	E40	CE mark	Marine salt protected coating	PC	CONV	SON-T	100 W
63552200	SGP340 SON-T100W I PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	100 W
63555300	SGP340 SON-T100W II PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	100 W
12704000	SGP340 SON-T150W K 240V I PC SKD P1 34/4	E40	CE mark	-	PC	CONV	SON-T	150 W
12654800	SGP340 SON-T150W K I PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	150 W
63559100	SGP340 SON-T150W I PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	150 W
63563800	SGP340 SON-T150W II PC MSP SKD 48/60	E40	CE mark	Marine salt protected coating	PC	CONV	SON-T	150 W
13330000	SGP340 SON-T250W K I PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	250 W
63567600	SGP340 SON-T250W K II PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	250 W
63569000	SGP340 SON-T250W II PC SKD 48/60	E40	CE mark	-	PC	CONV	SON-T	250 W
12651700	SGP340 SON-T50W K I PC SKD 48/60	E27	CE mark	-	PC	CONV	SON-T	50 W
12661600	SGP340 SON-T150W II FG SKD 76	E40	CE mark	-	FG	CONV	SON-T	150 W
63571300	SGP340 SON-T400W K I FG SKD 76	E40	CE mark	-	FG	CONV	SON-T	400 W

General Information (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
12767500	SGP340 E27 II FG 48/60	Open T-POT	63281100	SGP340 CDO-TT150W K I FG SKD 48/60	Open T-POT
12768200	SGP340 E40 II FG 48/60	Open T-POT	63283500	SGP340 CDO-TT150W K II FG SKD 48/60	Open T-POT
62616200	SGP340 CPO-TW45W K EB II OR FG 48/60	Open CT-POT	63285900	SGP340 CDO-TT250W K I FG SKD 48/60	Open T-POT
62618600	SGP340 CPO-TW60W K EB II OR FG 48/60	Open CT-POT	63287300	SGP340 CDO-TT250W K II FG SKD 48/60	Open T-POT
62620900	SGP340 CPO-TW90W K EB II OR FG 48/60	Open CT-POT	63572000	SGP340 SON-T50W K II FG SKD 48/60	Open T-POT
62622300	SGP340 CPO-TW140W K EB II OR FG 48/60	Open CT-POT	12775000	SGP340 SON-T70W II FG SKD FU KC 48/60	Open T-POT
62624700	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/	Open CT-POT	63546100	SGP340 SON-T70W II FG SKD 48/60	Open T-POT
62626100	SGP340 CPO-TW90W K EBR II OR FG LS-8 48/	Open CT-POT	12656200	SGP340 SON-T100W K II FG SKD 76	Open T-POT
62628500	SGP340 CPO-TW140W K EBR II OR FG LS-8 48	Open CT-POT	63557700	SGP340 SON-T100W K II FG SKD 48/60	Open T-POT
13151100	SGP340 SON-T400W I FG SKD 48/60	Open T-POT	12777400	SGP340 SON-T150W II FG SKD FU KC 48/60	Open T-POT
05951600	SGP340 SON-T70W K EBD II FG D9 48/60	Open T-POT	12773600	SGP340 SON-T150W II FG SKD KC 48/60	Open T-POT
05952300	SGP340 SON-T100W K EBD II FG D9 48/60	Open T-POT	61062800	SGP340 SON-T150W K 240V I FG SKD P1 34/4	Open T-POT
05953000	SGP340 SON-T150W K EBD II FG D9 48/60	Open T-POT	12695100	SGP340 SON-T150W K II FG SKD KC 48/60	Open T-POT
05955400	SGP340 SON-T70W K EBD I FG D9 48/60	Open T-POT	63560700	SGP340 SON-T150W K II FG SKD 48/60	Open T-POT
05956100	SGP340 SON-T100W K EBD I FG D9 48/60	Open T-POT	63564500	SGP340 SON-T150W II FG SKD 48/60	Open T-POT
05957800	SGP340 SON-T150W K EBD I FG D9 48/60	Open T-POT	12696800	SGP340 SON-T250W K II FG SKD KC 48/60	Open T-POT
05958500	SGP340 SON-T250W K EBD I FG D9 48/60	Open T-POT	12778100	SGP340 SON-T250W II FG SKD FU KC 48/60	Open T-POT
06418300	SGP340 SON-T100W K I FG SKD 48/60	Open T-POT	63566900	SGP340 SON-T250W K II FG SKD 48/60	Open T-POT
06419000	SGP340 SON-T150W K I FG SKD 48/60	Open T-POT	63568300	SGP340 SON-T250W II FG SKD 48/60	Open T-POT
06420600	SGP340 SON-T250W K I FG SKD 48/60	Open T-POT	63570600	SGP340 SON-T250W I FG SKD 48/60	Open T-POT
63273600	SGP340 CDO-TT70W K I OR FG SKD 48/60	Open CT-POT	13220400	SGP340 SON-T400W K I FG SKD 48/60	Open T-POT
63275000	SGP340 CDO-TT70W K II OR FG SKD 48/60	Open CT-POT	62615500	SGP340 CPO-TW45W K EB II OR PC 48/60	Open CT-POT
63279800	SGP340 CDO-TT100W K II FG SKD 48/60	Open T-POT	62617900	SGP340 CPO-TW60W K EB II OR PC 48/60	Open CT-POT

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
62619300	SGP340 CPO-TW90W K EB II OR PC 48/60	Open CT-POT	63550800	SGP340 SON-T70W II PC SKD 48/60	Open T-POT
62621600	SGP340 CPO-TW140W K EB II OR PC 48/60	Open CT-POT	12653100	SGP340 SON-T100W K I PC SKD 48/60	Open T-POT
62623000	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/	Open CT-POT	63047300	SGP340 SON-T100W K II PC MSP SKD 48/60	Open T-POT
62627800	SGP340 CPO-TW140W K EBR II OR PC LS-8 48	Open CT-POT	63552200	SGP340 SON-T100W I PC SKD 48/60	Open T-POT
05960800	SGP340 SON-T70W K EBD II PC D9 48/60	Open T-POT	63555300	SGP340 SON-T100W II PC SKD 48/60	Open T-POT
05961500	SGP340 SON-T100W K EBD II PC D9 48/60	Open T-POT	12704000	SGP340 SON-T150W K 240V I PC SKD P1 34/4	Open T-POT
05962200	SGP340 SON-T150W K EBD II PC D9 48/60	Open T-POT	12654800	SGP340 SON-T150W K I PC SKD 48/60	Open T-POT
05967700	SGP340 SON-T250W K EBD I PC D9 48/60	Open T-POT	63559100	SGP340 SON-T150W I PC SKD 48/60	Open T-POT
63272900	SGP340 CDO-TT50W K II OR PC SKD 48/60	Open CT-POT	63563800	SGP340 SON-T150W II PC MSP SKD 48/60	Open T-POT
63276700	SGP340 CDO-TT70W K II OR PC SKD 48/60	Open CT-POT	13330000	SGP340 SON-T250W K I PC SKD 48/60	Open T-POT
63280400	SGP340 CDO-TT100W K II PC SKD 48/60	Open T-POT	63567600	SGP340 SON-T250W K II PC SKD 48/60	Open T-POT
63284200	SGP340 CDO-TT150W K II PC SKD 48/60	Open T-POT	63569000	SGP340 SON-T250W II PC SKD 48/60	Open T-POT
12752100	SGP340 SON-T50W II PC SKD 48/60	Open T-POT	12651700	SGP340 SON-T50W K I PC SKD 48/60	Open T-POT
63573700	SGP340 SON-T50W K II PC SKD 48/60	Open T-POT	12661600	SGP340 SON-T150W II FG SKD 76	Open T-POT
12652400	SGP340 SON-T70W K I PC SKD 48/60	Open T-POT	63571300	SGP340 SON-T400W K I FG SKD 76	Open T-POT

