




Selenium – timeless design

Selenium

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).

Benefits

- Timeless design in an efficient, ergonomic road-lighting luminaire with a simple, rounded form that reduces daytime visual impact
- Incorporates the renowned T-POT reflector for excellent optical performance
- Energy savings are possible by means of dimming with a switch, or stand-alone Chronosense system without pilot cable

Features

- Timeless design
- T-POT optic
- Dimming with switch or stand-alone Chronosense system (without pilot cable)
- Three tilt angles for optimal installation on mast or bracket

Application

- Industrial areas
- Roads
- Crossings, roundabouts

Specifications

Type	SGP340	Light source	HID:
------	--------	--------------	------

	- 1 x MASTER SON-T PIA Plus / E27 / 50, 70 W
	- 1 x MASTER SON-T PIA Plus / E40 / 100, 150, 250, 400 W
	- 1 x SON / E27 / 50, 70 W
	- 1 x SON / E40 / 100, 150, 250 W
	- 1 x SON-I / E27 / 50, 70 W
Lamp included	Yes (K) No
Mains voltage	230 or 240 V
Gear	Electro magnetic (low loss), 230 or 240 V / 50 Hz: - Inductive (IN) Electronic, 220 - 240 V / 50 - 60 Hz: - Electronic (EB)
Optic	Facetted semi closed T-POT (TP)
Optical cover	Glass flat (FG), reduce glare and improve night nuisance Polycarbonate bowl (PC) vandal-resistant
Ignitor	Series (SI) Series, self-stopping (SS) Semi-parallel (SP) Semi-parallel, self-stopping (ST)
Options	Lighting controls: Chronosense (CH) Light regulation: - Dimming switch (SW) - Dimming switch with reverse function (SWR) Photocell: NEMA socket (P1), Minicell (P3) Fuse (FU) included Knife-connector (KC) included

Materials and finishing	Canopy and frame: die-cast aluminum Mounting module: die-cast aluminum Optical covers: polycarbonate bowl or toughened glass Reflector: high-purity aluminum Closing clip: stainless steel
Color	Grey (RAL 7035) Other RAL colors available on request
Installation	Side-entry mounting: lateral entry Ø 48 / 60 mm (48/60) Post-top mounting: axial entry Ø 48 / 60 mm (48/60) Spigot is reversible for side-entry and post-top Recommended mounting height: 10 m Standard tilt angle post top: 5° Adjustable tilt angle: 0.5 and 15° Adjustable light distribution: 5 positions Max windage area: 0.14 m Max SCx values by side: 0.077 m
Maintenance	From above by opening the housing with a single quick-release clip No tools needed for geartry and disconnection of plug and socket
Accessories	Spigots for 34 mm side-entry, ZGP340 SP34S and 76 mm post-top, ZGP340 SP76P
Main applications	Industrial areas, roads, crossings, roundabouts

Versions



Selenium SGP340, svítidlo
pouličního osvětlení s plochým
sklem (FG)



Selenium SGP340, svítidlo uličního
osvětlení s polykarbonátovým
krytem (PC)



Dimensional drawing


Product
SGP340 SON-T150W K EBD II PC D9 48/60
SGP340 SON-T50/70W K II FG SUD CH 48/60
SGP340 CPO-TW45W K EB II OR FG 48/60
SGP340 SON-T100W K EBD I FG D9 48/60
SGP340 SON-T50W K FG SKD 48/60
SGP340 SON-T400W I FG SKD 48/60
SGP340 SON-T100W K EBD II FG D9 48/60
SGP340 SON-T250W K I FG SKD 48/60
SGP340 CDO-TT70W K I OR FG SKD 48/60
SGP340 SON-T100W K II FG SKD 76
SGP340 CPO-TW60W K EBD II OR FG 48/60
SGP340 SON-T70/100W K II FG SUD SW 48/60
SGP340 SON-T250W II FG SKD FU KC 48/60
SGP340 SON-T250W K II FG SKD KC 48/60
SGP340 SON-T250W II FG SKD 76
SGP340 SON-T70W K EBD II FG D9 48/60
SGP340 SON-T100W K I PC SKD 48/60
SGP340 SON-T100/150W II FG SUD CH 48/60
SGP340 SON-T250W II FG SKD 48/60
SGP340 SON-T250W K II FG SKD 48/60
SGP340 SON-T150W I PC SKD 48/60
SGP340 SON-T100W I PC SKD 48/60
SGP340 SON-T100W II PC SKD 48/60
SGP340 SON-T70W K 240V I PC SKD P1 34/42
SGP340 SON-T50W K I PC SKD 48/60
SGP340 SON-T100W II FG SKD 48/60
SGP340 CDO-TT100W K II PC SKD 48/60
SGP340 SON-T250W K II PC SKD 48/60
SGP340 SON-T250W I FG SKD 48/60
SGP340 SON-T70W II FG SKD 48/60
SGP340 SON-T400W K I FG SKD 76
SGP340 SON-T150W II FG SKD KC 48/60
SGP340 SON-T70/100W K II PC SUD CH 48/60
SGP340 SON-T250W K EBD I FG D9 48/60
SGP340 SON-T50/70W K II PC SUD CH 48/60
SGP340 SON-T150W K I PC SKD 48/60
SGP340 SON-T250W K EBD II PC D9 48/60
SGP340 CDO-TT50W K II OR PC SKD 48/60
SGP340 CPO-TW140W K EB II OR FG 48/60
SGP340 SON-T250W I PC SKD 48/60
SGP340 SON-T100W K EBD II PC D9 48/60
SGP340 SON-T100W K II FG SKD 48/60
SGP340 CPO-TW90W K EB II OR FG 48/60
SGP340 CDO-TT150W K I FG SKD 48/60
SGP340 CPO-TW60W K EBR II OR FG LS-8 48/
SGP340 SON-T70/100W II FG SUD CH 48/60
SGP340 SON-T50/70W II PC SUD 48/60
SGP340 CPO-TW60W K EB II OR PC 48/60
SGP340 SON-T150W II FG SKD 76
SGP340 SON-T70/100W K II FG SUD CH 48/60

Dimensional drawing


Product
SGP340 SON-T150W K II PC SKD 48/60
SGP340 SON-T250W II PC SKD 48/60
SGP340 CDO-TT150W K II PC SKD 48/60
SGP340 SON-T70W K I FG 48/60
SGP340 SON-T50W K II FG SKD 48/60
SGP340 SON-T250W K II FG SKD 76
SGP340 SON-T150W K 240V I FG SKD P1 34/4
SGP340 CPO-TW90W K EB II OR PC 48/60
SGP340 SON-T250W K I PC SKD 48/60
SGP340 SON-T70W II PC SKD 48/60
SGP340 SON-T50/70W II PC SUD CH 48/60
SGP340 SON-T70W K EBD I FG D9 48/60
SGP340 CDO-TT100W K II FG SKD 48/60
SGP340 SON-T70W K II PC SKD 48/60
SGP340 SON-T150W K II FG SKD 48/60
SGP340 CPO-TW60W K EBR II OR PC LS-8 48/
SGP340 E27 II FG 48/60
SGP340 SON-T150W K 240V I PC SKD P1 34/4
SGP340 SON-T150W K EBD II FG D9 48/60
SGP340 SON-T250W K EBD I PC D9 48/60
SGP340 SON-T70W K I PC SKD 48/60
SGP340 CDO-TT250W K II FG SKD 48/60
SGP340 SON-T70W K EBD II PC D9 48/60
SGP340 SON-T50/70W II FG SUD 48/60
SGP340 CDO-TT250W K I FG SKD 48/60
SGP340 SON-T250W K EBD II FG D9 48/60
SGP340 CPO-TW140W K EB II OR PC 48/60
SGP340 SON-T70/100W II PC SUD CH 48/60
SGP340 SON-T70W K II FG SKD 48/60
SGP340 CDO-TT250W K II PC SKD 48/60
SGP340 SON-T100/150W K II FG SUD CH 48/6
SGP340 CPO-TW90W K EBR II OR FG LS-8 48/
SGP340 CDO-TT70W K II OR FG SKD 48/60
SGP340 SON-T400W K I FG SKD 48/60
SGP340 SON-T150W II PC SKD 48/60
SGP340 CPO-TW45W K EB II OR PC 48/60
SGP340 SON-T70W I PC SKD 48/60
SGP340 SON-T150W K EBD I FG D9 48/60
SGP340 SON-T100/150W K II FG SUD SW 48/6
SGP340 SON-T150W II FG SKD 48/60
SGP340 SON-T150W II PC MSP SKD 48/60
SGP340 CDO-TT70W K II OR PC SKD 48/60
SGP340 SON-T100W K II PC MSP SKD 48/60
SGP340 SON-T150W K II FG SKD 76
SGP340 SON-T100/150W K II PC SUD CH 48/6
SGP340 CPO-TW140W K EBR II OR FG LS-8 48
SGP340 SON-T150W II FG SKD FU KC 48/60
SGP340 SON-T70W II FG SKD FU KC 48/60
SGP340 SON-T150W K I FG SKD 48/60
SGP340 SON-T50W K II PC SKD 48/60

Product
SGP340 CDO-TT150W K II FG SKD 48/60
SGP340 SON-T100W K II PC SKD 48/60
SGP340 SON-T100W K I FG SKD 48/60
SGP340 SON-T50W II PC SKD 48/60
SGP340 CPO-TW140W K EBR II OR PC LS-8 48
SGP340 SON-T150W K II FG SKD KC 48/60
SGP340 CPO-TW60W K EB II OR FG 48/60
SGP340 E40 II FG 48/60
SGP340 SON-T100W K EBD II FG RF 48/60

Product details



Selenium SGP340 road-lighting luminaire with flat glass



Selenium SGP340 road-lighting luminaire with polycarbonate bowl

General Information	
Number of light sources	1 pc
Product Family Code	SGP340
Light Technical	
Standard tilt angle side entry	0°
Standard tilt angle posttop	5°
Mechanical and Housing	
Color	Gray

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
910500946612	SGP340 E27 II FG 48/60	IK08
910500946712	SGP340 E40 II FG 48/60	IK08
910500967112	SGP340 CPO-TW45W K EB II OR FG 48/60	IK08
910500967312	SGP340 CPO-TW60W K EB II OR FG 48/60	IK08
910500967512	SGP340 CPO-TW90W K EB II OR FG 48/60	IK08
910500967712	SGP340 CPO-TW140W K EB II OR FG 48/60	IK08
910500967912	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/	IK08
910500968112	SGP340 CPO-TW90W K EBR II OR FG LS-8 48/	IK08
910500968312	SGP340 CPO-TW140W K EBR II OR FG LS-8 48	IK08
910925701112	SGP340 SON-T400W I FG SKD 48/60	IK08
910925719512	SGP340 SON-T70W K EBD II FG D9 48/60	IK08
910925719612	SGP340 SON-T100W K EBD II FG D9 48/60	IK08

Order Code	Full Product Name	Mech. impact protection code
910925719712	SGP340 SON-T150W K EBD II FG D9 48/60	IK08
910925719912	SGP340 SON-T70W K EBD I FG D9 48/60	IK08
910925720012	SGP340 SON-T100W K EBD I FG D9 48/60	IK08
910925720112	SGP340 SON-T150W K EBD I FG D9 48/60	IK08
910925720212	SGP340 SON-T250W K EBD I FG D9 48/60	IK08
910925723812	SGP340 SON-T250W K EBD II FG D9 48/60	IK08
910925731712	SGP340 SON-T50/70W II FG SUD 48/60	IK08
910925732112	SGP340 SON-T50/70W K II FG SUD CH 48/60	IK08
910925732512	SGP340 SON-T70/100W II FG SUD CH 48/60	IK08
910925732612	SGP340 SON-T70/100W K II FG SUD SW 48/60	IK08
910925732812	SGP340 SON-T70/100W K II FG SUD CH 48/60	IK08
910925733012	SGP340 SON-T100/150W II FG SUD CH 48/60	IK08

Order Code	Full Product Name	Mech. impact protection code
910925733312	SGP340 SON-T100/150W K II FG SUD CH 48/6	IK08
910925733412	SGP340 SON-T100/150W K II FG SUD SW 48/6	IK08
910925738712	SGP340 SON-T70W K I FG 48/60	IK08
910925738812	SGP340 SON-T100W K I FG SKD 48/60	IK08
910925738912	SGP340 SON-T150W K I FG SKD 48/60	IK08
910925739012	SGP340 SON-T250W K I FG SKD 48/60	IK08
910925739112	SGP340 SON-T50W K FG SKD 48/60	IK08
910925743012	SGP340 SON-T100W K EBD II FG RF 48/60	IK08
910925807012	SGP340 CDO-TT70W K I OR FG SKD 48/60	IK08
910925807212	SGP340 CDO-TT70W K II OR FG SKD 48/60	IK08
910925807612	SGP340 CDO-TT100W K II FG SKD 48/60	IK08
910925807812	SGP340 CDO-TT150W K I FG SKD 48/60	IK08
910925808012	SGP340 CDO-TT150W K II FG SKD 48/60	IK08
910925808212	SGP340 CDO-TT250W K I FG SKD 48/60	IK08
910925808412	SGP340 CDO-TT250W K II FG SKD 48/60	IK08
910925810412	SGP340 CPO-TW60W K EBD II OR FG 48/60	IK08
910925837312	SGP340 SON-T50W K II FG SKD 48/60	IK08
910925837612	SGP340 SON-T70W II FG SKD FU KC 48/60	IK08
910925839712	SGP340 SON-T70W II FG SKD 48/60	IK08
910925839912	SGP340 SON-T70W K II FG SKD 48/60	IK08
910925842112	SGP340 SON-T100W K II FG SKD 76	IK08
910925842512	SGP340 SON-T100W II FG SKD 48/60	IK08
910925842912	SGP340 SON-T100W K II FG SKD 48/60	IK08
910925843112	SGP340 SON-T150W II FG SKD FU KC 48/60	IK08
910925843212	SGP340 SON-T150W II FG SKD KC 48/60	IK08
910925843512	SGP340 SON-T150W K 240V I FG SKD P1 34/4	IK08
910925844612	SGP340 SON-T150W K II FG SKD KC 48/60	IK08
910925845212	SGP340 SON-T150W K II FG SKD 48/60	IK08
910925845612	SGP340 SON-T150W II FG SKD 48/60	IK08
910925847412	SGP340 SON-T250W K II FG SKD KC 48/60	IK08
910925847712	SGP340 SON-T250W II FG SKD FU KC 48/60	IK08
910925848012	SGP340 SON-T250W K II FG SKD 48/60	IK08
910925848212	SGP340 SON-T250W II FG SKD 48/60	IK08
910925848412	SGP340 SON-T250W I FG SKD 48/60	IK08
910925848512	SGP340 SON-T400W K I FG SKD 48/60	IK08
910500967012	SGP340 CPO-TW45W K EB II OR PC 48/60	IK10
910500967212	SGP340 CPO-TW60W K EB II OR PC 48/60	IK10
910500967412	SGP340 CPO-TW90W K EB II OR PC 48/60	IK10
910500967612	SGP340 CPO-TW140W K EB II OR PC 48/60	IK10
910500967812	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/	IK10
910500968212	SGP340 CPO-TW140W K EBR II OR PC LS-8 48	IK10
910925720412	SGP340 SON-T70W K EBD II PC D9 48/60	IK10
910925720512	SGP340 SON-T100W K EBD II PC D9 48/60	IK10

Order Code	Full Product Name	Mech. impact protection code
910925720612	SGP340 SON-T150W K EBD II PC D9 48/60	IK10
910925721112	SGP340 SON-T250W K EBD I PC D9 48/60	IK10
910925723712	SGP340 SON-T250W K EBD II PC D9 48/60	IK10
910925731612	SGP340 SON-T50/70W II PC SUD 48/60	IK08
910925731912	SGP340 SON-T50/70W II PC SUD CH 48/60	IK08
910925732012	SGP340 SON-T50/70W K II PC SUD CH 48/60	IK08
910925732412	SGP340 SON-T70/100W II PC SUD CH 48/60	IK08
910925732712	SGP340 SON-T70/100W K II PC SUD CH 48/60	IK08
910925733212	SGP340 SON-T100/150W K II PC SUD CH 48/6	IK08
910925806912	SGP340 CDO-TT50W K II OR PC SKD 48/60	IK08
910925807312	SGP340 CDO-TT70W K II OR PC SKD 48/60	IK08
910925807712	SGP340 CDO-TT100W K II PC SKD 48/60	IK08
910925808112	SGP340 CDO-TT150W K II PC SKD 48/60	IK08
910925808512	SGP340 CDO-TT250W K II PC SKD 48/60	IK08
910925835812	SGP340 SON-T50W II PC SKD 48/60	IK08
910925837412	SGP340 SON-T50W K II PC SKD 48/60	IK08
910925838712	SGP340 SON-T70W K 240V I PC SKD P1 34/42	IK08
910925839112	SGP340 SON-T70W K I PC SKD 48/60	IK08
910925839512	SGP340 SON-T70W K II PC SKD 48/60	IK08
910925840012	SGP340 SON-T70W I PC SKD 48/60	IK08
910925840112	SGP340 SON-T70W II PC SKD 48/60	IK08
910925841912	SGP340 SON-T100W K I PC SKD 48/60	IK08
910925842212	SGP340 SON-T100W K II PC MSP SKD 48/60	IK08
910925842312	SGP340 SON-T100W K II PC SKD 48/60	IK08
910925842412	SGP340 SON-T100W I PC SKD 48/60	IK08
910925842712	SGP340 SON-T100W II PC SKD 48/60	IK08
910925844012	SGP340 SON-T150W K 240V I PC SKD P1 34/4	IK08
910925844412	SGP340 SON-T150W K I PC SKD 48/60	IK08
910925845012	SGP340 SON-T150W K II PC SKD 48/60	IK08
910925845112	SGP340 SON-T150W I PC SKD 48/60	IK08
910925845412	SGP340 SON-T150W II PC SKD 48/60	IK08
910925845512	SGP340 SON-T150W II PC MSP SKD 48/60	IK08
910925845912	SGP340 SON-T250W I PC SKD 48/60	IK08
910925847212	SGP340 SON-T250W K I PC SKD 48/60	IK08
910925848112	SGP340 SON-T250W K II PC SKD 48/60	IK08
910925848312	SGP340 SON-T250W II PC SKD 48/60	IK08
910925848712	SGP340 SON-T50W K I PC SKD 48/60	IK08
910925700412	SGP340 SON-T150W II FG SKD 76	IK08
910925700912	SGP340 SON-T250W II FG SKD 76	IK08
910925844812	SGP340 SON-T150W K II FG SKD 76	IK08
910925847512	SGP340 SON-T250W K II FG SKD 76	IK08
910925848612	SGP340 SON-T400W K I FG SKD 76	IK08

General Information (1/2)

Order Code	Full Product Name	Cap-Base	CE mark	Coating	Optical cover/lens type	Gear	Lamp family code	Lamp power
910500946612	SGP340 E27 II FG 48/60	E27	-	-	Flat glass	E	-	-
910500946712	SGP340 E40 II FG 48/60	E40	-	-	Flat glass	E	-	-
910500967112	SGP340 CPO-TW45W K EB II OR FG 48/60	PGZ12	CE mark	-	Flat glass	EB	CPO-TW	45 W
910500967312	SGP340 CPO-TW60W K EB II OR FG 48/60	PGZ12	CE mark	-	Flat glass	EB	CPO-TW	60 W

Order Code	Full Product Name	Cap-Base	CE mark	Coating	Optical cover/lens type	Gear	Lamp family code	Lamp power
910500967512	SGP340 CPO-TW90W K EB II OR FG 48/60	PGZ12	CE mark	-	Flat glass	EB	CPO-TW	90 W
910500967712	SGP340 CPO-TW140W K EB II OR FG 48/60	PGZ12	CE mark	-	Flat glass	EB	CPO-TW	140 W
910500967912	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/	PGZ12	CE mark	-	Flat glass	EBR	CPO-TW	60 W
910500968112	SGP340 CPO-TW90W K EBR II OR FG LS-8 48/	PGZ12	CE mark	-	Flat glass	EBR	CPO-TW	90 W
910500968312	SGP340 CPO-TW140W K EBR II OR FG LS-8 48	PGZ12	CE mark	-	Flat glass	EBR	CPO-TW	140 W
910925701112	SGP340 SON-T400W I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	400 W
910925719512	SGP340 SON-T70W K EBD II FG D9 48/60	E27	CE mark	-	Flat glass	EBD	SON-T	70 W
910925719612	SGP340 SON-T100W K EBD II FG D9 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	100 W
910925719712	SGP340 SON-T150W K EBD II FG D9 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	150 W
910925719912	SGP340 SON-T70W K EBD I FG D9 48/60	E27	CE mark	-	Flat glass	EBD	SON-T	70 W
910925720012	SGP340 SON-T100W K EBD I FG D9 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	100 W
910925720112	SGP340 SON-T150W K EBD I FG D9 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	150 W
910925720212	SGP340 SON-T250W K EBD I FG D9 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	250 W
910925723812	SGP340 SON-T250W K EBD II FG D9 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	250 W
910925731712	SGP340 SON-T50/70W II FG SUD 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	50, 70 W
910925732112	SGP340 SON-T50/70W K II FG SUD CH 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	50, 70 W
910925732512	SGP340 SON-T70/100W II FG SUD CH 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	70, 100 W
910925732612	SGP340 SON-T70/100W K II FG SUD SW 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	70, 100 W
910925732812	SGP340 SON-T70/100W K II FG SUD CH 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	70, 100 W
910925733012	SGP340 SON-T100/150W II FG SUD CH 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	100, 150 W
910925733312	SGP340 SON-T100/150W K II FG SUD CH 48/6	E40	CE mark	-	Flat glass	CONV	SON-T	100, 150 W
910925733412	SGP340 SON-T100/150W K II FG SUD SW 48/6	E40	CE mark	-	Flat glass	CONV	SON-T	100, 150 W
910925738712	SGP340 SON-T70W K I FG 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	70 W
910925738812	SGP340 SON-T100W K I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	100 W
910925738912	SGP340 SON-T150W K I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925739012	SGP340 SON-T250W K I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	250 W
910925739112	SGP340 SON-T50W K FG SKD 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	50 W
910925743012	SGP340 SON-T100W K EBD II FG RF 48/60	E40	CE mark	-	Flat glass	EBD	SON-T	100 W
910925807012	SGP340 CDO-TT70W K I OR FG SKD 48/60	E27	CE mark	-	Flat glass	CONV	CDO-TT	70 W
910925807212	SGP340 CDO-TT70W K II OR FG SKD 48/60	E27	CE mark	-	Flat glass	CONV	CDO-TT	70 W
910925807612	SGP340 CDO-TT100W K II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	CDO-TT	100 W
910925807812	SGP340 CDO-TT150W K I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	CDO-TT	150 W
910925808012	SGP340 CDO-TT150W K II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	CDO-TT	150 W
910925808212	SGP340 CDO-TT250W K I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	CDO-TT	250 W
910925808412	SGP340 CDO-TT250W K II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	CDO-TT	250 W
910925810412	SGP340 CPO-TW60W K EBD II OR FG 48/60	PGZ12	CE mark	-	Flat glass	EBD	CPO-TW	60 W
910925837312	SGP340 SON-T50W K II FG SKD 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	50 W
910925837612	SGP340 SON-T70W II FG SKD FU KC 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	70 W
910925839712	SGP340 SON-T70W II FG SKD 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	70 W
910925839912	SGP340 SON-T70W K II FG SKD 48/60	E27	CE mark	-	Flat glass	CONV	SON-T	70 W
910925842112	SGP340 SON-T100W K II FG SKD 76	E40	CE mark	-	Flat glass	CONV	SON-T	100 W
910925842512	SGP340 SON-T100W II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	100 W
910925842912	SGP340 SON-T100W K II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	100 W
910925843112	SGP340 SON-T150W II FG SKD FU KC 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925843212	SGP340 SON-T150W II FG SKD KC 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925843512	SGP340 SON-T150W K 240V I FG SKD P1 34/4	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925844612	SGP340 SON-T150W K II FG SKD KC 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925845212	SGP340 SON-T150W K II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925845612	SGP340 SON-T150W II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925847412	SGP340 SON-T250W K II FG SKD KC 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	250 W
910925847712	SGP340 SON-T250W II FG SKD FU KC 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	250 W
910925848012	SGP340 SON-T250W K II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	250 W

Order Code	Full Product Name	Cap-Base	CE mark	Coating	Optical cover/lens type	Gear	Lamp family code	Lamp power
910925848212	SGP340 SON-T250W II FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	250 W
910925848412	SGP340 SON-T250W I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	250 W
910925848512	SGP340 SON-T400W K I FG SKD 48/60	E40	CE mark	-	Flat glass	CONV	SON-T	400 W
910500967012	SGP340 CPO-TW45W K EB II OR PC 48/60	PGZ12	CE mark	-	Polycarbonate bowl/cover	EB	CPO-TW	45 W
910500967212	SGP340 CPO-TW60W K EB II OR PC 48/60	PGZ12	CE mark	-	Polycarbonate bowl/cover	EB	CPO-TW	60 W
910500967412	SGP340 CPO-TW90W K EB II OR PC 48/60	PGZ12	CE mark	-	Polycarbonate bowl/cover	EB	CPO-TW	90 W
910500967612	SGP340 CPO-TW140W K EB II OR PC 48/60	PGZ12	CE mark	-	Polycarbonate bowl/cover	EB	CPO-TW	140 W
910500967812	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/	PGZ12	CE mark	-	Polycarbonate bowl/cover	EBR	CPO-TW	60 W
910500968212	SGP340 CPO-TW140W K EBR II OR PC LS-8 48	PGZ12	CE mark	-	Polycarbonate bowl/cover	EBR	CPO-TW	140 W
910925720412	SGP340 SON-T70W K EBD II PC D9 48/60	E27	CE mark	-	Polycarbonate bowl/cover	EBD	SON-T	70 W
910925720512	SGP340 SON-T100W K EBD II PC D9 48/60	E40	CE mark	-	Polycarbonate bowl/cover	EBD	SON-T	100 W
910925720612	SGP340 SON-T150W K EBD II PC D9 48/60	E40	CE mark	-	Polycarbonate bowl/cover	EBD	SON-T	150 W
910925721112	SGP340 SON-T250W K EBD I PC D9 48/60	E40	CE mark	-	Polycarbonate bowl/cover	EBD	SON-T	250 W
910925723712	SGP340 SON-T250W K EBD II PC D9 48/60	E40	CE mark	-	Polycarbonate bowl/cover	EBD	SON-T	250 W
910925731612	SGP340 SON-T50/70W II PC SUD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	50, 70 W
910925731912	SGP340 SON-T50/70W II PC SUD CH 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	50, 70 W
910925732012	SGP340 SON-T50/70W K II PC SUD CH 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	50, 70 W
910925732412	SGP340 SON-T70/100W II PC SUD CH 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70, 100 W
910925732712	SGP340 SON-T70/100W K II PC SUD CH 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70, 100 W
910925733212	SGP340 SON-T100/150W K II PC SUD CH 48/6	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	100, 150 W
910925806912	SGP340 CDO-TT50W K II OR PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	CDO-TT	50 W
910925807312	SGP340 CDO-TT70W K II OR PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	CDO-TT	70 W
910925807712	SGP340 CDO-TT100W K II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	CDO-TT	100 W
910925808112	SGP340 CDO-TT150W K II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	CDO-TT	150 W
910925808512	SGP340 CDO-TT250W K II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	CDO-TT	250 W
910925835812	SGP340 SON-T50W II PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	50 W
910925837412	SGP340 SON-T50W K II PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	50 W
910925838712	SGP340 SON-T70W K 240V I PC SKD P1 34/42	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70 W
910925839112	SGP340 SON-T70W K I PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70 W
910925839512	SGP340 SON-T70W K II PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70 W
910925840012	SGP340 SON-T70W I PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70 W
910925840112	SGP340 SON-T70W II PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	70 W
910925841912	SGP340 SON-T100W K I PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	100 W
910925842212	SGP340 SON-T100W K II PC MSP SKD 48/60	E40	CE mark	Marine salt protected coating	Polycarbonate bowl/cover	CONV	SON-T	100 W
910925842312	SGP340 SON-T100W K II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	100 W
910925842412	SGP340 SON-T100W I PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	100 W
910925842712	SGP340 SON-T100W II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	100 W
910925844012	SGP340 SON-T150W K 240V I PC SKD P1 34/4	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	150 W
910925844412	SGP340 SON-T150W K I PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	150 W
910925845012	SGP340 SON-T150W K II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	150 W
910925845112	SGP340 SON-T150W I PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	150 W
910925845412	SGP340 SON-T150W II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	150 W
910925845512	SGP340 SON-T150W II PC MSP SKD 48/60	E40	CE mark	Marine salt protected coating	Polycarbonate bowl/cover	CONV	SON-T	150 W
910925845912	SGP340 SON-T250W I PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	250 W
910925847212	SGP340 SON-T250W K I PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	250 W
910925848112	SGP340 SON-T250W K II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	250 W
910925848312	SGP340 SON-T250W II PC SKD 48/60	E40	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	250 W
910925848712	SGP340 SON-T50W K I PC SKD 48/60	E27	CE mark	-	Polycarbonate bowl/cover	CONV	SON-T	50 W
910925700412	SGP340 SON-T150W II FG SKD 76	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925700912	SGP340 SON-T250W II FG SKD 76	E40	CE mark	-	Flat glass	CONV	SON-T	250 W

Order Code	Full Product Name	Cap-Base	CE mark	Coating	Optical cover/lens type	Gear	Lamp family code	Lamp power
910925844812	SGP340 SON-T150W K II FG SKD 76	E40	CE mark	-	Flat glass	CONV	SON-T	150 W
910925847512	SGP340 SON-T250W K II FG SKD 76	E40	CE mark	-	Flat glass	CONV	SON-T	250 W
910925848612	SGP340 SON-T400W K I FG SKD 76	E40	CE mark	-	Flat glass	CONV	SON-T	400 W

General Information (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
910500946612	SGP340 E27 II FG 48/60	Open T-POT	910925842512	SGP340 SON-T100W II FG SKD 48/60	Open T-POT
910500946712	SGP340 E40 II FG 48/60	Open T-POT	910925842912	SGP340 SON-T100W K II FG SKD 48/60	Open T-POT
910500967112	SGP340 CPO-TW45W K EB II OR FG 48/60	Open CT-POT	910925843112	SGP340 SON-T150W II FG SKD FU KC 48/60	Open T-POT
910500967312	SGP340 CPO-TW60W K EB II OR FG 48/60	Open CT-POT	910925843212	SGP340 SON-T150W II FG SKD KC 48/60	Open T-POT
910500967512	SGP340 CPO-TW90W K EB II OR FG 48/60	Open CT-POT	910925843512	SGP340 SON-T150W K 240V I FG SKD P1 34/4	Open T-POT
910500967712	SGP340 CPO-TW140W K EB II OR FG 48/60	Open CT-POT	910925844612	SGP340 SON-T150W K II FG SKD KC 48/60	Open T-POT
910500967912	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/	Open CT-POT	910925845212	SGP340 SON-T150W K II FG SKD 48/60	Open T-POT
910500968112	SGP340 CPO-TW90W K EBR II OR FG LS-8 48/	Open CT-POT	910925845612	SGP340 SON-T150W II FG SKD 48/60	Open T-POT
910500968312	SGP340 CPO-TW140W K EBR II OR FG LS-8 48	Open CT-POT	910925847412	SGP340 SON-T250W K II FG SKD KC 48/60	Open T-POT
910925701112	SGP340 SON-T400W I FG SKD 48/60	Open T-POT	910925847712	SGP340 SON-T250W II FG SKD FU KC 48/60	Open T-POT
910925719512	SGP340 SON-T70W K EBD II FG D9 48/60	Open T-POT	910925848012	SGP340 SON-T250W K II FG SKD 48/60	Open T-POT
910925719612	SGP340 SON-T100W K EBD II FG D9 48/60	Open T-POT	910925848212	SGP340 SON-T250W II FG SKD 48/60	Open T-POT
910925719712	SGP340 SON-T150W K EBD II FG D9 48/60	Open T-POT	910925848412	SGP340 SON-T250W I FG SKD 48/60	Open T-POT
910925719912	SGP340 SON-T70W K EBD I FG D9 48/60	Open T-POT	910925848512	SGP340 SON-T400W K I FG SKD 48/60	Open T-POT
910925720012	SGP340 SON-T100W K EBD I FG D9 48/60	Open T-POT	910500967012	SGP340 CPO-TW45W K EB II OR PC 48/60	Open CT-POT
910925720112	SGP340 SON-T150W K EBD I FG D9 48/60	Open T-POT	910500967212	SGP340 CPO-TW60W K EB II OR PC 48/60	Open CT-POT
910925720212	SGP340 SON-T250W K EBD I FG D9 48/60	Open T-POT	910500967412	SGP340 CPO-TW90W K EB II OR PC 48/60	Open CT-POT
910925723812	SGP340 SON-T250W K EBD II FG D9 48/60	Open T-POT	910500967612	SGP340 CPO-TW140W K EB II OR PC 48/60	Open CT-POT
910925731712	SGP340 SON-T50/70W II FG SUD 48/60	Open T-POT	910500967812	SGP340 CPO-TW60W K EBR II OR PC LS-8 48/	Open CT-POT
910925732112	SGP340 SON-T50/70W K II FG SUD CH 48/60	Open T-POT	910500968212	SGP340 CPO-TW140W K EBR II OR PC LS-8 48	Open CT-POT
910925732512	SGP340 SON-T70/100W II FG SUD CH 48/60	Open T-POT	910925720412	SGP340 SON-T70W K EBD II PC D9 48/60	Open T-POT
910925732612	SGP340 SON-T70/100W K II FG SUD SW 48/60	Open T-POT	910925720512	SGP340 SON-T100W K EBD II PC D9 48/60	Open T-POT
910925732812	SGP340 SON-T70/100W K II FG SUD CH 48/60	Open T-POT	910925720612	SGP340 SON-T150W K EBD II PC D9 48/60	Open T-POT
910925733012	SGP340 SON-T100/150W II FG SUD CH 48/60	Open T-POT	910925721112	SGP340 SON-T250W K EBD I PC D9 48/60	Open T-POT
910925733312	SGP340 SON-T100/150W K II FG SUD CH 48/6	Open T-POT	910925723712	SGP340 SON-T250W K EBD II PC D9 48/60	Open T-POT
910925733412	SGP340 SON-T100/150W K II FG SUD SW 48/6	Open T-POT	910925731612	SGP340 SON-T50/70W II PC SUD 48/60	Open T-POT
910925738712	SGP340 SON-T70W K I FG 48/60	Open T-POT	910925731912	SGP340 SON-T50/70W II PC SUD CH 48/60	Open T-POT
910925738812	SGP340 SON-T100W K I FG SKD 48/60	Open T-POT	910925732012	SGP340 SON-T50/70W K II PC SUD CH 48/60	Open T-POT
910925738912	SGP340 SON-T150W K I FG SKD 48/60	Open T-POT	910925732412	SGP340 SON-T70/100W II PC SUD CH 48/60	Open T-POT
910925739012	SGP340 SON-T250W K I FG SKD 48/60	Open T-POT	910925732712	SGP340 SON-T70/100W K II PC SUD CH 48/60	Open T-POT
910925739112	SGP340 SON-T50W K FG SKD 48/60	Open T-POT	910925733212	SGP340 SON-T100/150W K II PC SUD CH 48/6	Open T-POT
910925743012	SGP340 SON-T100W K EBD II FG RF 48/60	Open T-POT	910925806912	SGP340 CDO-TT50W K II OR PC SKD 48/60	Open CT-POT
910925807012	SGP340 CDO-TT70W K I OR FG SKD 48/60	Open CT-POT	910925807312	SGP340 CDO-TT70W K II OR PC SKD 48/60	Open CT-POT
910925807212	SGP340 CDO-TT70W K II OR FG SKD 48/60	Open CT-POT	910925807712	SGP340 CDO-TT100W K II PC SKD 48/60	Open T-POT
910925807612	SGP340 CDO-TT100W K II FG SKD 48/60	Open T-POT	910925808112	SGP340 CDO-TT150W K II PC SKD 48/60	Open T-POT
910925807812	SGP340 CDO-TT150W K I FG SKD 48/60	Open T-POT	910925808512	SGP340 CDO-TT250W K II PC SKD 48/60	Open T-POT
910925808012	SGP340 CDO-TT150W K II FG SKD 48/60	Open T-POT	910925835812	SGP340 SON-T50W II PC SKD 48/60	Open T-POT
910925808212	SGP340 CDO-TT250W K I FG SKD 48/60	Open T-POT	910925837412	SGP340 SON-T50W K II PC SKD 48/60	Open T-POT
910925808412	SGP340 CDO-TT250W K II FG SKD 48/60	Open T-POT	910925838712	SGP340 SON-T70W K 240V I PC SKD P1 34/42	Open T-POT
910925810412	SGP340 CPO-TW60W K EBD II OR FG 48/60	Open CT-POT	910925839112	SGP340 SON-T70W K I PC SKD 48/60	Open T-POT
910925837312	SGP340 SON-T50W K II FG SKD 48/60	Open T-POT	910925839512	SGP340 SON-T70W K II PC SKD 48/60	Open T-POT
910925837612	SGP340 SON-T70W II FG SKD FU KC 48/60	Open T-POT	910925840012	SGP340 SON-T70W I PC SKD 48/60	Open T-POT
910925839712	SGP340 SON-T70W II FG SKD 48/60	Open T-POT	910925840112	SGP340 SON-T70W II PC SKD 48/60	Open T-POT
910925839912	SGP340 SON-T70W K II FG SKD 48/60	Open T-POT	910925841912	SGP340 SON-T100W K I PC SKD 48/60	Open T-POT
910925842112	SGP340 SON-T100W K II FG SKD 76	Open T-POT	910925842212	SGP340 SON-T100W K II PC MSP SKD 48/60	Open T-POT

Order Code	Full Product Name	Optic type
910925842312	SGP340 SON-T100W K II PC SKD 48/60	Open T-POT
910925842412	SGP340 SON-T100W I PC SKD 48/60	Open T-POT
910925842712	SGP340 SON-T100W II PC SKD 48/60	Open T-POT
910925844012	SGP340 SON-T150W K 240V I PC SKD P1 34/4	Open T-POT
910925844412	SGP340 SON-T150W K I PC SKD 48/60	Open T-POT
910925845012	SGP340 SON-T150W K II PC SKD 48/60	Open T-POT
910925845112	SGP340 SON-T150W I PC SKD 48/60	Open T-POT
910925845412	SGP340 SON-T150W II PC SKD 48/60	Open T-POT
910925845512	SGP340 SON-T150W II PC MSP SKD 48/60	Open T-POT
910925845912	SGP340 SON-T250W I PC SKD 48/60	Open T-POT

Order Code	Full Product Name	Optic type
910925847212	SGP340 SON-T250W K I PC SKD 48/60	Open T-POT
910925848112	SGP340 SON-T250W K II PC SKD 48/60	Open T-POT
910925848312	SGP340 SON-T250W II PC SKD 48/60	Open T-POT
910925848712	SGP340 SON-T50W K I PC SKD 48/60	Open T-POT
910925700412	SGP340 SON-T150W II FG SKD 76	Open T-POT
910925700912	SGP340 SON-T250W II FG SKD 76	Open T-POT
910925844812	SGP340 SON-T150W K II FG SKD 76	Open T-POT
910925847512	SGP340 SON-T250W K II FG SKD 76	Open T-POT
910925848612	SGP340 SON-T400W K I FG SKD 76	Open T-POT

