



SGP398

SGP398

SGP398 is the first luminaire in its class to bring together beauty and lighting efficiency, and harmoniously combines elegance as well as photometric performance. The SGP398 range of luminaires is suitable for lamps up to SON-T 400W. It is equipped with an adjustable lamp holder so that lamp position can be adjusted to different light distribution for flexible application.

Features

- Strong and distinctive visual character, with a fluid and rounded form
- Smooth side-entry mounting, ensuring visual consistency between the luminaire and the bracket
- Standard color in metallic grey, other RAL colors available on request IP66 protection for optical system, guaranteeing long-lasting optical performance; IP43 for gear tray
- Easy maintenance from above, tool-free lamp replacement
- Optics: well accepted T-pot reflector for SON-T lamps
- Adjustable lamp holders, ensuring maximum flexibility for optical performance
- Choice of optic covers:
 - Glass bowl to reduce light pollution
 - Flat glass for minimum glare
- Energy saving option with step dimming gear system up to SON-T 400W lamps (GB). All parts can be recycled separately.

Application

- Major roads
- Motorways
- Expressways

SGP398

Dimensional drawing

SGP398

