



Malaga – contemporary style

Malaga SGS102

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

Benefícios

- Versatile road lighting luminaire offering modern styling and quality lighting for safe, comfortable driving and for area illumination
- Optical system delivers good beam control and light output, with optimal illuminance and good uniformity
- Designed for low investment and maintenance costs

Características

- Estilo moderno
- Controlo de feixe eficaz e distribuição de luz uniforme
- Adequado para montagem no topo do poste e na entrada lateral; braço de montagem em parede também disponível

Aplicação

- Áreas residenciais
- Rodoviária
- Parques de estacionamento
- Indústria


Especificações

Malaga SGS102


Type	SGS102 (versão grande)
Light source	HID: - 1 x MASTER SON-T PIA Plus / E40 / 100, 150, 250 W - 1 x SON-T / E40 / 100, 150, 250 W - 1 x HPL-N / E40 / 250 W
Lamp included	Yes (K) No
Gear	Electro magnetic (low loss, 230 or 240 V / 50 Hz: - Inductive (IN)
Mains voltage	230 or 240 V
Optic	3 parts optic of high finish stucco aluminum
Ignitor	Series (SI) Semi-parallel (SP) Semi-parallel, self-stopping (ST)
Options	Photocell: NEMA socket (P1)
Materials and finishing	Canopy: glass-fiber-reinforced polypropylene, UV-stabilized Optical cover: polycarbonate Mounting module: die-cast aluminum, non-corrosive Gear carrier: glass-fiber-reinforced polycarbonate

Color	Grey, RAL 7035 Opção de cinza claro, laranja vivo, vermelho ou azul para o compartimento
Installation	Side-entry mounting: lateral entry Ø 42 / 60 mm Post-top mounting: axial entry Ø 42 / 60 mm Spigot is reversible for side-entry and post-top mounting Recommended mounting height: 10 m Standard tilt angle post-top: 15° Adjustable tilt angle: n/a Adjustable light distribution: n/a Max windage area: 0,15 m Max SCx values by side: 0,06 m
Maintenance	Hinged bowl with quick-release clips and easily removable gear tray
Accessories	Spigots for 34 - 42 mm side-entry and 76 mm post-top Wall-mounting bracket
Main applications	Residential areas, roads, car parks, industry

Detalhes do produto



Malaga SGS102 road-lighting luminaire with flat glass, post-top mounting



Malaga SGS102 road-lighting luminaire with flat glass, side-entry mounting

Aprovação e aplicação

Código de proteção mecânica contra impactos	IK08
---	------

Informações gerais

Casquilho	E40
Marca CE	CE
Tipo de acessório de lente/difusor ótico	PC
Equipamento	CONV
Código da família das lâmpadas	SON-T
Número de fontes de luz	1
Tipo de ótica	Refletor móvel com parafuso Allen
Código da família de produtos	SGS102

Dados técnicos de luminosidade

Ângulo de inclinação standard na entrada lateral	15°
Ângulo de inclinação standard no topo da coluna	15°

Dados mecânicos e de revestimento

Cor	GR
-----	----

Informações gerais

Order Code	Full Product Name	Potência da lâmpada
63462400	SGS102 SON-T100W II MR-AS SKD 42/60	100 W
27102600	SGS102 SON-T150W II MR-AS SKD 42/60	150 W
63467900	SGS102 SON-T250W II MR-AS SKD 42/60	250 W

