



# CoreLine Surface-mounted – the clear choice for LED

## CoreLine Surface-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Surface-mounted range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Benefits

- Enables a simple switch from basic conventional luminaires to LED luminaires
- Energy saving of up to 45% compared to functional TL-D luminaires
- Slim design with a height of less than 40 mm

### Features

- Integrated LED technology
- Slim housing
- Suspension set available as an accessory
- Recessed version also available for use in grid ceilings

### Application

- General lighting

### Specifications

Type	SM120V	Luminous flux	LED37S version: 3700 lm
Light source	LED module		LED27S version: 2700 lm
Power	LED37S version: 40.5 W	Correlated Color	3000 K
	LED27S version: 24.5 W	Temperature	4000 K

## CoreLine Surface-mounted

Color Rendering Index	≥ 80
Lumen maintenance at median useful life*	L75 50000 h
Control gear failure rate at median useful life	5% 50000 h
Performance Ambient Temperature Tq	+25 °C
Operating temperature range	+10 to +40°C
Driver	Built-in

Mains voltage	220-240 V / 50-60 Hz
Dimming	DALI
Material	Housing: pre-painted steel
Color	White
Optical cover	VAR-PC PC-LIN-SAT
Connection	With pull relief
Installation	Individual; clicking the luminaire into pre-screwed ceiling brackets
Accessories	Suspension set, SM120Z
Options	Emergency lighting 3 hours duration

### Versions



Coreline Surface



Coreline Surface

### Product details



CoreLine\_Surface\_mounted-SM134V\_suspended\_W60L60-DPP.tif



CoreLine\_Surface\_mounted-SM134V\_W60L60-DPP.tif



CoreLine\_Surface\_mounted-SM134V\_suspended\_W20L120-DPP.tif



CoreLine\_Surface\_mounted-SM134V\_W20L120-DPP.tif

# CoreLine Surface-mounted

## Accessories



Suspension set

Ordercode 910925864854,  
910925864856



Coreline Surface Acc.

Ordercode 34896000

### Application Conditions

Ambient temperature range	+10 to +40 °C
Suitable for random switching	Yes (relates to presence/movement detection and daylight harvesting)

### Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

### General Information

CE mark	CE mark
Protection class IEC	Safety class I (I)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	F
Glow-wire test	850/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
Product Family Code	SM134V

### Initial Performance (IEC Compliant)

Init. Color Rendering Index	≥80
Luminous flux tolerance	+/-8%

### Mechanical and Housing

Color	White
-------	-------

### Application Conditions

Order Code	Full Product Name	Maximum dim level
34851900	SM134V LED37S/830 PSU W60L60 NOC	Not applicable
34852600	SM134V LED27S/830 PSU W60L60 NOC	Not applicable
34855700	SM134V LED37S/840 PSD W60L60 NOC	1%
34857100	SM134V LED37S/830 PSD W60L60 NOC	1%
34858800	SM134V LED27S/830 PSD W60L60 NOC	1%
34861800	SM134V LED37S/840 PSD W60L60 OC	1%
34862500	SM134V LED27S/840 PSD W60L60 OC	1%
34865600	SM134V LED37S/830 PSD W60L60 OC	1%
34866300	SM134V LED27S/830 PSD W60L60 OC	1%
34869400	SM134V LED37S/840 PSU W60L60 NOC	Not applicable
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	Not applicable
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	1% (no dimming in emergency mode)
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	1% (no dimming in emergency mode)
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	1% (no dimming in emergency mode)
34875500	SM134V LED27S/840 PSU W60L60 NOC	Not applicable
34877900	SM134V LED27S/840 PSD W60L60 NOC	1%
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	Not applicable
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	1% (no dimming in emergency mode)
34881600	SM134V LED37S/840 PSU W60L60 OC	Not applicable
34883000	SM134V LED37S/830 PSU W60L60 OC	Not applicable
99665200	SM134V LED37S/840 W60L60 IA1 NOC	1%
99667600	SM134V LED37S/840 W60L60 IA1 OC	1%
99668300	SM134V LED37S/830 W60L60 IA1 NOC	1%
99669000	SM134V LED37S/830 W60L60 IA1 OC	1%
34853300	SM134V LED37S/830 PSU W20L120 NOC	Not applicable
34854000	SM134V LED27S/830 PSU W20L120 NOC	Not applicable
34856400	SM134V LED37S/840 PSD W20L120 NOC	1%
34859500	SM134V LED37S/830 PSD W20L120 NOC	1%
34860100	SM134V LED27S/830 PSD W20L120 NOC	1%
34863200	SM134V LED37S/840 PSD W20L120 OC	1%
34864900	SM134V LED27S/840 PSD W20L120 OC	1%
34867000	SM134V LED37S/830 PSD W20L120 OC	1%
34868700	SM134V LED27S/830 PSD W20L120 OC	1%
34870000	SM134V LED37S/840 PSU W20L120 NOC	Not applicable
34876200	SM134V LED27S/840 PSU W20L120 NOC	Not applicable
34878600	SM134V LED27S/840 PSD W20L120 NOC	1%
34882300	SM134V LED37S/840 PSU W20L120 OC	Not applicable

## CoreLine Surface-mounted

Order Code	Full Product Name	Maximum dim level
34884700	SM134V LED37S/830 PSU W20L120 OC	Not applicable
34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	Not applicable
34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	Not applicable
34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	1% (no dimming in emergency mode)
34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	1% (no dimming in emergency mode)
34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	Not applicable
34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	Not applicable
34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
99662100	SM134V LED37S/840 W20L120 IA1 NOC	1%
99663800	SM134V LED37S/840 W20L120 IA1 OC	1%
99664500	SM134V LED37S/830 W20L120 IA1 NOC	1%
99666900	SM134V LED37S/830 W20L120 IA1 OC	1%

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
34851900	SM134V LED37S/830 PSU W60L60 NOC	No	34856400	SM134V LED37S/840 PSD W20L120 NOC	Yes
34852600	SM134V LED27S/830 PSU W60L60 NOC	No	34859500	SM134V LED37S/830 PSD W20L120 NOC	Yes
34855700	SM134V LED37S/840 PSD W60L60 NOC	Yes	34860100	SM134V LED27S/830 PSD W20L120 NOC	Yes
34857100	SM134V LED37S/830 PSD W60L60 NOC	Yes	34863200	SM134V LED37S/840 PSD W20L120 OC	Yes
34858800	SM134V LED27S/830 PSD W60L60 NOC	Yes	34864900	SM134V LED27S/840 PSD W20L120 OC	Yes
34861800	SM134V LED37S/840 PSD W60L60 OC	Yes	34867000	SM134V LED37S/830 PSD W20L120 OC	Yes
34862500	SM134V LED27S/840 PSD W60L60 OC	Yes	34868700	SM134V LED27S/830 PSD W20L120 OC	Yes
34865600	SM134V LED37S/830 PSD W60L60 OC	Yes	34870000	SM134V LED37S/840 PSU W20L120 NOC	No
34866300	SM134V LED27S/830 PSD W60L60 OC	Yes	34876200	SM134V LED27S/840 PSU W20L120 NOC	No
34869400	SM134V LED37S/840 PSU W60L60 NOC	No	34878600	SM134V LED27S/840 PSD W20L120 NOC	Yes
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	No	34882300	SM134V LED37S/840 PSU W20L120 OC	No
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	Yes	34884700	SM134V LED37S/830 PSU W20L120 OC	No
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	Yes	34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	No
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	Yes	34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	No
34875500	SM134V LED27S/840 PSU W60L60 NOC	No	34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	Yes
34877900	SM134V LED27S/840 PSD W60L60 NOC	Yes	34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	Yes
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	No	34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	Yes
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	Yes	34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	Yes
34881600	SM134V LED37S/840 PSU W60L60 OC	No	34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	No
34883000	SM134V LED37S/830 PSU W60L60 OC	No	34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	No
99665200	SM134V LED37S/840 W60L60 IA1 NOC	Wireless Dim	34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	Yes
99667600	SM134V LED37S/840 W60L60 IA1 OC	Wireless Dim	34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	Yes
99668300	SM134V LED37S/830 W60L60 IA1 NOC	Wireless Dim	99662100	SM134V LED37S/840 W20L120 IA1 NOC	Wireless Dim
99669000	SM134V LED37S/830 W60L60 IA1 OC	Wireless Dim	99663800	SM134V LED37S/840 W20L120 IA1 OC	Wireless Dim
34853300	SM134V LED37S/830 PSU W20L120 NOC	No	99664500	SM134V LED37S/830 W20L120 IA1 NOC	Wireless Dim
34854000	SM134V LED27S/830 PSU W20L120 NOC	No	99666900	SM134V LED37S/830 W20L120 IA1 OC	Wireless Dim

### Operating and Electrical

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
34851900	SM134V LED37S/830 PSU W60L60 NOC	220 to 240 V	34855700	SM134V LED37S/840 PSD W60L60 NOC	220 to 240 V
34852600	SM134V LED27S/830 PSU W60L60 NOC	220 to 240 V	34857100	SM134V LED37S/830 PSD W60L60 NOC	220 to 240 V

## CoreLine Surface-mounted

Order Code	Full Product Name	Input Voltage
34858800	SM134V LED27S/830 PSD W60L60 NOC	220 to 240 V
34861800	SM134V LED37S/840 PSD W60L60 OC	220 to 240 V
34862500	SM134V LED27S/840 PSD W60L60 OC	220 to 240 V
34865600	SM134V LED37S/830 PSD W60L60 OC	220 to 240 V
34866300	SM134V LED27S/830 PSD W60L60 OC	220 to 240 V
34869400	SM134V LED37S/840 PSU W60L60 NOC	220 to 240 V
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	220 to 240 V
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	220 to 240 V
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	220 to 240 V
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	220 to 240 V
34875500	SM134V LED27S/840 PSU W60L60 NOC	220 to 240 V
34877900	SM134V LED27S/840 PSD W60L60 NOC	220 to 240 V
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	220 to 240 V
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	220 to 240 V
34881600	SM134V LED37S/840 PSU W60L60 OC	220 to 240 V
34883000	SM134V LED37S/830 PSU W60L60 OC	220 to 240 V
99665200	SM134V LED37S/840 W60L60 IA1 NOC	220-240 V
99667600	SM134V LED37S/840 W60L60 IA1 OC	220-240 V
99668300	SM134V LED37S/830 W60L60 IA1 NOC	220-240 V
99669000	SM134V LED37S/830 W60L60 IA1 OC	220-240 V
34853300	SM134V LED37S/830 PSU W20L120 NOC	220 to 240 V
34854000	SM134V LED27S/830 PSU W20L120 NOC	220 to 240 V
34856400	SM134V LED37S/840 PSD W20L120 NOC	220 to 240 V
34859500	SM134V LED37S/830 PSD W20L120 NOC	220 to 240 V

Order Code	Full Product Name	Input Voltage
34860100	SM134V LED27S/830 PSD W20L120 NOC	220 to 240 V
34863200	SM134V LED37S/840 PSD W20L120 OC	220 to 240 V
34864900	SM134V LED27S/840 PSD W20L120 OC	220 to 240 V
34867000	SM134V LED37S/830 PSD W20L120 OC	220 to 240 V
34868700	SM134V LED27S/830 PSD W20L120 OC	220 to 240 V
34870000	SM134V LED37S/840 PSU W20L120 NOC	220 to 240 V
34876200	SM134V LED27S/840 PSU W20L120 NOC	220 to 240 V
34878600	SM134V LED27S/840 PSD W20L120 NOC	220 to 240 V
34882300	SM134V LED37S/840 PSU W20L120 OC	220 to 240 V
34884700	SM134V LED37S/830 PSU W20L120 OC	220 to 240 V
34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	220 to 240 V
34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	220 to 240 V
34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	220 to 240 V
34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	220 to 240 V
34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	220 to 240 V
34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	220 to 240 V
34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	220 to 240 V
34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	220 to 240 V
34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	220 to 240 V
34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	220 to 240 V
99662100	SM134V LED37S/840 W20L120 IA1 NOC	220-240 V
99663800	SM134V LED37S/840 W20L120 IA1 OC	220-240 V
99664500	SM134V LED37S/830 W20L120 IA1 NOC	220-240 V
99666900	SM134V LED37S/830 W20L120 IA1 OC	220-240 V

### Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
34851900	SM134V LED37S/830 PSU W60L60 NOC	(0.43, 0.40)	3000 K	109 lm/W	3700 lm
34852600	SM134V LED27S/830 PSU W60L60 NOC	(0.43, 0.40)	3000 K	95 lm/W	2700 lm
34855700	SM134V LED37S/840 PSD W60L60 NOC	(0.38, 0.38)	4000 K	104 lm/W	3700 lm
34857100	SM134V LED37S/830 PSD W60L60 NOC	(0.43, 0.40)	3000 K	104 lm/W	3700 lm
34858800	SM134V LED27S/830 PSD W60L60 NOC	(0.43, 0.40)	3000 K	89 lm/W	2700 lm
34861800	SM134V LED37S/840	(0.38, 0.38)	4000 K	117 lm/W	3700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
34860100	SM134V LED27S/830 PSD W20L120 NOC	(0.43, 0.40)	3000 K	109 lm/W	3700 lm
34862500	SM134V LED27S/840 PSD W60L60 OC	(0.38, 0.38)	4000 K	123 lm/W	2700 lm
34865600	SM134V LED37S/830 PSD W60L60 OC	(0.43, 0.40)	3000 K	117 lm/W	3700 lm
34866300	SM134V LED27S/830 PSD W60L60 OC	(0.43, 0.40)	3000 K	117 lm/W	2700 lm
34869400	SM134V LED37S/840 PSU W60L60 NOC	(0.38, 0.38)	4000 K	109 lm/W	3700 lm
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	(0.38, 0.38)	4000 K	97 lm/W	3700 lm

## CoreLine Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	95 lm/W	3700 lm
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	3700 lm
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	2700 lm
34875500	SM134V LED27S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	100 lm/W	2700 lm
34877900	SM134V LED27S/840 PSD W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	102 lm/W	2700 lm
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34881600	SM134V LED37S/840 PSU W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	121 lm/W	3700 lm
34883000	SM134V LED37S/830 PSU W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	107 lm/W	3700 lm
99665200	SM134V LED37S/840 W60L60 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99667600	SM134V LED37S/840 W60L60 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99668300	SM134V LED37S/830 W60L60 IA1 NOC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
99669000	SM134V LED37S/830	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	W60L60 IA1 OC				
34853300	SM134V LED37S/830 PSU W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	3700 lm
34854000	SM134V LED27S/830 PSU W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2700 lm
34856400	SM134V LED37S/840 PSD W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
34859500	SM134V LED37S/830 PSD W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	104 lm/W	3700 lm
34860100	SM134V LED27S/830 PSD W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	89 lm/W	2700 lm
34863200	SM134V LED37S/840 PSD W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	117 lm/W	3700 lm
34864900	SM134V LED27S/840 PSD W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	123 lm/W	2700 lm
34867000	SM134V LED37S/830 PSD W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	3700 lm
34868700	SM134V LED27S/830 PSD W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	2700 lm
34870000	SM134V LED37S/840 PSU W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	109 lm/W	3700 lm
34876200	SM134V LED27S/840 PSU W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	100 lm/W	2700 lm
34878600	SM134V LED27S/840 PSD W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	102 lm/W	2700 lm

## CoreLine Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
34882300	SM134V LED37S/840 PSU W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	121 lm/W	3700 lm
34884700	SM134V LED37S/830 PSU W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	107 lm/W	3700 lm
34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	97 lm/W	3700 lm
34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	2700 lm
34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	3700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	84 lm/W	2700 lm
34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	97 lm/W	3700 lm
34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	79 lm/W	2700 lm
34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	3700 lm
99662100	SM134V LED37S/840 W20L120 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99663800	SM134V LED37S/840 W20L120 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99664500	SM134V LED37S/830 W20L120 IA1 NOC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
99666900	SM134V LED37S/830 W20L120 IA1 OC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
34851900	SM134V LED37S/830 PSU W60L60 NOC	34 W
34852600	SM134V LED27S/830 PSU W60L60 NOC	28.5 W
34855700	SM134V LED37S/840 PSD W60L60 NOC	35.5 W
34857100	SM134V LED37S/830 PSD W60L60 NOC	35.5 W
34858800	SM134V LED27S/830 PSD W60L60 NOC	30.5 W
34861800	SM134V LED37S/840 PSD W60L60 OC	31.5 W
34862500	SM134V LED27S/840 PSD W60L60 OC	22 W
34865600	SM134V LED37S/830 PSD W60L60 OC	31.5 W
34866300	SM134V LED27S/830 PSD W60L60 OC	23 W
34869400	SM134V LED37S/840 PSU W60L60 NOC	34 W
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	38 W
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	39 W
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	35 W
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	25.5 W

Order Code	Full Product Name	Initial input power
34875500	SM134V LED27S/840 PSU W60L60 NOC	27 W
34877900	SM134V LED27S/840 PSD W60L60 NOC	26.5 W
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	30.5 W
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	30.5 W
34881600	SM134V LED37S/840 PSU W60L60 OC	30.5 W
34883000	SM134V LED37S/830 PSU W60L60 OC	34.5 W
99665200	SM134V LED37S/840 W60L60 IA1 NOC	35.4 W
99667600	SM134V LED37S/840 W60L60 IA1 OC	35.4 W
99668300	SM134V LED37S/830 W60L60 IA1 NOC	35.4 W
99669000	SM134V LED37S/830 W60L60 IA1 OC	35.4 W
34853300	SM134V LED37S/830 PSU W20L120 NOC	34 W
34854000	SM134V LED27S/830 PSU W20L120 NOC	28.5 W
34856400	SM134V LED37S/840 PSD W20L120 NOC	35.5 W
34859500	SM134V LED37S/830 PSD W20L120 NOC	35.5 W

## CoreLine Surface-mounted

Order Code	Full Product Name	Initial input power
34860100	SM134V LED27S/830 PSD W20L120 NOC	30.5 W
34863200	SM134V LED37S/840 PSD W20L120 OC	31.5 W
34864900	SM134V LED27S/840 PSD W20L120 OC	22 W
34867000	SM134V LED37S/830 PSD W20L120 OC	31.5 W
34868700	SM134V LED27S/830 PSD W20L120 OC	23 W
34870000	SM134V LED37S/840 PSU W20L120 NOC	34 W
34876200	SM134V LED27S/840 PSU W20L120 NOC	27 W
34878600	SM134V LED27S/840 PSD W20L120 NOC	26.5 W
34882300	SM134V LED37S/840 PSU W20L120 OC	30.5 W
34884700	SM134V LED37S/830 PSU W20L120 OC	34.5 W
34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	30.5 W
34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	38 W

Order Code	Full Product Name	Initial input power
34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	30.5 W
34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	35.5 W
34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	25.5 W
34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	35 W
34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	32 W
34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	38 W
34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	34 W
34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	39 W
99662100	SM134V LED37S/840 W20L120 IA1 NOC	35.4 W
99663800	SM134V LED37S/840 W20L120 IA1 OC	35.4 W
99664500	SM134V LED37S/830 W20L120 IA1 NOC	35.4 W
99666900	SM134V LED37S/830 W20L120 IA1 OC	35.4 W

