



# CoreLine Surface-mounted – the clear choice for LED

## CoreLine Surface-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Surface-mounted range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. Coreline Surface Mounted also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

### Benefits

- Enables a simple switch from basic conventional luminaires to LED luminaires
- Energy saving of up to 45% compared to functional TL-D luminaires
- Slim design with a height of less than 40 mm

### Features

- Integrated LED technology
- Slim housing
- Suspension set available as an accessory
- Recessed version also available for use in grid ceilings
- 3 hour Emergency version available
- Office compliant (UGR<19) flicker free and Non Office compliant versions available.

### Application

- General lighting


### Specifications

## CoreLine Surface-mounted


<b>Type</b>	SM120V
<b>Light source</b>	Non-replaceable LED module
<b>Power</b>	LED37S version: 40.5 W LED27S version: 24.5 W
<b>Luminous flux</b>	LED37S version: 3700 lm LED27S version: 2700 lm
<b>Correlated Colour Temperature</b>	4000 K
<b>Colour Rendering Index</b>	≥ 80
<b>Median useful life</b>	50,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	30,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	15,000 hours
<b>L90B50</b>	
<b>Driver failure rate</b>	1.0% per 5000 hours

<b>Average ambient temperature</b>	+25 °C
<b>Operating temperature range</b>	+10 to +40°C
<b>Driver</b>	Built-in
<b>Mains voltage</b>	220-240 V / 50-60 Hz
<b>Dimming</b>	No dimming and DALI Dimming
<b>Material</b>	Housing: pre-painted steel
<b>Colour</b>	White
<b>Optical cover</b>	Polycarbonate
<b>Connection</b>	With pull relief
<b>Installation</b>	Individual; clicking the luminaire into pre-screwed ceiling brackets
<b>Accessories</b>	Suspension set, SM120Z
<b>Options</b>	Emergency lighting 3 hours duration

### Versions




Coreline Surface




Coreline Surface

### Product details



CoreLine\_Surface\_mounted-SM134V\_suspended\_W60L60-DPP.tif




CoreLine\_Surface\_mounted-SM134V\_W60L60-DPP.tif

## CoreLine Surface-mounted

### Product details




CoreLine\_Surface\_mounted-  
SM134V\_suspended\_W20L120-  
DPP.tif




CoreLine\_Surface\_mounted-  
SM134V\_W20L120-DPP.tif

### Accessories



Suspension set  
  
Ordercode 910925864854,  
910925864856



Coreline Surface Acc.  
  
Ordercode 34896000

## CoreLine Surface-mounted

### Application Conditions

Ambient temperature range	+10 to +40 °C
Suitable for random switching	Yes

### Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

### General Information

CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	F
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
Product Family Code	SM134V

### Initial Performance (IEC Compliant)

Init. Colour Rendering Index	≥80
Luminous flux tolerance	+/-8%

### Mechanical and Housing

Colour	White
--------	-------

### Application Conditions

Order Code	Full Product Name	Maximum dim level
34851900	SM134V LED375/830 PSU W60L60 NOC	Not applicable
34852600	SM134V LED275/830 PSU W60L60 NOC	Not applicable
34855700	SM134V LED375/840 PSD W60L60 NOC	1%
34857100	SM134V LED375/830 PSD W60L60 NOC	1%
34858800	SM134V LED275/830 PSD W60L60 NOC	1%
34861800	SM134V LED375/840 PSD W60L60 OC	1%
34862500	SM134V LED275/840 PSD W60L60 OC	1%
34865600	SM134V LED375/830 PSD W60L60 OC	1%
34866300	SM134V LED275/830 PSD W60L60 OC	1%
34869400	SM134V LED375/840 PSU W60L60 NOC	Not applicable
34871700	SM134V LED375/840 PSU W60L60 ELB3 NOC	Not applicable
34872400	SM134V LED375/840 PSD W60L60 ELB3 NOC	1% (no dimming in emergency mode)
34873100	SM134V LED375/840 PSD W60L60 ELB3 OC	1% (no dimming in emergency mode)
34874800	SM134V LED275/840 PSD W60L60 ELB3 OC	1% (no dimming in emergency mode)
34875500	SM134V LED275/840 PSU W60L60 NOC	Not applicable
34877900	SM134V LED275/840 PSD W60L60 NOC	1%
34879300	SM134V LED275/840 PSU W60L60 ELB3 NOC	Not applicable
34880900	SM134V LED275/840 PSD W60L60 ELB3 NOC	1% (no dimming in emergency mode)
34881600	SM134V LED375/840 PSU W60L60 OC	Not applicable
34883000	SM134V LED375/830 PSU W60L60 OC	Not applicable
99665200	SM134V LED375/840 W60L60 IA1 NOC	1%
99667600	SM134V LED375/840 W60L60 IA1 OC	1%
99668300	SM134V LED375/830 W60L60 IA1 NOC	1%
99669000	SM134V LED375/830 W60L60 IA1 OC	1%
99672000	SM134V LED375/840 W60L60 ELB3 IA1 NOC	1%
99673700	SM134V LED375/840 W60L60 ELB3 IA1 OC	1%
34853300	SM134V LED375/830 PSU W20L120 NOC	Not applicable
34854000	SM134V LED275/830 PSU W20L120 NOC	Not applicable
34856400	SM134V LED375/840 PSD W20L120 NOC	1%
34859500	SM134V LED375/830 PSD W20L120 NOC	1%
34860100	SM134V LED275/830 PSD W20L120 NOC	1%
34863200	SM134V LED375/840 PSD W20L120 OC	1%
34864900	SM134V LED275/840 PSD W20L120 OC	1%
34867000	SM134V LED375/830 PSD W20L120 OC	1%
34868700	SM134V LED275/830 PSD W20L120 OC	1%
34870000	SM134V LED375/840 PSU W20L120 NOC	Not applicable
34876200	SM134V LED275/840 PSU W20L120 NOC	Not applicable
34878600	SM134V LED275/840 PSD W20L120 NOC	1%
34882300	SM134V LED375/840 PSU W20L120 OC	Not applicable
34884700	SM134V LED375/830 PSU W20L120 OC	Not applicable
34885400	SM134V LED275/840 PSU W20L120 ELB3 NOC	Not applicable
34886100	SM134V LED375/840 PSU W20L120 ELB3 NOC	Not applicable
34887800	SM134V LED275/840 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
34888500	SM134V LED375/840 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
34889200	SM134V LED275/840 PSD W20L120 ELB3 OC	1% (no dimming in emergency mode)
34890800	SM134V LED375/840 PSD W20L120 ELB3 OC	1% (no dimming in emergency mode)
34891500	SM134V LED275/830 PSU W20L120 ELB3 NOC	Not applicable
34892200	SM134V LED375/830 PSU W20L120 ELB3 NOC	Not applicable
34893900	SM134V LED275/830 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
34894600	SM134V LED375/830 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
99662100	SM134V LED375/840 W20L120 IA1 NOC	1%

## CoreLine Surface-mounted

Order Code	Full Product Name	Maximum dim level
99663800	SM134V LED37S/840 W20L120 IA1 OC	1%
99664500	SM134V LED37S/830 W20L120 IA1 NOC	1%
99666900	SM134V LED37S/830 W20L120 IA1 OC	1%
99670600	SM134V LED37S/840 W20L120 ELB3 IA1 OC	1%
99671300	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	1%

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
34851900	SM134V LED37S/830 PSU W60L60 NOC	No	34856400	SM134V LED37S/840 PSD W20L120 NOC	Yes
34852600	SM134V LED27S/830 PSU W60L60 NOC	No	34859500	SM134V LED37S/830 PSD W20L120 NOC	Yes
34855700	SM134V LED37S/840 PSD W60L60 NOC	Yes	34860100	SM134V LED27S/830 PSD W20L120 NOC	Yes
34857100	SM134V LED37S/830 PSD W60L60 NOC	Yes	34863200	SM134V LED37S/840 PSD W20L120 OC	Yes
34858800	SM134V LED27S/830 PSD W60L60 NOC	Yes	34864900	SM134V LED27S/840 PSD W20L120 OC	Yes
34861800	SM134V LED37S/840 PSD W60L60 OC	Yes	34867000	SM134V LED37S/830 PSD W20L120 OC	Yes
34862500	SM134V LED27S/840 PSD W60L60 OC	Yes	34868700	SM134V LED27S/830 PSD W20L120 OC	Yes
34865600	SM134V LED37S/830 PSD W60L60 OC	Yes	34870000	SM134V LED37S/840 PSU W20L120 NOC	No
34866300	SM134V LED27S/830 PSD W60L60 OC	Yes	34876200	SM134V LED27S/840 PSU W20L120 NOC	No
34869400	SM134V LED37S/840 PSU W60L60 NOC	No	34878600	SM134V LED27S/840 PSD W20L120 NOC	Yes
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	No	34882300	SM134V LED37S/840 PSU W20L120 OC	No
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	Yes	34884700	SM134V LED37S/830 PSU W20L120 OC	No
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	Yes	34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	No
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	Yes	34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	No
34875500	SM134V LED27S/840 PSU W60L60 NOC	No	34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	Yes
34877900	SM134V LED27S/840 PSD W60L60 NOC	Yes	34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	Yes
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	No	34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	Yes
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	Yes	34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	Yes
34881600	SM134V LED37S/840 PSU W60L60 OC	No	34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	No
34883000	SM134V LED37S/830 PSU W60L60 OC	No	34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	No
99665200	SM134V LED37S/840 W60L60 IA1 NOC	-	34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	Yes
99667600	SM134V LED37S/840 W60L60 IA1 OC	-	34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	Yes
99668300	SM134V LED37S/830 W60L60 IA1 NOC	-	99662100	SM134V LED37S/840 W20L120 IA1 NOC	-
99669000	SM134V LED37S/830 W60L60 IA1 OC	-	99663800	SM134V LED37S/840 W20L120 IA1 OC	-
99672000	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	-	99664500	SM134V LED37S/830 W20L120 IA1 NOC	-
99673700	SM134V LED37S/840 W60L60 ELB3 IA1 OC	-	99666900	SM134V LED37S/830 W20L120 IA1 OC	-
34853300	SM134V LED37S/830 PSU W20L120 NOC	No	99670600	SM134V LED37S/840 W20L120 ELB3 IA1 OC	-
34854000	SM134V LED27S/830 PSU W20L120 NOC	No	99671300	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	-

### Operating and Electrical

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
34851900	SM134V LED37S/830 PSU W60L60 NOC	220 to 240 V	34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	220 to 240 V
34852600	SM134V LED27S/830 PSU W60L60 NOC	220 to 240 V	34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	220 to 240 V
34855700	SM134V LED37S/840 PSD W60L60 NOC	220 to 240 V	34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	220 to 240 V
34857100	SM134V LED37S/830 PSD W60L60 NOC	220 to 240 V	34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	220 to 240 V
34858800	SM134V LED27S/830 PSD W60L60 NOC	220 to 240 V	34875500	SM134V LED27S/840 PSU W60L60 NOC	220 to 240 V
34861800	SM134V LED37S/840 PSD W60L60 OC	220 to 240 V	34877900	SM134V LED27S/840 PSD W60L60 NOC	220 to 240 V
34862500	SM134V LED27S/840 PSD W60L60 OC	220 to 240 V	34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	220 to 240 V
34865600	SM134V LED37S/830 PSD W60L60 OC	220 to 240 V	34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	220 to 240 V
34866300	SM134V LED27S/830 PSD W60L60 OC	220 to 240 V	34881600	SM134V LED37S/840 PSU W60L60 OC	220 to 240 V
34869400	SM134V LED37S/840 PSU W60L60 NOC	220 to 240 V	34883000	SM134V LED37S/830 PSU W60L60 OC	220 to 240 V

## CoreLine Surface-mounted

Order Code	Full Product Name	Input Voltage
99665200	SM134V LED375/840 W60L60 IA1 NOC	220-240 V
99667600	SM134V LED375/840 W60L60 IA1 OC	220-240 V
99668300	SM134V LED375/830 W60L60 IA1 NOC	220-240 V
99669000	SM134V LED375/830 W60L60 IA1 OC	220-240 V
99672000	SM134V LED375/840 W60L60 ELB3 IA1 NOC	220-240 V
99673700	SM134V LED375/840 W60L60 ELB3 IA1 OC	220-240 V
34853300	SM134V LED375/830 PSU W20L120 NOC	220 to 240 V
34854000	SM134V LED275/830 PSU W20L120 NOC	220 to 240 V
34856400	SM134V LED375/840 PSD W20L120 NOC	220 to 240 V
34859500	SM134V LED375/830 PSD W20L120 NOC	220 to 240 V
34860100	SM134V LED275/830 PSD W20L120 NOC	220 to 240 V
34863200	SM134V LED375/840 PSD W20L120 OC	220 to 240 V
34864900	SM134V LED275/840 PSD W20L120 OC	220 to 240 V
34867000	SM134V LED375/830 PSD W20L120 OC	220 to 240 V
34868700	SM134V LED275/830 PSD W20L120 OC	220 to 240 V
34870000	SM134V LED375/840 PSU W20L120 NOC	220 to 240 V
34876200	SM134V LED275/840 PSU W20L120 NOC	220 to 240 V
34878600	SM134V LED275/840 PSD W20L120 NOC	220 to 240 V

Order Code	Full Product Name	Input Voltage
34882300	SM134V LED375/840 PSU W20L120 OC	220 to 240 V
34884700	SM134V LED375/830 PSU W20L120 OC	220 to 240 V
34885400	SM134V LED275/840 PSU W20L120 ELB3 NOC	220 to 240 V
34886100	SM134V LED375/840 PSU W20L120 ELB3 NOC	220 to 240 V
34887800	SM134V LED275/840 PSD W20L120 ELB3 NOC	220 to 240 V
34888500	SM134V LED375/840 PSD W20L120 ELB3 NOC	220 to 240 V
34889200	SM134V LED275/840 PSD W20L120 ELB3 OC	220 to 240 V
34890800	SM134V LED375/840 PSD W20L120 ELB3 OC	220 to 240 V
34891500	SM134V LED275/830 PSU W20L120 ELB3 NOC	220 to 240 V
34892200	SM134V LED375/830 PSU W20L120 ELB3 NOC	220 to 240 V
34893900	SM134V LED275/830 PSD W20L120 ELB3 NOC	220 to 240 V
34894600	SM134V LED375/830 PSD W20L120 ELB3 NOC	220 to 240 V
99662100	SM134V LED375/840 W20L120 IA1 NOC	220-240 V
99663800	SM134V LED375/840 W20L120 IA1 OC	220-240 V
99664500	SM134V LED375/830 W20L120 IA1 NOC	220-240 V
99666900	SM134V LED375/830 W20L120 IA1 OC	220-240 V
99670600	SM134V LED375/840 W20L120 ELB3 IA1 OC	220-240 V
99671300	SM134V LED375/840 W20L120 ELB3 IA1 NOC	220-240 V

### Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
34851900	SM134V LED375/830 PSU W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	3700 lm
34852600	SM134V LED275/830 PSU W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2700 lm
34855700	SM134V LED375/840 PSD W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
34857100	SM134V LED375/830 PSD W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	104 lm/W	3700 lm
34858800	SM134V LED275/830 PSD W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	89 lm/W	2700 lm
34861800	SM134V LED375/840 PSD W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	117 lm/W	3700 lm
34862500	SM134V LED275/840 PSD W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	123 lm/W	2700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
34865600	SM134V LED375/830 PSD W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	3700 lm
34866300	SM134V LED275/830 PSD W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	2700 lm
34869400	SM134V LED375/840 PSU W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	109 lm/W	3700 lm
34871700	SM134V LED375/840 PSU W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	97 lm/W	3700 lm
34872400	SM134V LED375/840 PSD W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	95 lm/W	3700 lm
34873100	SM134V LED375/840 PSD W60L60 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	3700 lm
34874800	SM134V LED275/840 PSD W60L60 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	2700 lm

## CoreLine Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
34875500	SM134V LED27S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	100 lm/W	2700 lm
34877900	SM134V LED27S/840 PSD W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	102 lm/W	2700 lm
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34881600	SM134V LED37S/840 PSU W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	121 lm/W	3700 lm
34883000	SM134V LED37S/830 PSU W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	107 lm/W	3700 lm
99665200	SM134V LED37S/840 W60L60 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99667600	SM134V LED37S/840 W60L60 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99668300	SM134V LED37S/830 W60L60 IA1 NOC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
99669000	SM134V LED37S/830 W60L60 IA1 OC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
99672000	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm
99673700	SM134V LED37S/840 W60L60 ELB3 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm
34853300	SM134V LED37S/830	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	3700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU W20L120 NOC				
34854000	SM134V LED27S/830 PSU W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2700 lm
34856400	SM134V LED37S/840 PSD W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
34859500	SM134V LED37S/830 PSD W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	104 lm/W	3700 lm
34860100	SM134V LED27S/830 PSD W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	89 lm/W	2700 lm
34863200	SM134V LED37S/840 PSD W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	117 lm/W	3700 lm
34864900	SM134V LED27S/840 PSD W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	123 lm/W	2700 lm
34867000	SM134V LED37S/830 PSD W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	3700 lm
34868700	SM134V LED27S/830 PSD W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	2700 lm
34870000	SM134V LED37S/840 PSU W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	109 lm/W	3700 lm
34876200	SM134V LED27S/840 PSU W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	100 lm/W	2700 lm
34878600	SM134V LED27S/840 PSD W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	102 lm/W	2700 lm
34882300	SM134V LED37S/840 PSU W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	121 lm/W	3700 lm

## CoreLine Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
34884700	SM134V LED37S/830 PSU W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	107 lm/W	3700 lm
34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	97 lm/W	3700 lm
34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	2700 lm
34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	3700 lm
34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	84 lm/W	2700 lm
34892200	SM134V LED37S/830	(0.43, 0.40) SDCM <3	3000 K	97 lm/W	3700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU W20L120 ELB3 NOC				
34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	79 lm/W	2700 lm
34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	3700 lm
99662100	SM134V LED37S/840 W20L120 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99663800	SM134V LED37S/840 W20L120 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
99664500	SM134V LED37S/830 W20L120 IA1 NOC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
99666900	SM134V LED37S/830 W20L120 IA1 OC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
99670600	SM134V LED37S/840 W20L120 ELB3 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm
99671300	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
34851900	SM134V LED37S/830 PSU W60L60 NOC	34 W
34852600	SM134V LED27S/830 PSU W60L60 NOC	28.5 W
34855700	SM134V LED37S/840 PSD W60L60 NOC	35.5 W
34857100	SM134V LED37S/830 PSD W60L60 NOC	35.5 W
34858800	SM134V LED27S/830 PSD W60L60 NOC	30.5 W
34861800	SM134V LED37S/840 PSD W60L60 OC	31.5 W
34862500	SM134V LED27S/840 PSD W60L60 OC	22 W
34865600	SM134V LED37S/830 PSD W60L60 OC	31.5 W
34866300	SM134V LED27S/830 PSD W60L60 OC	23 W
34869400	SM134V LED37S/840 PSU W60L60 NOC	34 W
34871700	SM134V LED37S/840 PSU W60L60 ELB3 NOC	38 W
34872400	SM134V LED37S/840 PSD W60L60 ELB3 NOC	39 W

Order Code	Full Product Name	Initial input power
34873100	SM134V LED37S/840 PSD W60L60 ELB3 OC	35 W
34874800	SM134V LED27S/840 PSD W60L60 ELB3 OC	25.5 W
34875500	SM134V LED27S/840 PSU W60L60 NOC	27 W
34877900	SM134V LED27S/840 PSD W60L60 NOC	26.5 W
34879300	SM134V LED27S/840 PSU W60L60 ELB3 NOC	30.5 W
34880900	SM134V LED27S/840 PSD W60L60 ELB3 NOC	30.5 W
34881600	SM134V LED37S/840 PSU W60L60 OC	30.5 W
34883000	SM134V LED37S/830 PSU W60L60 OC	34.5 W
99665200	SM134V LED37S/840 W60L60 IA1 NOC	35.4 W
99667600	SM134V LED37S/840 W60L60 IA1 OC	35.4 W
99668300	SM134V LED37S/830 W60L60 IA1 NOC	35.4 W
99669000	SM134V LED37S/830 W60L60 IA1 OC	35.4 W



## CoreLine Surface-mounted

Order Code	Full Product Name	Initial input power
99672000	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	39.3 W
99673700	SM134V LED37S/840 W60L60 ELB3 IA1 OC	39.3 W
34853300	SM134V LED37S/830 PSU W20L120 NOC	34 W
34854000	SM134V LED27S/830 PSU W20L120 NOC	28.5 W
34856400	SM134V LED37S/840 PSD W20L120 NOC	35.5 W
34859500	SM134V LED37S/830 PSD W20L120 NOC	35.5 W
34860100	SM134V LED27S/830 PSD W20L120 NOC	30.5 W
34863200	SM134V LED37S/840 PSD W20L120 OC	31.5 W
34864900	SM134V LED27S/840 PSD W20L120 OC	22 W
34867000	SM134V LED37S/830 PSD W20L120 OC	31.5 W
34868700	SM134V LED27S/830 PSD W20L120 OC	23 W
34870000	SM134V LED37S/840 PSU W20L120 NOC	34 W
34876200	SM134V LED27S/840 PSU W20L120 NOC	27 W
34878600	SM134V LED27S/840 PSD W20L120 NOC	26.5 W
34882300	SM134V LED37S/840 PSU W20L120 OC	30.5 W
34884700	SM134V LED37S/830 PSU W20L120 OC	34.5 W

Order Code	Full Product Name	Initial input power
34885400	SM134V LED27S/840 PSU W20L120 ELB3 NOC	30.5 W
34886100	SM134V LED37S/840 PSU W20L120 ELB3 NOC	38 W
34887800	SM134V LED27S/840 PSD W20L120 ELB3 NOC	30.5 W
34888500	SM134V LED37S/840 PSD W20L120 ELB3 NOC	35.5 W
34889200	SM134V LED27S/840 PSD W20L120 ELB3 OC	25.5 W
34890800	SM134V LED37S/840 PSD W20L120 ELB3 OC	35 W
34891500	SM134V LED27S/830 PSU W20L120 ELB3 NOC	32 W
34892200	SM134V LED37S/830 PSU W20L120 ELB3 NOC	38 W
34893900	SM134V LED27S/830 PSD W20L120 ELB3 NOC	34 W
34894600	SM134V LED37S/830 PSD W20L120 ELB3 NOC	39 W
99662100	SM134V LED37S/840 W20L120 IA1 NOC	35.4 W
99663800	SM134V LED37S/840 W20L120 IA1 OC	35.4 W
99664500	SM134V LED37S/830 W20L120 IA1 NOC	35.4 W
99666900	SM134V LED37S/830 W20L120 IA1 OC	35.4 W
99670600	SM134V LED37S/840 W20L120 ELB3 IA1 OC	39.3 W
99671300	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	39.3 W

