



CoreLine Surface-mounted – the clear choice for LED

CoreLine Surface-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Surface-mounted range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. InterAct Ready luminaires with integrated wireless communications in this family available, to be used with InterAct gateways, sensors and software.

Benefits

- Enables a simple switch from basic conventional luminaires to LED luminaires
- Energy saving of up to 45% compared to functional TL-D luminaires
- Slim design with a height of less than 40 mm

Features

- Integrated LED technology
- Slim housing
- Suspension set available as an accessory
- Recessed version also available for use in grid ceilings

Application

- General lighting

Specifications

Type	SM120V
Light source	LED module

Power	LED37S version: 40.5 W
	LED27S version: 24.5 W

CoreLine Surface-mounted

Luminous flux	LED37S version: 3700 lm
	LED27S version: 2700 lm
Correlated Color	3000 K
Temperature	4000 K
Color Rendering Index	≥ 80
Lumen maintenance at median useful life*	L75
50000 h	
Control gear failure rate at median useful life	5%
50000 h	
Performance Ambient Temperature Tq	+25 °C
Operating temperature range	+10 to +40°C

Driver	Built-in
Mains voltage	220-240 V / 50-60 Hz
Dimming	DALI
Material	Housing: pre-painted steel
Color	White
Optical cover	VAR-PC
	PC-LIN-SAT
Connection	With pull relief
Installation	Individual; clicking the luminaire into pre-screwed ceiling brackets
Accessories	Suspension set, SM120Z
Options	Emergency lighting 3 hours duration

Versions



Coreline Surface



Coreline Surface

Product details



CoreLine_Surface_mounted-SM134V_suspended_W60L60-DPP.tif



CoreLine_Surface_mounted-SM134V_W60L60-DPP.tif

CoreLine Surface-mounted

Product details



CoreLine_Surface_mounted-
SM134V_suspended_W20L120-
DPP.tif



CoreLine_Surface_mounted-
SM134V_W20L120-DPP.tif

Accessories



Suspension set

Ordercode 910925864854,
910925864856



Coreline Surface Acc.

Ordercode 910925864855

CoreLine Surface-mounted

Application Conditions

Ambient temperature range	+10 to +40 °C
Suitable for random switching	Yes

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

General Information

CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	Wide beam
Product Family Code	SM134V

Initial Performance (IEC Compliant)

Init. Color Rendering Index	≥80
Luminous flux tolerance	+/-8%

Mechanical and Housing

Color	White
-------	-------

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925864810	SM134V LED37S/830 PSU W60L60 NOC	Not applicable
910925864811	SM134V LED27S/830 PSU W60L60 NOC	Not applicable
910925864814	SM134V LED37S/840 PSD W60L60 NOC	1%
910925864816	SM134V LED37S/830 PSD W60L60 NOC	1%
910925864817	SM134V LED27S/830 PSD W60L60 NOC	1%
910925864820	SM134V LED37S/840 PSD W60L60 OC	1%
910925864821	SM134V LED27S/840 PSD W60L60 OC	1%
910925864824	SM134V LED37S/830 PSD W60L60 OC	1%
910925864825	SM134V LED27S/830 PSD W60L60 OC	1%
910925864828	SM134V LED37S/840 PSU W60L60 NOC	Not applicable
910925864830	SM134V LED37S/840 PSU W60L60 ELB3 NOC	Not applicable
910925864831	SM134V LED37S/840 PSD W60L60 ELB3 NOC	1% (no dimming in emergency mode)
910925864832	SM134V LED37S/840 PSD W60L60 ELB3 OC	1% (no dimming in emergency mode)
910925864833	SM134V LED27S/840 PSD W60L60 ELB3 OC	1% (no dimming in emergency mode)
910925864834	SM134V LED27S/840 PSU W60L60 NOC	Not applicable
910925864836	SM134V LED27S/840 PSD W60L60 NOC	1%
910925864838	SM134V LED27S/840 PSU W60L60 ELB3 NOC	Not applicable
910925864839	SM134V LED27S/840 PSD W60L60 ELB3 NOC	1% (no dimming in emergency mode)
910925864840	SM134V LED37S/840 PSU W60L60 OC	Not applicable
910925864842	SM134V LED37S/830 PSU W60L60 OC	Not applicable
910925865186	SM134V LED37S/840 W60L60 IA1 NOC	1%
910925865188	SM134V LED37S/840 W60L60 IA1 OC	1%
910925865189	SM134V LED37S/830 W60L60 IA1 NOC	1%
910925865190	SM134V LED37S/830 W60L60 IA1 OC	1%
910925865193	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	1%
910925865194	SM134V LED37S/840 W60L60 ELB3 IA1 OC	1%
910925864812	SM134V LED37S/830 PSU W20L120 NOC	Not applicable
910925864813	SM134V LED27S/830 PSU W20L120 NOC	Not applicable
910925864815	SM134V LED37S/840 PSD W20L120 NOC	1%
910925864818	SM134V LED37S/830 PSD W20L120 NOC	1%
910925864819	SM134V LED27S/830 PSD W20L120 NOC	1%
910925864822	SM134V LED37S/840 PSD W20L120 OC	1%
910925864823	SM134V LED27S/840 PSD W20L120 OC	1%
910925864826	SM134V LED37S/830 PSD W20L120 OC	1%
910925864827	SM134V LED27S/830 PSD W20L120 OC	1%
910925864829	SM134V LED37S/840 PSU W20L120 NOC	Not applicable
910925864835	SM134V LED27S/840 PSU W20L120 NOC	Not applicable
910925864837	SM134V LED27S/840 PSD W20L120 NOC	1%
910925864841	SM134V LED37S/840 PSU W20L120 OC	Not applicable
910925864843	SM134V LED37S/830 PSU W20L120 OC	Not applicable
910925864844	SM134V LED27S/840 PSU W20L120 ELB3 NOC	Not applicable
910925864845	SM134V LED37S/840 PSU W20L120 ELB3 NOC	Not applicable
910925864846	SM134V LED27S/840 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
910925864847	SM134V LED37S/840 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
910925864848	SM134V LED27S/840 PSD W20L120 ELB3 OC	1% (no dimming in emergency mode)
910925864849	SM134V LED37S/840 PSD W20L120 ELB3 OC	1% (no dimming in emergency mode)
910925864850	SM134V LED27S/830 PSU W20L120 ELB3 NOC	Not applicable
910925864851	SM134V LED37S/830 PSU W20L120 ELB3 NOC	Not applicable
910925864852	SM134V LED27S/830 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
910925864853	SM134V LED37S/830 PSD W20L120 ELB3 NOC	1% (no dimming in emergency mode)
910925865183	SM134V LED37S/840 W20L120 IA1 NOC	1%

CoreLine Surface-mounted

Order Code	Full Product Name	Maximum dim level
910925865184	SM134V LED37S/840 W20L120 IA1 OC	1%
910925865185	SM134V LED37S/830 W20L120 IA1 NOC	1%
910925865187	SM134V LED37S/830 W20L120 IA1 OC	1%
910925865191	SM134V LED37S/840 W20L120 ELB3 IA1 OC	1%
910925865192	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	1%

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910925864810	SM134V LED37S/830 PSU W60L60 NOC	No	910925864815	SM134V LED37S/840 PSD W20L120 NOC	Yes
910925864811	SM134V LED27S/830 PSU W60L60 NOC	No	910925864818	SM134V LED37S/830 PSD W20L120 NOC	Yes
910925864814	SM134V LED37S/840 PSD W60L60 NOC	Yes	910925864819	SM134V LED27S/830 PSD W20L120 NOC	Yes
910925864816	SM134V LED37S/830 PSD W60L60 NOC	Yes	910925864822	SM134V LED37S/840 PSD W20L120 OC	Yes
910925864817	SM134V LED27S/830 PSD W60L60 NOC	Yes	910925864823	SM134V LED27S/840 PSD W20L120 OC	Yes
910925864820	SM134V LED37S/840 PSD W60L60 OC	Yes	910925864826	SM134V LED37S/830 PSD W20L120 OC	Yes
910925864821	SM134V LED27S/840 PSD W60L60 OC	Yes	910925864827	SM134V LED27S/830 PSD W20L120 OC	Yes
910925864824	SM134V LED37S/830 PSD W60L60 OC	Yes	910925864829	SM134V LED37S/840 PSU W20L120 NOC	No
910925864825	SM134V LED27S/830 PSD W60L60 OC	Yes	910925864835	SM134V LED27S/840 PSU W20L120 NOC	No
910925864828	SM134V LED37S/840 PSU W60L60 NOC	No	910925864837	SM134V LED27S/840 PSD W20L120 NOC	Yes
910925864830	SM134V LED37S/840 PSU W60L60 ELB3 NOC	No	910925864841	SM134V LED37S/840 PSU W20L120 OC	No
910925864831	SM134V LED37S/840 PSD W60L60 ELB3 NOC	Yes	910925864843	SM134V LED37S/830 PSU W20L120 OC	No
910925864832	SM134V LED37S/840 PSD W60L60 ELB3 OC	Yes	910925864844	SM134V LED27S/840 PSU W20L120 ELB3 NOC	No
910925864833	SM134V LED27S/840 PSD W60L60 ELB3 OC	Yes	910925864845	SM134V LED37S/840 PSU W20L120 ELB3 NOC	No
910925864834	SM134V LED27S/840 PSU W60L60 NOC	No	910925864846	SM134V LED27S/840 PSD W20L120 ELB3 NOC	Yes
910925864836	SM134V LED27S/840 PSD W60L60 NOC	Yes	910925864847	SM134V LED37S/840 PSD W20L120 ELB3 NOC	Yes
910925864838	SM134V LED27S/840 PSU W60L60 ELB3 NOC	No	910925864848	SM134V LED27S/840 PSD W20L120 ELB3 OC	Yes
910925864839	SM134V LED27S/840 PSD W60L60 ELB3 NOC	Yes	910925864849	SM134V LED37S/840 PSD W20L120 ELB3 OC	Yes
910925864840	SM134V LED37S/840 PSU W60L60 OC	No	910925864850	SM134V LED27S/830 PSU W20L120 ELB3 NOC	No
910925864842	SM134V LED37S/830 PSU W60L60 OC	No	910925864851	SM134V LED37S/830 PSU W20L120 ELB3 NOC	No
910925865186	SM134V LED37S/840 W60L60 IA1 NOC	Wireless Dim	910925864852	SM134V LED27S/830 PSD W20L120 ELB3 NOC	Yes
910925865188	SM134V LED37S/840 W60L60 IA1 OC	Wireless Dim	910925864853	SM134V LED37S/830 PSD W20L120 ELB3 NOC	Yes
910925865189	SM134V LED37S/830 W60L60 IA1 NOC	Wireless Dim	910925865183	SM134V LED37S/840 W20L120 IA1 NOC	Wireless Dim
910925865190	SM134V LED37S/830 W60L60 IA1 OC	Wireless Dim	910925865184	SM134V LED37S/840 W20L120 IA1 OC	Wireless Dim
910925865193	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	Wireless Dim	910925865185	SM134V LED37S/830 W20L120 IA1 NOC	Wireless Dim
910925865194	SM134V LED37S/840 W60L60 ELB3 IA1 OC	Wireless Dim	910925865187	SM134V LED37S/830 W20L120 IA1 OC	Wireless Dim
910925864812	SM134V LED37S/830 PSU W20L120 NOC	No	910925865191	SM134V LED37S/840 W20L120 ELB3 IA1 OC	Wireless Dim
910925864813	SM134V LED27S/830 PSU W20L120 NOC	No	910925865192	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	Wireless Dim

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
910925864810	SM134V LED37S/830 PSU W60L60 NOC	220 to 240 V	910925864830	SM134V LED37S/840 PSU W60L60 ELB3 NOC	220 to 240 V
910925864811	SM134V LED27S/830 PSU W60L60 NOC	220 to 240 V	910925864831	SM134V LED37S/840 PSD W60L60 ELB3 NOC	220 to 240 V
910925864814	SM134V LED37S/840 PSD W60L60 NOC	220 to 240 V	910925864832	SM134V LED37S/840 PSD W60L60 ELB3 OC	220 to 240 V
910925864816	SM134V LED37S/830 PSD W60L60 NOC	220 to 240 V	910925864833	SM134V LED27S/840 PSD W60L60 ELB3 OC	220 to 240 V
910925864817	SM134V LED27S/830 PSD W60L60 NOC	220 to 240 V	910925864834	SM134V LED27S/840 PSU W60L60 NOC	220 to 240 V
910925864820	SM134V LED37S/840 PSD W60L60 OC	220 to 240 V	910925864836	SM134V LED27S/840 PSD W60L60 NOC	220 to 240 V
910925864821	SM134V LED27S/840 PSD W60L60 OC	220 to 240 V	910925864838	SM134V LED27S/840 PSU W60L60 ELB3 NOC	220 to 240 V
910925864824	SM134V LED37S/830 PSD W60L60 OC	220 to 240 V	910925864839	SM134V LED27S/840 PSD W60L60 ELB3 NOC	220 to 240 V
910925864825	SM134V LED27S/830 PSD W60L60 OC	220 to 240 V	910925864840	SM134V LED37S/840 PSU W60L60 OC	220 to 240 V
910925864828	SM134V LED37S/840 PSU W60L60 NOC	220 to 240 V	910925864842	SM134V LED37S/830 PSU W60L60 OC	220 to 240 V

CoreLine Surface-mounted

Order Code	Full Product Name	Input Voltage
910925865186	SM134V LED37S/840 W60L60 IA1 NOC	220–240 V
910925865188	SM134V LED37S/840 W60L60 IA1 OC	220–240 V
910925865189	SM134V LED37S/830 W60L60 IA1 NOC	220–240 V
910925865190	SM134V LED37S/830 W60L60 IA1 OC	220–240 V
910925865193	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	220–240 V
910925865194	SM134V LED37S/840 W60L60 ELB3 IA1 OC	220–240 V
910925864812	SM134V LED37S/830 PSU W20L120 NOC	220 to 240 V
910925864813	SM134V LED27S/830 PSU W20L120 NOC	220 to 240 V
910925864815	SM134V LED37S/840 PSD W20L120 NOC	220 to 240 V
910925864818	SM134V LED37S/830 PSD W20L120 NOC	220 to 240 V
910925864819	SM134V LED27S/830 PSD W20L120 NOC	220 to 240 V
910925864822	SM134V LED37S/840 PSD W20L120 OC	220 to 240 V
910925864823	SM134V LED27S/840 PSD W20L120 OC	220 to 240 V
910925864826	SM134V LED37S/830 PSD W20L120 OC	220 to 240 V
910925864827	SM134V LED27S/830 PSD W20L120 OC	220 to 240 V
910925864829	SM134V LED37S/840 PSU W20L120 NOC	220 to 240 V
910925864835	SM134V LED27S/840 PSU W20L120 NOC	220 to 240 V
910925864837	SM134V LED27S/840 PSD W20L120 NOC	220 to 240 V

Order Code	Full Product Name	Input Voltage
910925864841	SM134V LED37S/840 PSU W20L120 OC	220 to 240 V
910925864843	SM134V LED37S/830 PSU W20L120 OC	220 to 240 V
910925864844	SM134V LED27S/840 PSU W20L120 ELB3 NOC	220 to 240 V
910925864845	SM134V LED37S/840 PSU W20L120 ELB3 NOC	220 to 240 V
910925864846	SM134V LED27S/840 PSD W20L120 ELB3 NOC	220 to 240 V
910925864847	SM134V LED37S/840 PSD W20L120 ELB3 NOC	220 to 240 V
910925864848	SM134V LED27S/840 PSD W20L120 ELB3 OC	220 to 240 V
910925864849	SM134V LED37S/840 PSD W20L120 ELB3 OC	220 to 240 V
910925864850	SM134V LED27S/830 PSU W20L120 ELB3 NOC	220 to 240 V
910925864851	SM134V LED37S/830 PSU W20L120 ELB3 NOC	220 to 240 V
910925864852	SM134V LED27S/830 PSD W20L120 ELB3 NOC	220 to 240 V
910925864853	SM134V LED37S/830 PSD W20L120 ELB3 NOC	220 to 240 V
910925865183	SM134V LED37S/840 W20L120 IA1 NOC	220–240 V
910925865184	SM134V LED37S/840 W20L120 IA1 OC	220–240 V
910925865185	SM134V LED37S/830 W20L120 IA1 NOC	220–240 V
910925865187	SM134V LED37S/830 W20L120 IA1 OC	220–240 V
910925865191	SM134V LED37S/840 W20L120 ELB3 IA1 OC	220–240 V
910925865192	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	220–240 V

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864810	SM134V LED37S/830 PSU W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	3700 lm
910925864811	SM134V LED27S/830 PSU W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2700 lm
910925864814	SM134V LED37S/840 PSD W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
910925864816	SM134V LED37S/830 PSD W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	104 lm/W	3700 lm
910925864817	SM134V LED27S/830 PSD W60L60 NOC	(0.43, 0.40) SDCM <3	3000 K	89 lm/W	2700 lm
910925864820	SM134V LED37S/840 PSD W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	117 lm/W	3700 lm
910925864821	SM134V LED27S/840 PSD W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	123 lm/W	2700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864824	SM134V LED37S/830 PSD W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	3700 lm
910925864825	SM134V LED27S/830 PSD W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	2700 lm
910925864828	SM134V LED37S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	109 lm/W	3700 lm
910925864830	SM134V LED37S/840 PSU W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	97 lm/W	3700 lm
910925864831	SM134V LED37S/840 PSD W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	95 lm/W	3700 lm
910925864832	SM134V LED37S/840 PSD W60L60 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	3700 lm
910925864833	SM134V LED27S/840 PSD W60L60 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	2700 lm

CoreLine Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864834	SM134V LED27S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	100 lm/W	2700 lm
910925864836	SM134V LED27S/840 PSD W60L60 NOC	(0.38, 0.38) SDCM <3	4000 K	102 lm/W	2700 lm
910925864838	SM134V LED27S/840 PSU W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
910925864839	SM134V LED27S/840 PSD W60L60 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
910925864840	SM134V LED37S/840 PSU W60L60 OC	(0.38, 0.38) SDCM <3	4000 K	121 lm/W	3700 lm
910925864842	SM134V LED37S/830 PSU W60L60 OC	(0.43, 0.40) SDCM <3	3000 K	107 lm/W	3700 lm
910925865186	SM134V LED37S/840 W60L60 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
910925865188	SM134V LED37S/840 W60L60 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
910925865189	SM134V LED37S/830 W60L60 IA1 NOC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
910925865190	SM134V LED37S/830 W60L60 IA1 OC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
910925865193	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm
910925865194	SM134V LED37S/840 W60L60 ELB3 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm
910925864812	SM134V LED37S/830	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	3700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU W20L120 NOC				
910925864813	SM134V LED27S/830 PSU W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2700 lm
910925864815	SM134V LED37S/840 PSD W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
910925864818	SM134V LED37S/830 PSD W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	104 lm/W	3700 lm
910925864819	SM134V LED27S/830 PSD W20L120 NOC	(0.43, 0.40) SDCM <3	3000 K	89 lm/W	2700 lm
910925864822	SM134V LED37S/840 PSD W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	117 lm/W	3700 lm
910925864823	SM134V LED27S/840 PSD W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	123 lm/W	2700 lm
910925864826	SM134V LED37S/830 PSD W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	3700 lm
910925864827	SM134V LED27S/830 PSD W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	117 lm/W	2700 lm
910925864829	SM134V LED37S/840 PSU W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	109 lm/W	3700 lm
910925864835	SM134V LED27S/840 PSU W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	100 lm/W	2700 lm
910925864837	SM134V LED27S/840 PSD W20L120 NOC	(0.38, 0.38) SDCM <3	4000 K	102 lm/W	2700 lm

CoreLine Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910925864841	SM134V LED37S/840 PSU W20L120 OC	(0.38, 0.38) SDCM <3	4000 K	121 lm/W	3700 lm
910925864843	SM134V LED37S/830 PSU W20L120 OC	(0.43, 0.40) SDCM <3	3000 K	107 lm/W	3700 lm
910925864844	SM134V LED27S/840 PSU W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
910925864845	SM134V LED37S/840 PSU W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	97 lm/W	3700 lm
910925864846	SM134V LED27S/840 PSD W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	89 lm/W	2700 lm
910925864847	SM134V LED37S/840 PSD W20L120 ELB3 NOC	(0.38, 0.38) SDCM <3	4000 K	104 lm/W	3700 lm
910925864848	SM134V LED27S/840 PSD W20L120 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	2700 lm
910925864849	SM134V LED37S/840 PSD W20L120 ELB3 OC	(0.38, 0.38) SDCM <3	4000 K	106 lm/W	3700 lm
910925864850	SM134V LED27S/830	(0.43, 0.40) SDCM <3	3000 K	84 lm/W	2700 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU W20L120 ELB3 NOC				
910925864851	SM134V LED37S/830 PSU W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	97 lm/W	3700 lm
910925864852	SM134V LED27S/830 PSD W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	79 lm/W	2700 lm
910925864853	SM134V LED37S/830 PSD W20L120 ELB3 NOC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	3700 lm
910925865183	SM134V LED37S/840 W20L120 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
910925865184	SM134V LED37S/840 W20L120 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	104.5 lm/W	3700 lm
910925865185	SM134V LED37S/830 W20L120 IA1 NOC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
910925865187	SM134V LED37S/830 W20L120 IA1 OC	(0.43, 0.40) SDCM <3	3000 K	104.5 lm/W	3700 lm
910925865191	SM134V LED37S/840 W20L120 ELB3 IA1 OC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm
910925865192	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	(0.38, 0.38) SDCM <3	4000 K	94 lm/W	3700 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910925864810	SM134V LED37S/830 PSU W60L60 NOC	34 W
910925864811	SM134V LED27S/830 PSU W60L60 NOC	28.5 W
910925864814	SM134V LED37S/840 PSD W60L60 NOC	35.5 W
910925864816	SM134V LED37S/830 PSD W60L60 NOC	35.5 W
910925864817	SM134V LED27S/830 PSD W60L60 NOC	30.5 W
910925864820	SM134V LED37S/840 PSD W60L60 OC	31.5 W

Order Code	Full Product Name	Initial input power
910925864821	SM134V LED27S/840 PSD W60L60 OC	22 W
910925864824	SM134V LED37S/830 PSD W60L60 OC	31.5 W
910925864825	SM134V LED27S/830 PSD W60L60 OC	23 W
910925864828	SM134V LED37S/840 PSU W60L60 NOC	34 W
910925864830	SM134V LED37S/840 PSU W60L60 ELB3 NOC	38 W
910925864831	SM134V LED37S/840 PSD W60L60 ELB3 NOC	39 W

CoreLine Surface-mounted

Order Code	Full Product Name	Initial input power
910925864832	SM134V LED37S/840 PSD W60L60 ELB3 OC	35 W
910925864833	SM134V LED27S/840 PSD W60L60 ELB3 OC	25.5 W
910925864834	SM134V LED27S/840 PSU W60L60 NOC	27 W
910925864836	SM134V LED27S/840 PSD W60L60 NOC	26.5 W
910925864838	SM134V LED27S/840 PSU W60L60 ELB3 NOC	30.5 W
910925864839	SM134V LED27S/840 PSD W60L60 ELB3 NOC	30.5 W
910925864840	SM134V LED37S/840 PSU W60L60 OC	30.5 W
910925864842	SM134V LED37S/830 PSU W60L60 OC	34.5 W
910925865186	SM134V LED37S/840 W60L60 IA1 NOC	35.4 W
910925865188	SM134V LED37S/840 W60L60 IA1 OC	35.4 W
910925865189	SM134V LED37S/830 W60L60 IA1 NOC	35.4 W
910925865190	SM134V LED37S/830 W60L60 IA1 OC	35.4 W
910925865193	SM134V LED37S/840 W60L60 ELB3 IA1 NOC	39.3 W
910925865194	SM134V LED37S/840 W60L60 ELB3 IA1 OC	39.3 W
910925864812	SM134V LED37S/830 PSU W20L120 NOC	34 W
910925864813	SM134V LED27S/830 PSU W20L120 NOC	28.5 W
910925864815	SM134V LED37S/840 PSD W20L120 NOC	35.5 W
910925864818	SM134V LED37S/830 PSD W20L120 NOC	35.5 W
910925864819	SM134V LED27S/830 PSD W20L120 NOC	30.5 W
910925864822	SM134V LED37S/840 PSD W20L120 OC	31.5 W
910925864823	SM134V LED27S/840 PSD W20L120 OC	22 W
910925864826	SM134V LED37S/830 PSD W20L120 OC	31.5 W

Order Code	Full Product Name	Initial input power
910925864827	SM134V LED27S/830 PSD W20L120 OC	23 W
910925864829	SM134V LED37S/840 PSU W20L120 NOC	34 W
910925864835	SM134V LED27S/840 PSU W20L120 NOC	27 W
910925864837	SM134V LED27S/840 PSD W20L120 NOC	26.5 W
910925864841	SM134V LED37S/840 PSU W20L120 OC	30.5 W
910925864843	SM134V LED37S/830 PSU W20L120 OC	34.5 W
910925864844	SM134V LED27S/840 PSU W20L120 ELB3 NOC	30.5 W
910925864845	SM134V LED37S/840 PSU W20L120 ELB3 NOC	38 W
910925864846	SM134V LED27S/840 PSD W20L120 ELB3 NOC	30.5 W
910925864847	SM134V LED37S/840 PSD W20L120 ELB3 NOC	35.5 W
910925864848	SM134V LED27S/840 PSD W20L120 ELB3 OC	25.5 W
910925864849	SM134V LED37S/840 PSD W20L120 ELB3 OC	35 W
910925864850	SM134V LED27S/830 PSU W20L120 ELB3 NOC	32 W
910925864851	SM134V LED37S/830 PSU W20L120 ELB3 NOC	38 W
910925864852	SM134V LED27S/830 PSD W20L120 ELB3 NOC	34 W
910925864853	SM134V LED37S/830 PSD W20L120 ELB3 NOC	39 W
910925865183	SM134V LED37S/840 W20L120 IA1 NOC	35.4 W
910925865184	SM134V LED37S/840 W20L120 IA1 OC	35.4 W
910925865185	SM134V LED37S/830 W20L120 IA1 NOC	35.4 W
910925865187	SM134V LED37S/830 W20L120 IA1 OC	35.4 W
910925865191	SM134V LED37S/840 W20L120 ELB3 IA1 OC	39.3 W
910925865192	SM134V LED37S/840 W20L120 ELB3 IA1 NOC	39.3 W

