



ComfortVision – asymmetric downlighting

ComfortVision SNF111

ComfortVision is a high-efficiency, asymmetric floodlight, distributing a low-glare beam evenly and accurately. It can accommodate metal-halide lamps for good color rendering or a high-pressure sodium lamp for economical performance. Available in medium- or narrow-beam versions, the floodlight accepts a single 1000 or two 400 or 600 W lamps. The twin-lamp version offers switching flexibility that permits tailoring to the user's needs while allowing energy savings. ComfortVision's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing. For optimal downlighting, the luminaire should be mounted horizontally at a height of 15-25 meters. It has an adjustment range of $\pm 12^\circ$ from the horizontal. A universal mounting bracket allows mounting to headframes, ceilings and walls.

Benefits

- High-efficiency asymmetrical floodlight that distributes a low-glare beam evenly and accurately
- Maximum flexibility with a choice of medium- or narrow-beam versions and a single 1000 W or two switchable 400 or 600 W lamps
- Rugged, all-weather construction designed for easy aiming, simple cleaning and speedy servicing

Features

- Rugged, all-weather construction
- Single 1000 W or two switchable 400 or 600 W lamps
- Medium or narrow beam
- Adjustment range of $\pm 12^\circ$ from the horizontal
- Universal mounting bracket

ComfortVision SNF111

Application

- Industrial areas
- Roundabouts
- Car parks
- Sports lighting


Specifications

Aiming Horizontal	to °
Aiming Vertical	to °
Ballast	Conventional(CONV)
Material of Bracket	Bracket:
Material of Gear box	Gear box:

Material	Housing:
Material of Reflector	Reflector:
Material	:
Material	:

Versions

ComfortVision SNF111 area-lighting luminaire




Product details

Second cable gland



Quick-release clips for easy access



General Information

CE mark	CE mark
ENEC mark	-
Gear	CONV
Optic type	Medium beam
Product Family Code	SNF111

General Information

ComfortVision SNF111

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources
54753400	SNF111 1xHPI-TP1000W K	HPI-TP	1000 W	1
	MB			

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources
54755800	SNF111 2xSON-TP400W K	SON-TP	400 W	2
	MB			

