



# SPP368 Spectrum

## Spectrum SPP368

A road lighting luminaire for tubular high-pressure sodium lamps up to 600W. With its compact design and T-pot reflector, it brings optimal lighting performance while minimizing cost. A step dimming option is available for SON-T 400W and SON-T 250W lamps.

### Features

- Patented design
- High pressure die-cast aluminium housing for strength and anticorrosion
- High purity aluminium T-POT reflector
- Toughened flat or curved glass cover
- Easy maintenance and lamp replacement from above in an ergonomic position
- Suitable lamps: SON-T 150-600W or HPI-T 250W-400W
- Lamps in wattages 400W and above are only available with curved bowl versions only

### Application

- Expressways
- Major roads
- Industrial parks
- Crossings and roundabouts

Spectrum SPP368

Dimensional drawing

Spectrum SPP368

General Information	
Cap-Base	E40
Color	Silver
Country version	NO
Optical cover/lens type	GB
Gear	SON gear
Lamp family code	SON-T
Number of light sources	1
Optic type	Closed T-POT
Product Family Code	SPP368

General Information

order code	Lamp power
910401964880	250
910401964980	400

Light Technical

order code	Light output ratio
910401964880	0.7

order code	Light output ratio
910401964980	0.68

