



SPP368 Spectrum

Spectrum SPP368

A road lighting luminaire for tubular high-pressure sodium lamps up to 600W. With its compact design and T-pot reflector, it brings optimal lighting performance while minimizing cost. A step dimming option is available for SON-T 400W and SON-T 250W lamps.

Features

- Patented design
- High pressure die-cast aluminium housing for strength and anticorrosion
- High purity aluminium T-POT reflector
- Toughened flat or curved glass cover
- Easy maintenance and lamp replacement from above in an ergonomic position
- Suitable lamps: SON-T 150-600W or HPI-T 250W-400W
- Lamps in wattages 400W and above are only available with curved bowl versions only

Application

- Expressways
- Major roads
- Industrial parks
- Crossings and roundabouts

Spectrum SPP368

Dimensional drawing

Spectrum SPP368

