



SRX509

SRX509 *do not use*

Underpass luminaire suitable for use with SON-T 150W, 250W, 400W high pressure sodium vapour lamps..

Benefits

- Removable gear tray for easy repair and maintenance

Features

- Reflector is made of high purity anodised aluminium to give a wide beam and maximum optical efficiency
- Removable gear tray for easy repair and maintenance
- Socket plug terminal for easy and fast lamp connection
- Gear unit uses Philips standard basic ballast
- Ambient temperature of max 45°C

Application

- Toll gate station.
- Underpass.
- Basement parking areas.

SRX509 *do not use*

Versions



SRX509 SON 220V

General Information

Cap-Base	E40
Gear	SGR
Lamp family code	SON-T
Number of light sources	1 pc

General Information

Order Code	Full Product Name	Lamp power	Optic type
910401602280	SRX509 SON-T150W 220V-50Hz S	150 W	Symmetrical
910401602380	SRX509 SON-T250W 220V-50Hz S	250 W	Symmetrical

Order Code	Full Product Name	Lamp power	Optic type
910401602480	SRX509 SON-T400W 220V-50Hz S	400 W	Symmetrical
910401602780	SRX509 SON-T150W 220V-50Hz A	150 W	Asymmetrical

