



# StoreFit – the best fit for your store

## StoreFit Projector

This attractively priced projector brings together MASTERColour CDM Elite lamp technology, a dedicated driver and an efficient reflector to deliver excellent light quality and significant energy savings. Offering a choice of power, color and beam width, the flexible StoreFit is ideal for illuminating shop windows, sales floors, racks and shelves, truly bringing the merchandise on display to life.

### Benefits

- Up to 30% energy savings and short payback time compared to CDM
- Excellent light quality
- Flexible – various combinations of wattages, beam widths and colors

### Features

- Efficient reflector (70%)
- Color rendering index 90
- Choice of architecture: projector, cardanic or elbow
- Choice of color: black, white or grey
- Choice of narrow, medium and wide beams
- 35/50/70 W versions

### Application

- Retail

### Specifications

Type	ST130T
Light source	HID: - MASTERColour CDM-T Elite / G12 / 35, 50, 70 W
Lamp included	Yes (lamp color 930)
Light distribution	Direct

Ballast	Electronic, High Frequency 220 - 240 V / 50 - 60 Hz: - HID PV Ecoballast (EBE)
Optic	Narrow (12°), medium (24°) or wide beam (42°)
Optical cover	Glass
Connection	3-circuit track connector

# StoreFit Projector

Material	Housing: metal, folded
	End caps: plastic
	Reflector: aluminum
	Cover: glass
Color	Grey (RAL9006)
	White (RAL9010)
	Black (RAL9004)

Installation	On 3-circuit track (3C)
	Rotation: 340° horizontal, -120/+120° vertical
Maintenance	No tool needed for relamping maintenance

## Product details



StoreFit Projector - Simple design,  
efficient optics and perfect-quality light

