



Product Description

Safety & Comfort Starters

Range of premium quality electronic starters for igniting fluorescent lamps operating on conventional electromagnetic ballast.

Benefits

- Lower cost of lighting ownership: Electronic starters turn-off lamps at end-of-life, which avoids irritation (no flickering), useless electricity consumption and fire risk. / Lamps last much longer thanks to a totally smooth, flicker-free and fast starting. / -Longer starter service life compared to conventional starters.
- · Contribution to a green environment (no lead and no radioactivity)
- Flame-retardant components & UV-resistant canister lead to additional safety and a secure ignition
- · Easy recognition & installation and replacement friendly

Features

- $\boldsymbol{\cdot}$ Full thermal safety monitor which cuts off defective or end-of-life lamps
- Instant flicker-free ignition (nom. 2.3 sec)
- Cut-off circuit to protect the starter and overheating of the control gear
- · Premium reliability with 100.000 safe switches
- · Radioactive-free (patented) and lead-free (RoHS-compliant)
- · 2-pin igniter in plastic (flame-retardant polycarbonate) canister
- · Narrowed top & installation notch

Application

• Starters are used in conventional electromagnetic fluorescent lamp systems using TL-D (T8), TL (T12), TL mini, PL-S and PL-L lamps.

Safety & Comfort Starters

Versions



Dimensional drawing

F

Product	C (max)	E (max)
S10E 18-75W SIN 220-240V BL/20X25CT	40.3 mm	21.5 mm

Product details



S10E, 18-75W, BL

Safety & Comfort Starters



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.