



# Philips tanning starters: a complete range of easy-to-install eco-friendly starters for tanning lamps operating on a conventional electromagnetic ballast

## Starters for tanning lamps

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

### Benefits

- Easy to install (click and switch)
- Safe ignition
- Eco-friendly

# Starters for tanning lamps

## Features

- Narrowed starter shape and two extra notches (patented innovation)
- Flame-retardant components and UV-resistant canister
- Lead-free, and no radioactive substances

## Application

- Ignite fluorescent lamps (all brands) operating on a conventional electromagnetic ballast.
- Bodytone Starter 25-100W - 220-240V~, 25-100W, Single application
- Bodytone Starter 120-180W - 220-240V~, 120-180W, Single application
- S12 Bodytone Starter 115-140W - 220-240V~, 115-140W, Single application
- S16 Starter 220-240~, 70, 75, 85, 100, 125W, Single application

## Warnings and Safety


- Flame-retardant components
- UV-resistant canister

## Versions



LPPR STARTER PHL 0004

## Dimensional drawing



Product	C (max)	E (max)
S12 115-140W 220-240V UNP/20X25CT	40.3 mm	21.5 mm

Starters for tanning lamps

Product details



S12, 115-140W

