



TBH375

TBH375

Ball-impact-resistant luminaire for TL-D fluorescent lamps, specially designed for multipurpose sports halls and tennis halls. Lamellae prevent players from seeing directly into the lamps. Strong housing construction protects lamps against ball impact. For surface or recessed mounting. Optics supplied with the luminaire.

Beneficii

- Impact-resistant luminaire specifically designed for multi-purpose sports halls - can be surface-mounted or recessed
- Lamps are protected against ball impact by the strong housing
- Optical system with cross-lamellae reduces glare by preventing users from looking directly into the lamps

Caracteristici

- Carcasă rezistentă la impact
- Lămpi fluorescente TL-D
- Sistem optic cu lamele transversale

Cerere


- Săli de sport polivalente
- Săli de tenis

TBH375

Versions



Cote



Product
TBH375 6xTL5-49W/830 HFR PI
TBH375 3xTL5-49W/830 HFR PI
TBH375 4xTL5-80W/830 HFR PI
TBH375 4xTL5-49W/830 HFR PI
TBH375 2xTL5-80W/830 HFR PI
TBH375 2xTL5-49W/830 HFR PI
TBH375 3xTL5-80W/830 HFR PI
TBH375 6xTL5-80W/830 HFP PI
TBH375 3xTL5-80W/830 HFP PI
TBH375 3xTL5-49W/830 HFP PI
TBH375 3xTL-D58W/830 HFP PI
TBH375 4xTL5-80W/830 HFP PI
TBH375 4xTL5-49W/830 HFP PI
TBH375 2xTL5-80W/830 HFP PI
TBH375 2xTL5-49W/830 HFP PI
TBH375 2xTL-D58W/830 HFP PI
TBH375 3xTL-D58W HFR PI
TBH375 2xTL-D58W HFR PI
TBH375 3xTL-D58W HFP
TBH375 2xTL-D58W HFP

Approval and Application

Cod protecție împotriva infiltrărilor	IP20
---------------------------------------	------

Operating and Electrical

Tensiune de intrare	220 to 240 V
---------------------	--------------

General Information

Marcaj pentru rezistența la impactul mingii	Ball Impact Resistance mark
Marcaj CE	CE mark
Clasă de protecție IEC	Clasa de siguranță I
Circuit de compensare	-
Marcaj ENEC	ENEC mark
Cod familie de produse	TBH375

General Information

Order Code	Full Product Name	Echipament	Cod familie lămpi	Putere lampă	Număr de surse de lumină
05093500	TBH375 2xTL-D58W HFP	HFP	TL-D	58 W	2
05096600	TBH375 3xTL-D58W HFP	HFP	TL-D	58 W	3
63563700	TBH375 2xTL-D58W HFR PI	HF Regulator	TL-D	58 W	2
75804600	TBH375 2xTL-D58W/830 HFP PI	HFP	TL-D	58 W	2
75807700	TBH375 2xTL5-49W/830 HFP PI	HFP	TL5	49 W	2
75808400	TBH375 2xTL5-80W/830 HFP PI	HFP	TL5	80 W	2
75810700	TBH375 4xTL5-49W/830 HFP PI	HFP	TL5	49 W	4
75806000	TBH375 3xTL-D58W/830 HFP PI	HFP	TL-D	58 W	3
75813800	TBH375 3xTL5-49W/830 HFP PI	HFP	TL5	49 W	3
75814500	TBH375 3xTL5-80W/830 HFP PI	HFP	TL5	80 W	3

