



Excellent light distribution with maximum energy efficiency

TBS022

The TBS022 luminaire has a high-reflectance, high-gloss aluminum reflector. This guarantees high performance, making this system the best lighting solution for retail applications. It also features excellent light distribution, elegance, and advanced technology. This recessed luminaire consists of two TL5 lamps of 50 and 54 W and can be used to replace systems with luminaires for HO 110 W lamps. The high-performance electronic ballast ensures a longer lamp life and is internally mounted in the luminaire, preventing any risk of the wiring being accidentally disconnected during installation.

Benefits

- Easy to install
- Very high performance
- Excellent finish on entire luminaire

Features

- Steel-plate body (0.5 mm) in white color and high-purity aluminum reflector
- Recessed
- For two TL5 lamps of 54/50 W and 28/25 W

Application

- Ideal for general supermarket lighting

Specifications

TBS022

Type	TBS022
Light source	MASTER TL5 28/54 W MASTER TL5 Eco 25/50 W
Mains voltage	220-240 V / 50-60 Hz

Materials and finishing	Phosphated steel-plate body (0.5 mm) in white color and high-purity aluminum reflector
Installation	Recessed in the ceiling

Versions



General Information

Lamp family code	TL5
Number of light sources	2 pcs
Optic type	Reflector high reflectance

General Information

Order Code	Full Product Name	Gear	Lamp power
919106032161	TBS022 2XTL5-54W/840 EB R-H	EB	54 W
919106032162	TBS022 2XTL5-50W/840 EB R-H	EB	50 W
919106032163	TBS022 2XTL5-28W/840 EB R-H	EB	28 W

Order Code	Full Product Name	Gear	Lamp power
919106032164	TBS022 2XTL5-50W/840 HFD R-H	HFD	50 W
919106032169	TBS022 2xTL5-25W R-H	-	25 W

