



TBS027 – Functional and convenient

TBS027

The TBS027 luminaires have a compact design for use in areas that require diffuse light in large quantities. The recessed models are designed for use with 32 W TL-D tubular fluorescent lamps and are easy to install and maintain. Also available for surface mounting (TCS027).

Benefits

- Functional and convenient for easy application and quality of light
- Easy installation and maintenance

Features

- High-gloss aluminum reflectors
- Perfect light distribution that enhances your project
- Ideal luminaire for projects that require high-level lighting

Application

- Offices
- Buildings
- Schools
- Universities
- Libraries
- Shops
- Hospitals

Specifications

| | |
|---------------|-----------------------------------|
| Type | TBS027 |
| Light source | 2 x 32 W TL-D |
| Mains voltage | Electronic 220 V / 60-50 Hz: (EB) |

| | |
|-------------------------|--------------------------------------|
| Materials and finishing | Phosphated steel body in white color |
| | High-purity aluminum optics |

TBS027

| | |
|---------------------|---|
| Installation | Surface-mounted TBS027: for plaster ceilings 2 x 32 W (1380 x 275 mm) |
|---------------------|---|

Versions



General Information

| | |
|-------------------------|----------------------------|
| Lamp family code | TL-D |
| Lamp power | 32 W |
| Number of light sources | 2 pcs |
| Optic type | Reflector high reflectance |

Operating and Electrical

| Order Code | Full Product Name | Input Voltage |
|--------------|--------------------------------------|---------------|
| 919106050091 | TBS027 2XTL-D32W/840 EI 110/220V R-H | 110 to 220 V |

| Order Code | Full Product Name | Input Voltage |
|--------------|-----------------------------|---------------|
| 919106050101 | TBS027 2XTL-D32W/840 EB R-H | - |

General Information

| Order Code | Full Product Name | Gear |
|--------------|--------------------------------------|------|
| 919106050091 | TBS027 2XTL-D32W/840 EI 110/220V R-H | EI |

| Order Code | Full Product Name | Gear |
|--------------|-----------------------------|------|
| 919106050101 | TBS027 2XTL-D32W/840 EB R-H | EB |

