



TBS065 – Extensive functionality

TBS065

The TBS065 luminaires were specially developed for indoor commercial lighting, and are available in recessed (TBS065) and surface-mounted (TCS065) models. This is an economical range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TBS can be recessed in any type of ceiling (plaster or paneled) and has a C4 optical system that guarantees high-quality projects, energy savings, excellent lighting efficiency, and easy installation.

Benefits

- Functional and convenient for easy application and quality of light
- C4 optic that provides good-quality lighting
- Easy installation and maintenance

Features

- High-gloss aluminum reflectors
- Perfect light distribution that enhances your project

Application

- Offices
- Buildings
- Schools
- Universities
- Libraries
- Shops
- Hospitals

Specifications


Type	TBS065	Light source	4 x 16 W / 2 x 32 W TL-D
------	--------	--------------	--------------------------

TBS065

Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
Materials and finishing	Phosphated steel body of 0.5 mm thickness in white color
	High-purity aluminum optics
	Parabolic wings in high-gloss aluminum (C4)

Installation	Surface-mounted TBS065: for modular "T" profile, plaster, or paneled ceilings
---------------------	---

Versions



General Information

Gear	EB
Lamp family code	TL-D
Optic type	High-gloss optic with V-shaped cross-lamellae

General Information

Order Code	Full Product Name	Lamp power	Number of light sources
919106031841	TBS065 2XTL-D32W/840 EB C4	32 W	2 pcs

Order Code	Full Product Name	Lamp power	Number of light sources
919106031861	TBS065 4XTL-D16W/840 EB C4	16 W	4 pcs

