




TBS068

TBS068

An economical recessed mounted luminaire for TL-D fluorescent lamps with gloss or matt optics for indoor general lighting applications. It offers an economical lighting solution for exposed T-bar ceilings.

Features

- Extremely flat housing design
- Ease of installation by means of specially designed flip-flat plates

Application

- Office open plans
- Entrance halls

Dimensional drawing

TBS068

Product	A	B
TBS068 2xTL-D36W HF C2	1197 mm	297 mm
TBS068 2xTL-D36W IC FC2	1197 mm	297 mm
TBS068 3xTL-D36W I FM2	1197 mm	297 mm
TBS068 2xTL-D36W I FC2	1197 mm	297 mm
TBS068 3XTLD-36W EBE M2	1197 mm	297 mm
TBS068 4xTL-D18W I FM2	597 mm	597 mm
TBS068 2xTL-D36W I FM2	1197 mm	297 mm
TBS068 2XTLD-36W EBE G2	1197 mm	297 mm
TBS068 4xTL-D18W HF M2	597 mm	597 mm
TBS068 3xTL-D18W IC FC2	597 mm	597 mm
TBS068 3xTL-D36W I FC2	1197 mm	297 mm
TBS068 4XTLD-18W EBE M2	597 mm	597 mm
TBS068 3xTL-D36W IC FC2	1197 mm	297 mm
TBS068 3xTL-D18W HF M2	597 mm	597 mm
TBS068 4xTL-D18W I FC2	597 mm	597 mm
TBS068 3xTL-D18W I FM2	597 mm	597 mm
TBS068 4xTL-D18W HF C2	597 mm	597 mm
TBS068 4xTL-D18W EBE FC2	597 mm	597 mm
TBS068 3XTLD-18W EBE M2	597 mm	597 mm
TBS068 3xTL-D18W I FC2	597 mm	597 mm
TBS068 3xTL-D36W HF M2	1197 mm	297 mm
TBS068 3xTL-D18W HF C2	597 mm	597 mm
TBS068 3xTL-D36W HF C2	1197 mm	297 mm
TBS068 3XTLD-36W EBE G2	1197 mm	297 mm
TBS068 4xTL-D18W IC FC2	597 mm	597 mm
TBS068 3xTL-D18W EBE FC2	597 mm	597 mm
TBS068 2XTLD-36W EBE M2	1197 mm	297 mm
TBS068 2xTL-D36W HF M2	1197 mm	297 mm

Approval and Application	
Ingress protection code	IP20
General Information	
Compensation circuit	Inductive parallel compensated
Gear	CONV
Lamp family code	TL-D
Optic type	FC2
Product Family Code	TBS068

General Information

order code	Lamp power	Number of light sources
910401994180	18	4

order code	Lamp power	Number of light sources
910401994280	36	2

