



TBS068

TBS068

An economical recessed mounted luminaire for TL-D fluorescent lamps with gloss or matt optics for indoor general lighting applications. It offers an economical lighting solution for exposed T-bar ceilings.

Features

- Extremely flat housing design
- Ease of installation by means of specially designed flip-flat plates

Application

- Office open plans
- Entrance halls



Versions



TBS068 recessed luminaire

TBS068

Dimensional drawing



Product	A	B
TBS068 4xTL-D18W HF M2	597 mm	597 mm
TBS068 2xTL-D36W HF C2	1197 mm	297 mm
TBS068 2xTL-D36W HF M2	1197 mm	297 mm
TBS068 3xTL-D36W HF C2	1197 mm	297 mm
TBS068 3xTL-D18W HF C2	597 mm	597 mm
TBS068 3xTL-D36W HF M2	1197 mm	297 mm
TBS068 4xTL-D18W HF C2	597 mm	597 mm
TBS068 3xTL-D18W HF M2	597 mm	597 mm

Approval and Application

Ingress protection code IP20

General Information

Gear HF

Lamp family code TL-D

General Information

order code	Compensation circuit	Lamp power	Number of light sources	Optic type
910403398501	-	18 W	3	C2
910403398601	-	18 W	4	C2
910403398701	-	36 W	2	C2
910403398801	-	36 W	3	C2

order code	Compensation circuit	Lamp power	Number of light sources	Optic type
910403398901	-	36 W	3	M2
910403399001	-	36 W	2	M2
910403399101	-	18 W	4	M2
910403399201	-	18 W	3	M2

