



# T5 Commodity Office TBS288

## TBS288/299 Commodity Office

Express yourself. Create elegance. Add ambience and illuminate your space in pleasant, comfortable light. It is all possible with the new Philips electronic office lighting system, TBS288. By featuring a super slim design, exceptional aesthetics and ease of maintenance, we can give you the freedom to inspire and to design inexpensively in almost any general indoor application. This commodity office luminaire is fitted with T5 lamps and has a highly efficient electronic HF ballast. TBS288 is available in industrial packs (2 pieces per pack).

### Features

- Super slim ergonomic design
- High quality aluminum glossy reflectors and matt rippled louvers for optimum brightness and less glare
- Its trendy PMMA panel with patented 't Radiance' concept renders subtle luminescence suitable for various interiors
- Easy access terminal enables top-connection without detaching louvers, easing installation and maintenance

### Application

- General office spaces
- Recreational areas
- Public buildings
- Departmental stores

Dimensional drawing

TBS299

Product	L
TBS299 3xTL5-14W EBE M2	610 mm
TBS299 2xTL5-14W HF FC2	610 mm
TBS299 3xTL5-21W HF G2	910 mm
TBS299 2xTL5-21W HF G2	910 mm
TBS299 3xTL5-28W EBE M2	1210 mm
TBS299 3xTL5-14W HF G2	610 mm
TBS299 3xTL5-28W HF G2	1210 mm
TBS299 2xTL5-14W EBE M2	610 mm
TBS299 4xTL5-14W HF G2	610 mm
TBS299 2xTL5-28W EBE M2	1210 mm
TBS299 2xTL5-28W HF G2	1210 mm
TBS299 3xTL5-14W EBE M2	610 mm
TBS299 3xTL5-28W EBE M2	1210 mm
TBS299 4xTL5-14W EBE M2	610 mm
TBS299 4xTL5-14W EBE M2	610 mm
TBS299 2xTL5-28W EBE M2	1210 mm

