



SchoolVision – the lighting solution that enhances children's learning

SchoolVision, SmartForm TBS477-Einbauleuchten

This recessed luminaire is part of our SchoolVision lighting concept – the only energy-efficient lighting solution that has proven to increase the learning performance of children and students. It is designed to fit in a wide range of modular ceiling types and plaster ceilings. Highly energy-efficient SchoolVision luminaires use energy-efficient MASTER TL5 lamps and electronic ballasts. Moreover, SchoolVision utilizes controls with integrated daylight sensing and presence detection. This makes the overall solution highly energy-efficient, enabling the lowest possible energy consumption and a significant reduction in CO₂ emissions. SchoolVision – a powerful Dynamic Lighting solution SchoolVision recessed TBS477 is a Dynamic Lighting luminaire, which can provide the various lighting settings that are needed to give children the best learning experience. Thanks to its integrated micro-lens optic (MLO) technology, it creates a true “surface of light”, which makes it a very comfortable solution. If you would like to know more about SchoolVision, please go to www.philips.com/schoolvision.

Vorteile

- Low power density through use of energy-efficient Dynamic Lighting solution
- Luminaire fits a wide variety of modular ceiling types and plaster ceilings
- Clean surface of light

Merkmale

- Dynamic Lighting luminaire optimized to save energy
- A real “surface of light” thanks to micro-lens optic (MLO) technology


Anwendung

- Schools

Abmessungsskizzen

SmartForm TBS460-TBS478

Zubehör



Einbausatz für SmartForm
Einbauleuchten für die Montage in
Deckensysteme mit unsichtbaren
Tragprofilen (ZBS460 SMB SET)

Ordercode 49307799

