



TBS569

TBS569

Functional modular luminaire for TL-5 fluorescent lamps with a choice of 5 optics. All versions are suitable for air handling systems. Extra-length version is available upon request.

Features

- Suitable for all metric ceilings
- Developed professionally using high purity anodized aluminum coupled with delta-shaped beam to provide good uniformity, high efficiency and optimized glare control
- Five types of louvre: D6, C6, M6, M5 and M2
- Built-in height of 55mm: creates more void space and able to lower the total height of the building
- Comes with a specially designed housing structure that composes of a flange, V-clip and a bracket slot. This combination can effectively avoid light leakage while enhancing mechanical strength and safety

Application

- General industries
- Representative offices
- Conference rooms
- Small offices
- General open plan offices
- Data processing offices
- Reception and public service areas

Dimensional drawing

TBS569

Product	A	B
TBS569 2xTL5-14W HFA C6	655 mm	355 mm
TBS569 3xTL5-28W HF M5	1255 mm	655 mm
TBS569 2xTL5-14W HF M5	655 mm	355 mm
TBS569 4xTL5-14W HFP M2 FTB	655 mm	655 mm
TBS569 4xTL5-14W HFA M2	655 mm	655 mm
TBS569 2xTL5-14W HF M2	655 mm	355 mm
TBS569 2xTL5-14W/840 K HFP D6 FTB CAU	655 mm	355 mm
TBS569 3xTL5-28W/840 K HFP M6 FTB CAU	1255 mm	655 mm
TBS569 2xTL5-14W HFP M6 FTB	655 mm	355 mm
TBS569 2xTL5-14W HFE C2	655 mm	355 mm
TBS569 3xTL5-14W HF M2	655 mm	655 mm
TBS569 2xTL5-14W HFP D6 FTB	655 mm	355 mm
TBS569 2xTL5-28W/840 K HFP D6 FTB CAU	1255 mm	355 mm
TBS569 2xTL5-14W/840 K HFP C6 FTB CAU	655 mm	355 mm
TBS569 3xTL5-28W HFP M2 FTB	1255 mm	655 mm
TBS569 2xTL5-28W HFA M2	1255 mm	355 mm
TBS569 2xTL5-14W HFP M2 FTB	655 mm	355 mm
TBS569 3xTL5-14W HFP M6 FTB	655 mm	655 mm
TBS569 3xTL5-28W HF C6	1255 mm	655 mm
TBS569 2xTL5-28W HF M5	1255 mm	355 mm
TBS569 3xTL5-14W/840 K HFP D6 FTB CAU	655 mm	655 mm
TBS569 3xTL5-28W/840 K HFP C6 FTB CAU	1255 mm	655 mm
TBS569 4xTL5-14W HF M2	655 mm	655 mm
TBS569 2xTL5-28W/840 K HFP C6 FTB CAU	1255 mm	355 mm
TBS569 3xTL5-14W HFP M2 FTB	655 mm	655 mm
TBS569 4xTL5-14W/840 K HFP C6 FTB CAU	655 mm	655 mm
TBS569 4xTL5-14W/840 K HFP M6 FTB CAU	655 mm	655 mm
TBS569 4xTL5-14W HFA M5	655 mm	655 mm
TBS569 3xTL5-14W HFA M2	655 mm	655 mm
TBS569 2xTL5-28W HFP M6 FTB	1255 mm	355 mm
TBS569 3xTL5-28W HF M2	1255 mm	655 mm
TBS569 2xTL5-28W HFE C2	1255 mm	355 mm
TBS569 2xTL5-14W/840 K HFP M6 FTB CAU	655 mm	355 mm
TBS569 3xTL5-14W HF M5	655 mm	655 mm
TBS569 2xTL5-28W HFP M2 FTB	1255 mm	355 mm
TBS569 3xTL5-28W/840 K HFP D6 FTB CAU	1255 mm	655 mm
TBS569 3xTL5-14W HFP D6 FTB	655 mm	655 mm
TBS569 3xTL5-28W HFA M2	1255 mm	655 mm
TBS569 4xTL5-14W HFP D6 FTB	655 mm	655 mm
TBS569 2xTL5-28W HF M2	1255 mm	355 mm
TBS569 4xTL5-14W/840 K HFP D6 FTB CAU	655 mm	655 mm
TBS569 3xTL5-28W HFA M5	1255 mm	655 mm
TBS569 3xTL5-14W/840 K HFP M6 FTB CAU	655 mm	655 mm
TBS569 2xTL5-28W HFA M5	1255 mm	355 mm
TBS569 3xTL5-14W/840 K HFP C6 FTB CAU	655 mm	655 mm
TBS569 3xTL5-14W HF C6	655 mm	655 mm
TBS569 3xTL5-28W HF D6	1255 mm	655 mm
TBS569 4xTL5-14W HFP M6 FTB	655 mm	655 mm
TBS569 2xTL5-14W HFA M2	655 mm	355 mm
TBS569 3xTL5-14W HFA M5	655 mm	655 mm

Dimensional drawing

Product	A	B
TBS569 3xTL5-28W HFP D6 FTB	1255 mm	655 mm
TBS569 2xTL5-28W HF C6	1255 mm	355 mm
TBS569 2xTL5-28W/840 K HFP M6 FTB CAU	1255 mm	355 mm
TBS569 3xTL5-28W HFP M6 FTB	1255 mm	655 mm
TBS569 2xTL5-28W HFP D6 FTB	1255 mm	355 mm

Approval and Application

Ingress protection code IP20

General Information

Lamp family code TL5
 Number of gear units 1 unit
 Product Family Code TBS569

General Information

order code	Gear	Lamp power	Number of light sources	Optic type
911400940080	EBE	14	3	C6
911400940280	EBE	28	2	C6
911400940380	EBE	28	3	C6
911400941480	HFA	14	2	C6
911401118380	HFA	14	3	M2
911401118480	HFA	14	3	M5
911401118580	EBE	14	3	M5
911401118780	EBE	14	4	M2

order code	Gear	Lamp power	Number of light sources	Optic type
911401119080	HFA	28	2	M2
911401119180	EBE	14	3	M2
911401119280	EBE	28	2	M2
911401119380	HFA	28	2	M5
911401119480	EBE	28	2	M5
911401119680	EBE	28	3	M2
911401119880	EBE	28	3	M5

