



# TBS737 Wing-C

## TBS737

Recessed luminaire for TL-5 fluorescent lamps that combine performance with aesthetics in direct and indirect lighting for creating a lighting ambience.

### Features

- TBS737 blends the direct/indirect lighting experience with an even light distribution while offering the option of glare-free highlights or softer, diffused, shadow-less light.
- Elegant and comfortable solution: offers a choice of high efficiency, low-glare micro 3D OLC optics to create a more comfortable environment.

### Application

- Open-plan offices
- Cell-office
- Call-center
- Reception areas
- Corridors
- Retail outlets

# TBS737

## Versions



### TBS737 recessed luminaire

#### Approval and Application

Ingress protection code	IP20
-------------------------	------

#### General Information

Gear	HFA
Lamp family code	TL5
Lamp power	28 W
Number of light sources	2

## General Information

order code	Optic type	order code	Optic type
910403390901	M8	910403391601	D8

