



Sereno TBS869

Sereno TBS869/528

The new Philips range Sereno recessed luminaires are more energy efficient than ever before. The latest optical technology was used to create a highly effective optic, giving rise to new opportunities for saving energy. This family of advanced TL5 recessed luminaire with micro optic technology use up to 25% less energy than standard TL5 solutions. Even greater savings can be made by retrofitting TLD lighting installations with our new TL5 recessed luminaires. The quality of the lighting is maintained, thanks to the Omni directional Lighting Control optic which increases luminous efficacy while reducing glare in all directions and complying with relevant brightness limits. As a result, our luminaires enable sustainable and green lighting solutions to be created. Because daylight-linking and presence-detecting lighting control systems can be optionally packaged into your recessed luminaire lighting solution, your energy consumption can easily be halved in comparison to conventional office lighting solutions.

Features


- Energy efficiency: Sereno advanced TL5 recessed luminaire with micro optic technology use up to 25% less energy than standard TL5 solutions and with PHILIPS advance lighting control up to 75% energy saving.
- Architecturally appealing: comfort visual appearance and ultra flat light with only 47mm in height
- An easy choice offer installation, replacement and maintenance

Application

- General industries
- Representative offices
- Conference rooms
- Small offices
- General open plan offices
- Data processing offices
- Reception and public service areas

Dimensional drawing


TBS528



TBS528



TBS528



TBS869 C

TBS869 C

Approval and Application	
Ingress protection code	IP20
General Information	
Lamp family code	TL5

General Information

order code	Gear	Kombipack	Lamp power	Number of light sources	Optic type	Product Family Code
910403390601	EBP	-	28	2	D8-H	TBS869
910403391901	EBP	Lamp(s) included	14	3	D8-H	TBS869
910403395201	EBP	-	14	3	D8-H	TBS869

Sereno TBS869/528

order code	Gear	Kombipack	Lamp power	Number of light sources	Optic type	Product Family Code
910403392601	HFA	-	28	3	M8	TBS528
910403394901	EBP	-	14	2	M8	TBS528
910403395501	EBP	-	28	2	M8	TBS528

