



MEGALUX – Extensive functionality

Megalux TBS912

Featuring an elegant, compact design, Megalux luminaires are specially designed for use with TL-D tubular fluorescent lamps of 16 or 32 W. Ideal for indoor use such as in offices or commercial areas. Available in recessed and surface-mounted versions, they can be recessed in any type of ceiling (plaster or paneled). Two optic options provide the freedom to create projects that are fully integrated into the environment while also providing efficient and economical lighting. They are easy to install and the ballast is accessed from below without the need to remove the luminaire from the installed location.

Benefits

- Functional and convenient for easy application and quality of light
- Wide range of optics for different uses and effects
- Easy installation and maintenance

Features

- High-gloss aluminum reflectors
- Two wing options: C1 or C5
- Perfect light distribution that enhances your project

Application

- Offices
- Buildings
- Schools
- Universities
- Libraries
- Shops
- Hospitals

Specifications

Megalux TBS912

Type	TBS912
Light source	2 x 16 W / 4 x 16 W / 2 x 32 W TL-D
Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
Materials and finishing	Phosphated steel body of 0.6 mm thickness in white color High-purity aluminum optics High-gloss aluminum parabolic wings (C5) or flat aluminum wings in white color (C1)

Installation	Surface-mounted TBS912: for modular "T" profile, plaster, or paneled ceilings A tilting system pulls the optical system aside to provide access to the lamps and ballasts through the front section
---------------------	--

Versions



General Information

Gear	EB
Lamp family code	TL-D

General Information

Order Code	Full Product Name	Lamp power	Number of light sources	Optic type
820619254431	TBS912 4xTL-D16W/840 EB C5	16 W	4 pcs	High-gloss optic double parabolic
820619257061	TBS912 4xTL-D16W/840 EB C1	16 W	4 pcs	High-gloss mirror flat lamellae louver

Order Code	Full Product Name	Lamp power	Number of light sources	Optic type
919106026431	TBS912 2xTLD-32W/840 EB C1	32 W	2 pcs	High-gloss mirror flat lamellae louver
919106027261	TBS912 2xTL-D32W/840 EB C5	32 W	2 pcs	High-gloss optic double parabolic

