



ELEGANCE – Pure light

Elegance TBS930

With their advanced design and compact size, Elegance luminaires are suitable for use in a wide variety of commercial lighting projects and offices, providing a contemporary and harmonious look. Available in recessed or surface-mounted versions and with two optical system options (C5 and CD), the TBS/SCT 930 luminaires add a touch of sophistication wherever they are installed. They were designed to be used with TL5 lamps of 14, 25, 28, 50 and 54 W - the most advanced technology in fluorescent lighting - which enable high levels of performance and therefore ensure exceptional energy savings.

Benefits

- Elegant design and excellent performance for general and work lighting
- Great visual comfort
- Two optic options for optimum distribution of light and glare control

Features

- High-gloss aluminum reflectors
- Two wing options: CD or C5
- Perfect light distribution that enhances your project

Application

- Offices
- Buildings
- Schools
- Universities
- Libraries
- Shops
- Hospitals

Specifications

Type	TBS930	Light source	2 x 14 W / 2 x 25 W / 2 x 28 W / 2 x 50 W / 2 x 54 W TL5
------	--------	--------------	--

Elegance TBS930

Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
Materials and finishing	Body: phosphated steel of 0.5 mm thickness in white color
	High-purity aluminum optics
	Aluminum or polycarbonate wings
Installation	Surface-mounted TBS930: for "T" profile or plaster ceilings
	For plaster modules: 2 x 14 W: 580 x 140 mm; 28/54 W: 1180 x 140 mm
	A tilting system pulls the optical system aside to provide access to the lamps. In the recessed version access to the ballast is via the luminaire, whereas in the surface-mounted version the optical system is removed and the ballast is on the side

Versions



General Information	
Gear	EB
Lamp family code	TL5
Number of light sources	2 pcs

General Information

Order Code	Full Product Name	Lamp power	Optic type
919106027461	TBS930 2xTL5-14W/840 EB C5	14 W	High-gloss optic double parabolic
919106027471	TBS930 2xTL5-14W/840 EB CD	14 W	High-gloss optic decorative
919106027487	TBS930 2xTL5-28W/840 EB C5	28 W	High-gloss optic double parabolic

Order Code	Full Product Name	Lamp power	Optic type
919106027541	TBS930 2xTL5-54W/840 EB C5	54 W	High-gloss optic double parabolic
919106027551	TBS930 2xTL5-54W/840 EB CD	54 W	High-gloss optic decorative
919106031161	TBS930 2xTL5-28W/840 EB CD	28 W	High-gloss optic decorative

