



T5 Essential Batten TCH086C – A brighter way to extra savings

TCH086

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Benefits

- No worries about safety and reliability
- Easy to install and maintain
- 25% energy savings compared with T8 batten

Features

- Wide voltage coverage
- Flicker-free Buzz-free
- Trunkable, up to 8 pieces (TCH086 only)

Application

- Cove lighting
- Counter and background lighting
- Home

TCH086

Versions



T5 Essential Batten TCH084

T5 Essential Batten TCH084

Operating and Electrical

Input Voltage 220 to 240 V

General Information

Lamp family code TL5

General Information

Order Code	Full Product Name	Gear	Lamp power	Order Code	Full Product Name	Gear	Lamp power
911400874380	TCH084 TL5-28W/865 HF 220-240V	HF	28 W	911400874680	TCH084 TL5-14W/865 EI 220-240V	EI	14 W
911400874480	TCH084 TL5-28W/830 HF 220-240V	HF	28 W	911400874780	TCH084 TL5-14W/830 EI 220-240V	EI	14 W
911400874580	TCH084 TL5-28W/840 HF 220-240V	HF	28 W	911400874880	TCH084 TL5-14W/840 EI 220-240V	EI	14 W

