




T5 Essential Batten TCH086C – A brighter way to extra savings

TCH086

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Преимущества

- No worries about safety and reliability
- Easy to install and maintain
- 25% energy savings compared with T8 batten

Характеристики

- Wide voltage coverage
- Flicker-free Buzz-free
- Trunkable, up to 8 pieces (TCH086 only)

Применение

- Cove lighting
- Counter and background lighting
- Home

TCH086

Versions



Эксплуатационные и электрические характеристики	
Входное напряжение	220 to 240 V
Общая информация	
Код лампового семейства	TL5

Общая информация

Order Code	Full Product Name	ПРА	Мощность лампы
911400874380	TCH084 TL5-28W/865 HF 220-240V	HF	28 W
911400874480	TCH084 TL5-28W/830 HF 220-240V	HF	28 W
911400874580	TCH084 TL5-28W/840 HF 220-240V	HF	28 W

Order Code	Full Product Name	ПРА	Мощность лампы
911400874680	TCH084 TL5-14W/865 EI 220-240V	EI	14 W
911400874780	TCH084 TL5-14W/830 EI 220-240V	EI	14 W
911400874880	TCH084 TL5-14W/840 EI 220-240V	EI	14 W

Polar Wide Diagrams

IFPS_TCH086 1xTL5-28W HF-Polar Normal
(separate)

IFPS_TCH086 1xTL5-14W EI-Polar Normal
(separate)

IFPS_TCH086 1xTL5-21W EI-Polar Normal
(separate)

