



Pentura Mini CC – brighten your workload

Pentura Mini CC

Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.

Benefits

- Ultra-slim decorative batten providing a cost-effective, ready-to-install mini fluorescent solution for domestic use
- The energy-saving benefits of miniature fluorescent lamp technology with lightweight electronics and a patented internal reflector for improved lighting performance
- Easy to install to provide bright light where needed, even if installation space is limited

Features

- Miniature fluorescent lamp technology
- Patented internal reflector
- Polycarbonate diffuser
- Push-button connection blocks

Application

- Home lighting
- Undershelf lighting
- Task lighting

Specifications

Type	TCH129	Light source	Fluorescent: - 1 x TL5 Essential / G5 / 8, 14, 21, 28 W
------	--------	--------------	--

Pentura Mini CC


	- 1 x MASTER TL5 / G5 / 35 W
Lamp included	Yes (lamp color 830 or 840, 8 W version is 827) No (35 W version only)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF)

Material	Housing and end caps: polycarbonate, white Cover: polycarbonate, RAL 9023
Installation	Individual or in-line; screw mounting
Remarks	All installation accessories included; ready to install
Main applications	Home, undershelf, task lighting

Versions



Dimensional drawing



Product	A
TCH129 1xTL5-28W/840 HF	1205 mm

Product details

Interlinking cables



Ultra-slim batten



