



Pentura Mini CC – brighten your workload

Pentura Mini CC

Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.

Benefits

- Ultra-slim decorative batten providing a cost-effective, ready-to-install mini fluorescent solution for domestic use
- The energy-saving benefits of miniature fluorescent lamp technology with lightweight electronics and a patented internal reflector for improved lighting performance
- Easy to install to provide bright light where needed, even if installation space is limited

Features

- Miniature fluorescent lamp technology
- Patented internal reflector
- Polycarbonate diffuser
- Push-button connection blocks

Application

- Home lighting
- Undershelf lighting
- Task lighting

Specifications

Type	TCH129	Light source	Fluorescent: - 1 x TL5 Essential / G5 / 8, 14, 21, 28 W
------	--------	--------------	--

Pentura Mini CC


	- 1 x MASTER TL5 / G5 / 35 W
Lamp included	Yes (lamp color 830 or 840, 8 W version is 827) No (35 W version only)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF)

Material	Housing and end caps: polycarbonate, white Cover: polycarbonate, RAL 9023
Installation	Individual or in-line; screw mounting
Remarks	All installation accessories included; ready to install
Main applications	Home, undershelf, task lighting

Versions



Dimensional drawing



Product	A
TCH129 1xTL5-35W HF	1505 mm
TCH129 1xTL5-28W/830 HF	1205 mm
TCH129 1xTL5-28W/840 HF	1205 mm
TCH129 1xTL5-21W/830 HF	905 mm
TCH129 1xTL5-21W/840 HF	905 mm
TCH129 1xTL5-14W/830 HF	605 mm
TCH129 1xTL5-14W/840 HF	605 mm

Product details

Interlinking cables



Ultra-slim batten



Pentura Mini CC

Approval and Application

Ingress protection code	IP20
-------------------------	------

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class II (II)
Flammability mark	F
Gear	HF
Glow-wire test	850/5
Lamp family code	TL5
Number of light sources	1

General Information

Order Code	Full Product Name	Kombipack	Lamp power
00873899	TCH129 1xTL5-14W/840 HF	Lamp(s) included	14 W
00874599	TCH129 1xTL5-14W/830 HF	Lamp(s) included	14 W
00875299	TCH129 1xTL5-21W/840 HF	Lamp(s) included	21 W
00876999	TCH129 1xTL5-21W/830 HF	Lamp(s) included	21 W
00877699	TCH129 1xTL5-28W/840 HF	Lamp(s) included	28 W
00878399	TCH129 1xTL5-28W/830 HF	Lamp(s) included	28 W
81518399	TCH129 1xTL5-35W HF	-	35 W

