



# Pentura Mini CC – brighten your workload

## Pentura Mini CC

Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.

### Benefits

- Ultra-slim decorative batten providing a cost-effective, ready-to-install mini fluorescent solution for domestic use
- The energy-saving benefits of miniature fluorescent lamp technology with lightweight electronics and a patented internal reflector for improved lighting performance
- Easy to install to provide bright light where needed, even if installation space is limited

### Features

- Miniature fluorescent lamp technology
- Patented internal reflector
- Polycarbonate diffuser
- Push-button connection blocks

### Application

- Home lighting
- Undershelf lighting
- Task lighting

### Specifications

Type	TCH129	Light source	Fluorescent: - 1 x TL5 Essential / G5 / 8, 14, 21, 28 W
------	--------	--------------	--

Pentura Mini CC


	- 1 x MASTER TL5 / G5 / 35 W
Lamp included	Yes (lamp color 830 or 840, 8 W version is 827) No (35 W version only)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF)

Material	Housing and end caps: polycarbonate, white Cover: polycarbonate, RAL 9023
Installation	Individual or in-line; screw mounting
Remarks	All installation accessories included; ready to install
Main applications	Home, undershelf, task lighting

Versions



Dimensional drawing



Product	A
TCH129 1xTL5-35W HF	1505 mm
TCH129 1xTL5-28W/830 HF	1205 mm
TCH129 1xTL5-28W/840 HF	1205 mm
TCH129 1xTL5-14W/840 HF	605 mm
TCH129 1xTL5-21W/840 HF	905 mm
TCH129 1xTL5-14W/830 HF	605 mm
TCH129 1xTL5-21W/830 HF	905 mm

Product details

Interlinking cables



Ultra-slim batten



## Pentura Mini CC

### Approval and Application

Ingress protection code	IP20
-------------------------	------

### Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

### General Information

CE mark	CE mark
---------	---------

Protection class IEC	Safety class II
----------------------	-----------------

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

Gear	HF
------	----

Glow-wire test	Temperature 850 °C, duration 5 s
----------------	-------------------------------------

Lamp family code	TL5
------------------	-----

Number of light sources	1 pc
-------------------------	------

### General Information

Order Code	Full Product Name	Kombipack	Lamp power
910502545818	TCH129 1xTL5-14W/840 HF	Lamp(s) included	14 W
910502545918	TCH129 1xTL5-14W/830 HF	Lamp(s) included	14 W
910502546618	TCH129 1xTL5-21W/840 HF	Lamp(s) included	21 W
910502546718	TCH129 1xTL5-21W/830 HF	Lamp(s) included	21 W
910502546818	TCH129 1xTL5-28W/840 HF	Lamp(s) included	28 W
910502546918	TCH129 1xTL5-28W/830 HF	Lamp(s) included	28 W
910503610018	TCH129 1xTL5-35W HF	-	35 W

