



SlimLine – Extensive functionality

SlimLine TCS020

SlimLine luminaires are compact and versatile to allow better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

Benefits

- Extensive functionality in recessed and surface-mounted luminaires
- The best choice for high-performance luminaires with four optic options
- Slim design that integrates with the architecture
- Easy installation and maintenance

Features

- Perfect light distribution that enhances your project
- Slim design

Application

- Offices
- Shops
- Banks
- Schools
- Hotels

Specifications

Type	TCS020
Light source	2 x 16 W / 2 x 32 W / 2 x 25 W / 2 x 28 W / 2 x 50 W / 2 x 54 W TL-D / TL5

Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
	Electronic Touch&Dim DALI (HFD)
Optical cover	Textured transparent acrylic diffuser - diffuse light (AC)

SlimLine TCS020

Materials and finishing Phosphated steel-plate body of 0.5 mm thickness in white color

High-purity aluminum optics. Parabolic wings in high-gloss aluminum (C5) or flat aluminum wings in white color (C1)

Installation For plaster modules: 615 x 165 mm or 1230 x 165 mm

Versions



General Information

Gear	EB
Number of light sources	2 pcs

General Information

Order Code	Full Product Name	Optical cover/ lens type	Lamp family code	Lamp power	Optic type
820619256281	TCS020 2xTL-D32W/840 EB C5	-	TL-D	32 W	High-gloss optic double parabolic
820619256301	TCS020 2xTL-D32W/840 EB C1	-	TL-D	32 W	High-gloss mirror flat lamellae louver
919106031791	TCS020 2xTL5-28W/840 EB C5	-	TL5	28 W	High-gloss optic double parabolic
919106031801	TCS020 2xTL5-28W/840 EB C1	-	TL5	28 W	High-gloss mirror flat lamellae louver
919106031811	TCS020 2xTL5-54W/840 EB C5	-	TL5	54 W	High-gloss optic double parabolic
919106031821	TCS020 2xTL5-54W/840 EB C1	-	TL5	54 W	High-gloss mirror flat lamellae louver
919106032731	TCS020 2xTL5-25W/840 EB C5	-	TL5	25 W	High-gloss optic double parabolic
919106032741	TCS020 2xTL5-25W/840 EB C1	-	TL5	25 W	High-gloss mirror flat lamellae louver
919106032751	TCS020 2xTL5-50W/840 EB C5	-	TL5	50 W	High-gloss optic double parabolic
919106032761	TCS020 2xTL5-50W/840 EB C1	-	TL5	50 W	High-gloss mirror flat lamellae louver

Order Code	Full Product Name	Optical cover/ lens type	Lamp family code	Lamp power	Optic type
919106027271	TCS020 2xTL-D32W/840 EB AC	Acrylic bowl/cover	TL-D	32 W	-
919106027321	TCS020 2xTL-D32W/840 EB R-H	-	TL-D	32 W	Reflector high reflectance
919106032691	TCS020 2xTL5-50W/840 EB R-H	-	TL5	50 W	Reflector high reflectance
919106032701	TCS020 2xTL5-25W/840 EB R-H	-	TL5	25 W	Reflector high reflectance
919106032711	TCS020 2xTL5-28W/840 EB R-H	-	TL5	28 W	Reflector high reflectance
919106032721	TCS020 2xTL5-54W/840 EB R-H	-	TL5	54 W	Reflector high reflectance

