



# EcoFIX – The new standard for lighting in offices

## EcoFIX TCS262

EcoFIX is a modular luminaire for TL5 tubular fluorescent lamps. At only 55 mm in height, it is especially designed for ceilings of 625 mm. It is available in very high-performance recessed versions for two, three or four TL5 lamps of 14, 25, 28, 50 or 54 W with compact dimensions which integrate better into the environment. With very high-performance and efficient C6 optics, it offers excellent light control thanks to its innovative optical system with omni-directional luminance control (OLC), which makes maximum use of the light emitted by the lamp without creating any glare.

### Benefits

- Square or rectangular luminaires for recessed or surface mounting
- At only 55 mm in height, it is ideal for new constructions or renovations where the space between the ceiling and the slab is limited
- Luminaire with innovative design which integrates into the environment, making the lighting softer

### Features

- C6 optical system with excellent glare control
- Square or rectangular versions
- Luminaire can be recessed or surface-mounted
- At only 55 mm in height, it is ideal for new constructions or renovations where the space between the ceiling and the slab is limited

# EcoFIX TCS262

## Application

- Offices
- Schools
- Libraries
- Shops
- Hospitals
- Public buildings
- Universities

## Specifications

Type	TCS262
Light source	2 x 25 W / 2 x 28 W / 2 x 50 W / 2 x 54 W / 3 x 13 W / 3 x 14 W / 4 x 13 W / 4 x 14 W / 4 x 25 W / 4 x 28 W / 4 x 50 W / 4 x 54 W TL5
Mains voltage	Electronic 220 V / 60-50 Hz: (EB) Electronic Touch&Dim DALI (HFD)

Materials and finishing	Body: phosphated steel of 0.5 mm thickness in white color High-purity aluminum optics and wings
Installation	Surface-mounted TCS262

## Versions



### General Information

Gear	EB
Lamp family code	TL5
Optic type	High-gloss optic double parabolic closed

## General Information

Order Code	Full Product Name	Lamp power	Number of light sources
919106029132	TCS262 2xTL5-25W/840 EB C6	25 W	2 pcs
919106029149	TCS262 2xTL5-28W/840 EB C6	28 W	2 pcs
919106029641	TCS262 2xTL5-54W/840 EB C6	54 W	2 pcs
919106031391	TCS262 2xTL5-50W/840 EB C6	50 W	2 pcs

Order Code	Full Product Name	Lamp power	Number of light sources
919106029152	TCS262 3xTL5-13W/840 EB C6	13 W	3 pcs
919106029161	TCS262 3xTL5-14W/840 EB C6	14 W	3 pcs
919106029172	TCS262 4xTL5-13W/840 EB C6	13 W	4 pcs
919106029181	TCS262 4xTL5-14W/840 EB C6	14 W	4 pcs

