



TCS398

TCS398 C

TCS398 is also suitable for TL5 or TLD fluorescent lamps, with a wide range of high-performance optics. The luminaire is a direct version and can be surface-mounted or suspended. Two types of suspension systems are available: wire and tube suspension. The luminaire can be mounted individually and in configurations.

Features


- Wide selection of best-in-class optics, customized to meet your specific needs
- Choice of fluorescent lamps TL5 or TLD: increased efficiency, luminaire is optimized with TL5 version
- Compact dimensions, clean lines and subtly-round edges: offer stylish design & a high quality appearance
- Semi-matt housing (RAL9010), suitable for modern interiors
- Philips V-clips to ease installation and maintenance
- Choice of suspended or surface mounting offers flexibility in application
- Top mirror on request: offers higher luminaire performance
- In-line mounting on request for a smooth visual appearance

Application

- Club offices
- Cell offices
- Hive offices
- Meet office spaces
- Lobby office spaces
- Recreational areas
- Public buildings, schools, and hospitals
- General industries


TCS398 C

Versions



X-tend TCS398 surface-mounted
luminaire

Dimensional drawing



Xtend TCS398 C

Product	A	B	C
TCS398 C 2xTL-D36W HFE M6	1240 mm	1310 mm	195 mm
TCS398 C 2xTL5-35W HFP M6 FTB	1488 mm	1558 mm	195 mm
TCS398 C 2xTL5-28W K HFP M6 FTB	1188 mm	1258 mm	195 mm
TCS398 C 2xTL5-28W HFP M2 FTB	1188 mm	1258 mm	195 mm
TCS398 C 2xTL-D58W HFP M2	1540 mm	1610 mm	195 mm
TCS398 C 2xTL5-35W HFE M2	1488 mm	1558 mm	195 mm
TCS398 C 2xTL-D36W HFP D6 FTB	1240 mm	1310 mm	195 mm
TCS398 C 2xTL5-35W K HFP D6 FTB	1488 mm	1558 mm	195 mm
TCS398 C 2xTL5-28W HFE D6	1188 mm	1258 mm	195 mm
TCS398 C 2xTL5-35W K HFP M6 FTB	1488 mm	1558 mm	195 mm
TCS398 C 2xTL5-28W HFP M6 FTB	1188 mm	1258 mm	195 mm
TCS398 C 1xTL-D36W K HFP D6 FTB	1240 mm	1310 mm	195 mm
TCS398 C 1xTL-D58W K HFP M6 FTB	1540 mm	1610 mm	195 mm
TCS398 C 2xTL-D58W HFP D6	1540 mm	1610 mm	195 mm
TCS398 C 1xTL-D58W K HFP D6 FTB	1540 mm	1610 mm	195 mm
TCS398 C 1xTL5-28W K HFP D6 FTB	1188 mm	1258 mm	195 mm
TCS398 C 2xTL-D36W HFP M6 FTB	1240 mm	1310 mm	195 mm
TCS398 C 2xTL5-35W HFE D6	1488 mm	1558 mm	195 mm
TCS398 C 1xTL-D36W K HFP M6 FTB	1240 mm	1310 mm	195 mm
TCS398 C 2xTL-D58W HFP M6	1540 mm	1610 mm	195 mm
TCS398 C 2xTL-D58W HFP M6 FTB	1540 mm	1610 mm	195 mm
TCS398 C 2xTL-D36W HFE M2	1240 mm	1310 mm	195 mm
TCS398 C 2xTL-D58W HFP M2 FTB	1540 mm	1610 mm	195 mm
TCS398 C 2xTL5-35W HFP M2 FTB	1488 mm	1558 mm	195 mm
TCS398 C 1xTL5-28W K HFP M6 FTB	1188 mm	1258 mm	195 mm
TCS398 C 2xTL-D58W HFP D6 FTB	1540 mm	1610 mm	195 mm
TCS398 C 2xTL5-35W HFE M6	1488 mm	1558 mm	195 mm
TCS398 C 2xTL-D36W HFP M2 FTB	1240 mm	1310 mm	195 mm
TCS398 C 2xTL-D58W K HFP M6 FTB	1540 mm	1610 mm	195 mm
TCS398 C 2xTL-D36W HFE D6	1240 mm	1310 mm	195 mm
TCS398 C 2xTL5-28W HFP D6 FTB	1188 mm	1258 mm	195 mm
TCS398 C 2xTL-D36W K HFP D6 FTB	1240 mm	1310 mm	195 mm
TCS398 C 1xTL5-35W K HFP M6 FTB	1488 mm	1558 mm	195 mm
TCS398 C 2xTL5-28W HFE M6	1188 mm	1258 mm	195 mm
TCS398 C 2xTL5-35W HFP D6 FTB	1488 mm	1558 mm	195 mm
TCS398 C 2xTL-D36W K HFP M6 FTB	1240 mm	1310 mm	195 mm
TCS398 C 2xTL5-28W K HFP D6 FTB	1188 mm	1258 mm	195 mm
TCS398 C 2xTL-D58W K HFP D6 FTB	1540 mm	1610 mm	195 mm
TCS398 C 1xTL5-35W K HFP D6 FTB	1488 mm	1558 mm	195 mm
TCS398 C 2xTL5-28W HFE M2	1188 mm	1258 mm	195 mm


Accessories

ZPH300

ZPS398



Ordercode 910403301880



Ordercode 910403313680

Approval and Application

Ingress protection code IP20

General Information

Product Family Code TCS398

General Information

order code	Compensation circuit	Gear	Kombipack	Lamp family code	Lamp power	Number of light sources	Optic type
910403398201	-	EBP	-	TL-D	58	2 pcs	Matt mirror ribbed lamellae louver
910403398301	-	EBP	-	TL-D	58	2 pcs	Matt optic double parabolic louver closed
910403398401	-	EBP	-	TL-D	58	2 pcs	Semi-high-gloss optic double parabolic
911400631480	-	EBP	Lamp(s) included	TL-D	36	2 pcs	Matt optic double parabolic louver closed
911400631680	-	EBP	-	TL-D	36	2 pcs	Semi-high-gloss optic double parabolic
911400631780	-	EBP	-	TL-D	36	2 pcs	Matt optic double parabolic louver closed
911400633180	-	EBP	-	TL5	35	2 pcs	Semi-high-gloss optic double parabolic
911400633280	-	EBP	-	TL5	35	2 pcs	Matt mirror ribbed lamellae louver
911400633380	-	EBP	-	TL5	28	2 pcs	Matt mirror ribbed lamellae louver
911400633480	-	EBP	-	TL5	28	2 pcs	Semi-high-gloss optic double parabolic
911400633580	-	HFE	-	TL-D	36	2 pcs	Matt optic double parabolic louver closed
911400633680	-	EBP	Lamp(s) included	TL5	28	1 pc	Matt optic double parabolic louver closed
911400633880	-	EBP	Lamp(s) included	TL5	28	2 pcs	Matt optic double parabolic louver closed
911400634080	-	EBP	-	TL5	28	2 pcs	Matt optic double parabolic louver closed
911400634180	-	EBP	-	TL5	35	2 pcs	Matt optic double parabolic louver closed
911400634280	-	HFE	-	TL-D	36	2 pcs	Matt mirror ribbed lamellae louver
911400634380	-	HFE	-	TL-D	36	2 pcs	Semi-high-gloss optic double parabolic
911400634580	-	EBP	Lamp(s) included	TL-D	36	1 pc	Matt optic double parabolic louver closed
911400634880	-	HFE	-	TL5	28	2 pcs	Matt optic double parabolic louver closed
911400634980	-	HFE	-	TL5	35	2 pcs	Matt mirror ribbed lamellae louver
911400635080	-	HFE	-	TL5	28	2 pcs	Semi-high-gloss optic double parabolic
911400635180	-	HFE	-	TL5	35	2 pcs	Semi-high-gloss optic double parabolic
911400635280	-	HFE	-	TL5	35	2 pcs	Matt optic double parabolic louver closed
911400635480	-	EBP	Lamp(s) included	TL5	28	2 pcs	Semi-high-gloss optic double parabolic
911400635580	-	EBP	Lamp(s) included	TL5	28	1 pc	Semi-high-gloss optic double parabolic
911400635680	-	EBP	Lamp(s) included	TL5	35	2 pcs	Matt optic double parabolic louver closed
911400637480	-	HFE	-	TL5	28	2 pcs	Matt mirror ribbed lamellae louver

