



Arano asymmetric – high-performance wall-washer

Arano, asymmetric

Arano asymmetric is a wall-washer luminaire incorporating 1 or 2 TL5 fluorescent lamps. Its best-in-class lighting performance ensures a uniform light distribution, fully compliant with the current norms for office, school and shop lighting. Featuring the Arano family design aesthetic, this luminaire is available in white and aluminum finishes.

Benefits

- Minimalistic design offering very comfortable lighting
- Office compliant micro optic solutions
- Allows for coupling into line arrangements

Features

- Minimalistic design: white or aluminum finish
- Choice of one or two TL5 fluorescent lamps
- Office norm-compliant micro optics
- Mounting individually or in lines

Application

- Offices
- Schools
- Department stores

Specifications

Type	TCS649	Light source	Fluorescent: - 1 x or 2 x MASTER TL5 / G5 / 28, 35, 49, 54, 80 W
------	--------	--------------	---

Arano, asymmetric


Lamp included	Yes (827, 830 or 840)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz:
	- High Frequency Performer (HFP)
	- High Frequency Regulator, DALI (HFD)
	- High Frequency Regulator (HFR)
Optic	Wall-washer, asymmetrical mirror (A)

Option	Fuse (FU) included
Material	Housing: natural anodized aluminum (ALU) or in white (WH)
	End caps: natural anodized aluminum (ALU) or in white (WH)
	Optic: aluminum
Installation	Individual, mounting by screw fixing
Main applications	Office, schools, department stores

Versions



Dimensional drawing



Product	A	B
TCS649 1x54W/830 HFP A ALU	1194 mm	1281 mm

