

## Fit-for-use TL5 lamp

### TL5 EssentialView Super 80

Philips TL5 EssentialView is a compact, highly efficient fluorescent lamp that provides functional light at an affordable price.

#### Benefits

- Same lifetime as Standard TL-D and most cost-efficient TL5 lamps
- Slim tube allows more compact and flexible luminaire design
- Maximum lumen output at suitable ambient temperature

#### Features

- Small diameter of only 16 mm
- To be used with electronic ballast for TL5 only
- Operating temperature from 5 to 50 °C

#### Application


- Offices, shops, supermarkets, schools, hospitals and industrial facilities

#### Versions



# TL5 EssentialView Super 80

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 EssentialView 14W/865	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
1SL/40					

