



Shatterfree fluorescent lighting

MASTER TL5 High Output Secura

This TL5 High Output Secura lamp (tube diameter 16 mm) has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. This lamp is compliant with HACCP regulations and supports HACCP certification.

Benefits

- Special protective coating around the lamp prevents products from contamination in case of accidental lamp breakage
- The protective coating has a high temperature-resistance and no degradation to be expected under influence of temperature or UV within specified lamp life (50% failures @ 3 hrs switching cycle)
- Making luminaires compliant with relevant standards in the industry, such as HACCP, ISO 22000 and IEC 61549

Features

- Protective coating around the lamp
- Fully compliant with IEC 61549 - Fragment Retention Lamp Standard
- Superior coating material (Teflon) with high temperature-resistance (up to 200 °C) and no degradation under influence of temperature or UV
- Single blue ring around one end for identification
- Direct retrofit for all TL5 HO lamps

Application

- For use where contamination resulting from lamp breakage must be prevented, e.g. in food industry, suppliers to the food industry, health care, pharmaceuticals, cleanrooms etc.
- Suitable for use in environments with increased risk of breakage, e.g. sports halls

MASTER TL5 High Output Secura

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Versions



LPPR TL5HO8SE

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Secura 49W/840 UNP/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm
MASTER TL5 HO Secura 54W/840 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
MASTER TL5 HO Secura 80W/840 UNP/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

MASTER TL5 High Output Secura

General Information	
Cap-Base	G5
Light Technical	
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	1.2 mg

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
927927684018	MASTER TL5 HO Secura 49W/840 UNP/40	89 lm/W	4,250 lm
927929184018	MASTER TL5 HO Secura 54W/840 UNP/40	83 lm/W	4,425 lm
927929684018	MASTER TL5 HO Secura 80W/840 UNP/40	82 lm/W	6,550 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927927684018	MASTER TL5 HO Secura 49W/840 UNP/40	0.255 A	49.4 W
927929184018	MASTER TL5 HO Secura 54W/840 UNP/40	0.455 A	53.8 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927929684018	MASTER TL5 HO Secura 80W/840 UNP/40	0.530 A	80.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927927684018	MASTER TL5 HO Secura 49W/840 UNP/40	50 kWh
927929184018	MASTER TL5 HO Secura 54W/840 UNP/40	54 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927929684018	MASTER TL5 HO Secura 80W/840 UNP/40	80 kWh

