



Uzun ömürlü floresanlı aydınlatma

MASTER TL5 High Output Xtra

Bu TL5 lamba (tüp çapı 16 mm) bir TL5 High Output lambasının avantajlarını (TL5 HO lambaları, yüksek ışık çıkışı gerektiren kurulumlar için çok uygundur ve mükemmel lümen sürekliliği ve renksel geriverim sağlarlar) uzun ve güvenilir bir kullanım ömrüyle bir araya getirmektedir. Bu da sonuç olarak, son derece düşük bakım maliyetleri ve pahalı spot yenilemelerinden kurtulma anlamına gelir. Ana uygulama alanları arasında lamba yenileme maliyetlerinin ve/veya iş kesintisi maliyetlerinin yüksek olduğu yerler bulunur.

Faydaları

- Longer lifetime and fewer early failures mean lower maintenance costs and facilitate change from spot to group replacement
- Less waste and disposal cost at end-of-life
- Allows system miniaturisation with maximum luminaire design freedom

Özellikler


- Significant reduction of early failures through advanced long life technology
- Extra long lifetime
- Designed for high light output and system miniaturization (40% thinner than TL-D lamps)
- Maximum light output reached at approximately 35 °C in free-burning position if an electronic driver with cut-off feature is used
- Low mercury dose

Uygulama


- Where maintenance costs are high, e.g. high ceilings or other hard-to-reach locations
- Department stores, supermarkets, warehouses, production halls and public areas like car parks and railway stations

MASTER TL5 High Output Xtra

Versions



Boyutlu çizim



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Xtra 80W/840 SLV/20	17 mm	1449,0 mm	1456,1 mm	1453,7 mm	1463,2 mm

